



Immerse yourself in the game with the curved GB3266QSU Red Eagle with 144Hz refresh rate

The 1500R curved VA panel with 144Hz refresh rate, 1ms MPRT and the 2560x1440 resolution gives you an immersive viewing experience and guarantees superb image quality. The height adjustable stand ensures you can easily adjust the screen position and easily customizable screen settings using the predefined and custom gaming modes along with the Black Tuner function gives you control over the dark scenes to make sure details are always clearly visible.



CURVED DESIGN 1500R

Inspired by the human field of view, the 1500R curvature of the screen guarantees a realistic and comfortable viewing experience allowing you to really immerse yourself in the game.



1ms

Fast response time is key to ultra-smooth gaming. It reduces ghosting and blurring providing the user with an improved graphic performance.

01 DISPLAY CHARACTERISTICS

Diagonal	31.5", 80cm
Panel	VA LED, matte finish
Curved	1500R
Native resolution	2560 x 1440 @144Hz (3.7 megapixel WQHD)
Aspect ratio	16:9
Brightness	400 cd/m ² typical
Static contrast	3000:1 typical
Advanced contrast	80M:1
Response time (MPRT)	1ms
Viewing zone	horizontal/vertical: 178°/178°, right/left: 89°/89°, up/down: 89°/89°
Colour support	16.7mIn (sRGB: 96%, NTSC: 72%)
Horizontal Sync	30 - 225kHz
Vertical Sync	48 - 144Hz
Viewable area W x H	697.3 x 392.3mm, 27.5 x 15.4"
Pixel pitch	0.272mm
Colour	matte,

02 INTERFACES / CONNECTORS / CONTROLS

Signal input	HDMI x2 (HDMI1: max. 2560 x 1440 @75Hz, HDMI2: max.2560 x 1440 @144Hz) DisplayPort x2
USB HUB	x4 (2x v.3.0 DC5V, 900mA, 2x v.2.0 DC5V, 500mA)
HDCP	yes
Headphone connector	yes

03 FEATURES

Blue light reducer	yes
Flicker free	yes
FreeSync support	DP: 2560 x 1440 @144Hz, HDMI2: 2560 x 1440 @144Hz
HDR	yes (HDR ready)
Control buttons	joystick controller: Power / Menu, Up / Input Select, Down, Left / ECO, Right/ Volume
User controls	picture adjust (contrast, brightness, OD, ACR, ECO, blue light reducer, black tuner, MBR, gamma), input select (auto, manual), audio adjust (volume, mute), store user settings, colour settings (colour temp., 6-Axis, user preset), image adjust (i-Style colour, X-Res Technology, sharp and soft, HDMI range, direct drive mode, video mode adjust), language, setup menu (OSD H. position, OSD V. position, OSD time, opening logo, HDR, AMD FreeSync Premium, LED), display information, reset
Speakers	2 x 5W
Convenience	Kensington-lock™ prepared, DDC2B, Mac OSX

04 MECHANICAL

Display position adjustments	height, swivel, tilt
Height adjustment	120mm
Swivel stand	90°; ° left; 45° right
Tilt angle	22° up; 5° down
VESA mounting	100 x 100mm

Cable management system	yes
-------------------------	-----

05 ACCESSORIES INCLUDED

Cables	power, USB, HDMI, DP
Other	quick start guide, safety guide

06 POWER MANAGEMENT

Power supply unit	external
Power supply	DC DC 19 V
Power usage	47W typical, 0.5W stand by, 0.3W off mode

07 SUSTAINABILITY

Regulations	CE, TÜV-Bauart, EAC, RoHS support, WEEE
Energy efficiency class	B
Other	REACH SVHC above 0.1%: Lead

08 DIMENSIONS / WEIGHT

Product dimensions W x H x D	712.5 x 452 (572) x 230mm
Box dimensions W x H x D	836 x 527 x 248mm
Weight (without box)	9kg
Weight (with box)	13.5kg
EAN code	4948570117383

09 EU ENERGY EFFICIENCY LABEL

Manufacturer	iiyama
Model	G-Master GB3266QSU-B1
Energy efficiency class	B
Visible screen diagonal	80cm; "; (31.5" segment)
ON mode power consumption	40.8W
Annual energy consumption	60kWh/annum*
Power in Standby	0.5W stand by
Power in OFF Mode	0.3W off mode
Resolution	2560 x 1440

*This is information under Regulation (EU) No 1062/2010.*Based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.*

All trademarks and registered trademarks acknowledged. E & O E. Specification subject to change without notice. All LCD's comply with ISO-9241-307:2008 in connection with pixel defects.

© IIYAMA CORPORATION. ALL RIGHTS RESERVED