



## Immerse yourself in the game with the curved G2466HSU with 165Hz refresh rate

Offering an immersive viewing experience, the 1500R curved VA panel with 165Hz refresh rate, 1ms MPRT and the 1920x1080 resolution guarantees superb image quality.

The ability to customize the screen settings using the predefined and custom gaming modes along with the Black Tuner function gives you total control over the dark scenes and makes sure details are always clearly visible.



### CURVED DESIGN 1500R

Inspired by the human field of view, the 1500R curvature of the screen guarantees a realistic and comfortable viewing experience allowing you to really immerse yourself in the game.



### 1ms

Fast response time is key to ultra-smooth gaming. It reduces ghosting and blurring providing the user with an improved graphic performance.

## 01 DISPLAY CHARACTERISTICS

Diagonal	23.6", 60cm
Panel	VA LED, matte finish
Curved	1500R
Native resolution	1920 x 1080 @165Hz (2.1 megapixel Full HD)
Aspect ratio	16:9
Brightness	250 cd/m² typical
Static contrast	3000:1 typical
Advanced contrast	80M:1
Response time (MPRT)	1ms
Viewing zone	horizontal/vertical: 178°/178°, right/left: 89°/89°, up/down: 89°/89°
Colour support	16.7mln
Horizontal Sync	30 - 184kHz
Vertical Sync	40 - 165Hz
Viewable area W x H	521.39 x 293.28mm, 20.5 x 11.5"
Pixel pitch	0.271mm
Colour	matte,

## 02 INTERFACES / CONNECTORS / CONTROLS

Signal input	HDMI x2 DisplayPort x1
USB HUB	x2 (v.2.0 DC5V, 500mA)
HDCP	yes
Headphone connector	yes

## 03 FEATURES

Blue light reducer	yes
Flicker free	yes
FreeSync support	1920 x 1080 @165Hz
HDR	yes (HDR ready)
OSD languages	EN, DE, FR, ES, IT, RU, JP, CZ, NL, PL
Control buttons	Power, joystick controller: Menu, Up/ i-Style colour, Down/ Input Select, Left/ Eco Mode, Right/ Volume
User controls	picture adjust (contrast, brightness, OD, ACR, ECO, blue light reducer, black tuner, colour saturation, gamma), input select (auto, manual), audio (volume, mute), store user settings, colour settings (colour temp., user preset), image adjust (i-Style colour, sharp and soft, HDMI RGB range, video mode adjust), language, setup menu (OSD H. position, OSD V. position, OSD time, opening logo, AMD FreeSync Premium, MBR), display information, recall
Speakers	2 x 2W
Convenience	Kensington-lock™ prepared, DDC2B, Mac OSX

## 04 MECHANICAL

Display position adjustments	tilt
Tilt angle	22° up; 5° down
VESA mounting	100 x 100mm
Cable management system	yes

## 05 ACCESSORIES INCLUDED

Cables	power, USB, DP
Other	quick start guide, safety guide

## 06 POWER MANAGEMENT


Power supply unit	internal
Power supply	AC 100 - 240V, 50/60Hz
Power usage	65W typical, 0.5W stand by, 0.3W off mode

## 07 SUSTAINABILITY

Regulations	CE, TÜV-Bauart, EAC, RoHS support, WEEE
Other	REACH SVHC above 0.1%: Lead

## 08 DIMENSIONS / WEIGHT

Product dimensions W x H x D	535.5 x 394.5 x 202mm
Box dimensions W x H x D	612 x 408 x 190mm
Weight (without box)	3.7kg
EAN code	4948570117703



## 09 EU ENERGY EFFICIENCY LABEL

Manufacturer	iiyama
Model	G-Master G2466HSU-B1

Energy efficiency class	A
Visible screen diagonal	60cm; "; (24" segment)
ON mode power consumption	22W
Annual energy consumption	31kWh/annum*
Power in Standby	0.5W stand by
Power in OFF Mode	0.3W off mode
Resolution	1920 x 1080

*This is information under Regulation (EU) No 1062/2010.\*Based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.*

*All trademarks and registered trademarks acknowledged. E & O E. Specification subject to change without notice. All LCD's comply with ISO-9241-307:2008 in connection with pixel defects.*

© IIYAMA CORPORATION. ALL RIGHTS RESERVED