

OS	Windows 10 Pro
Color	Ink Black
Screen Size / Type	15.6" FHD, IPS-Level 60Hz 72%NTSC Thin Bezel, close to 100% sRGB
Resolution/ Ratio	1920x1080 16:9
CPU/Processor	Core i7-1185G7
CPU Frequency	1.2 - 4.8GHz
Graphics	NVIDIA GeForce® GTX1650 Ti Max-Q
Video Memory	4G GDDR6
System Memory	DDR IV 8GB*2 3200MHz
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	1TB NVMe PCIe SSD
HDD Interface	NVMe
SSD	1x M.2 SSD Combo (NVMe PCIe Gen3x4 / SATA), 1x M.2 SSD PCIe Gen4x4
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
BT	BT 5.1
Card Reader	Micro SD (UHS-III)
HDMI-out	4K @ 60Hz
USB Type C	Thunderbolt 4*2 [Support Power delivery, DP 1.4a, USB 4.0]
USB	USB 3.2 Gen2 *2
Keyboard	White backlight keyboard (84 Key)
Touch Pad	Silky Glass Multi Touch with Finger print reader [Support FIDO 2]
Mic-in/ Headphone-out	Mic-in/Headphone-out Combo
Speaker	Speakers 2W * 2
Webcam	IR HD Type [30fps/720p]
Battery Pack	4 cell (82Whr) Li-Polymer
AC Adapter	90W Compact
Unit weight	3.64 lbs
Unit Dimension	14.06" x 9.21" x 0.67"
UPC	824142232811
UCC-14	10824142232818
Warranty	1 year Limited warranty (Include 1 Year Global)