



Key Features

Works with myViewBoard Software | Ultra-Portable Design | Advanced Touch Capabilities and Screen Performance | 2-Way Power with USB Type-C | Full-HD 1080p resolution




Product Description

The ViewSonic® ID1655 ViewBoard Touch Display is part of ViewSonic's full line of interactive devices designed for a variety of education scenarios including h... The ID1655 ViewBoard Touch Display is a portable 15.6" touch display that can serve as a complementary touchscreen to a laptop or tablet for more effective HD 1080p resolution, this touch display delivers a crystal-clear viewing experience so users can see more and do more for a more efficient workflow. In addition to the touchscreen and included stylus pen, the ID1655 ViewBoard Touch Display delivers a smooth and natural writing experience and streamlined navigation with... ports enable quick and easy transmission of video, audio, and data. The USB-C ports also deliver up to 60W of two-way power: a connected laptop can power the ID1655 can power a connected laptop via a USB-C power bank or AC adapter and outlet. Measuring less than an inch thick and weighing only two pound any bag, briefcase, or backpack so you can teach from wherever you are.



1. Internal Speakers
2. Power Button/Toggle Switch
3. Built-In Stand
4. Audio Out
5. Mini HDMI


6. USB Type C (x2)



15.6"
DISPLAY






TN
PANEL



1920 x 1080
RESOLUTION

Contact Sales

-  call: 888.
-  email: sa
-  visit: view

Display:

Display Size (in.):	15.6
Viewable Area (in.):	15.6
Panel Type:	TN
Resolution:	1920 x 1080
Resolution Type:	Full HD (1920x1080)
Static Contrast Ratio:	800:1
Dynamic Contrast Ratio:	50,000,000:1
Light Source:	LED
Brightness:	250 cd/m2
Colors:	262K
Color Space Support:	6 bit
Aspect Ratio:	16:9
Response Time (Typical GTG):	14ms
Response Time (GTG w/OD):	6.5ms
Viewing Angles:	170° horizontal, 170° vertical
Backlight Life (Hours):	15,000
Panel Surface:	Glossy, Hardness (6H)

Compatibility:

PC Resolution (max):	1920x1080
Mac® Resolution (max):	1920x1080

Connector:

USB 3.2 Gen 1 Type C(2), Mini HDMI 1.4(1)

Touch:

Touch Technology:	Projective Capacitive
Touch Points:	10-Point Touch

Audio:

Internal Speakers:	0.8W (x2)
--------------------	-----------

Power:

Eco Mode (Conserve):	6.0W
Eco Mode (optimized):	6.9W
Consumption (typical):	8.6W
Consumption (max):	10.5W
Voltage:	AC 100-240V (universal), 50-60Hz
Stand-by:	0.3W
Power Supply:	Wall type (detachable type-C)

Controls:

Physical Controls:	1, 2, 3, 4, 5 (Power)
On Screen Display:	Image Adjust, Contrast, Brightness, Input Select, Audio Adjust, Color Adjust, Information, Manual Image Adjust, Setup Menu, Memory Recall

Operating Conditions:

Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	20-90%

Video Signal:

Frequency Horizontal:	15 ~ 82KHz
Frequency Vertical:	50 ~ 75Hz

Video Input:

Digital Sync:	TMD5 for miniHDMI (v
---------------	----------------------

Ergonomics:

Tilt (Forward/Back):	0° / 60°
----------------------	----------

Weight (imperial):

Net (lbs):	2.1
Net Without Stand (lbs):	2.1
Gross (lbs):	5.1

Weight (metric):

Net (kg):	1.0
Net Without Stand (kg):	1.0
Gross (kg):	2.3

Dimensions (imperial) (WxHxD):

Packaging (in.):	17.3 x 11.3 x 3.5
Physical (in.):	14.0 x 8.8 x 0.6
Physical Without Stand (in.):	14.0 x 8.8 x 0.6

Dimensions (metric) (WxHxD):

Packaging (mm):	440.0 x 288.0 x 89.0
Physical (mm):	355.0 x 223.0 x 16.0
Physical Without Stand (mm):	355.0 x 223.0 x 16.0

General:

Regulations: cTUVus, FCC-B, ICES003, Energy Star 8.0, EPEAT

PACKAGE CONTENTS: 1 x LCD Display, 1 x USB type-C to type-A cable, 1 x mini HDMI cable, 1 x Power Adapter, 1 x Passive Touch F

Recycle/Disposal: Please dispose of in accordance with local regulations.

UPC: 766907010633

Accessories:

VB-PEN-005