

ThinkBook 13s G2 ITL 20V9001RUS

Product

ThinkBook 13s G2 ITL

Region

NA

Country/Region

USA

Machine Type

20V9

TopSeller

TopSeller

Processor

Intel Core i5-1135G7 (4C / 8T, 2.4 / 4.2GHz, 8MB)

Graphics

Integrated Intel Iris Xe Graphics

Chipset

Intel SoC Platform

Memory

8GB Soldered LPDDR4x-4266

Storage

256GB SSD M.2 2242 PCIe 3.0x4 NVMe

Display

13.3" WQXGA (2560x1600) Low power IPS 300nits Anti-glare, 100% sRGB, Dolby Vision

Touchscreen

None

Optical

None

Card Reader

None

Ethernet

None

WLAN + Bluetooth

Intel AX201 11ax, 2x2 + BT5.1

Camera

720p with ThinkShutter

Microphone

2x, Array

Case Color

Mineral Grey

Surface Treatment

Anodizing sandblasting

Case Material

Aluminium (Top), Aluminium (Bottom)

Keyboard

Backlit, English (US)

Fingerprint Reader

Touch Style

Security Chip

Discrete TPM 2.0

Battery

Integrated 56Wh

Power Adapter

65W USB-C

Operating System

Windows 10 Pro 64, English

Bundled Software

Office Trial

Base Warranty

1-year, Depot

Additional Certificates

None

Bundled Service

None

EAN / UPC / JAN

195348151306

End of Support

2027-04-30

Announce Date

2020-09-30

Recommended Services**Good**

3Y Premier Support Upgrade from 1Y Depot/CCI (5WSOT36151)

Notes:**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

ThinkBook 13s G2 ITL Platform Specifications

Product Specifications Reference (PSREF)

Processor	11th Generation Intel® Core™ i5 / i7 Processor										Media reader Ports	None One Thunderbolt 4 / USB4 40Gbps (with the function of PD 3.0 and DP 1.4), two USB 3.2 Gen 1 (one Always On), HDMI 2.0b, headphone / microphone combo jack, security keyhole <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>	
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics					
	i5-1135G7	4	8	2.4 GHz	4.2 GHz	8MB	LPDDR4X -4266	Intel Iris® Xe Graphics					
i7-1165G7	2.8 GHz			4.7 GHz	12MB								
Graphics	Intel Iris Xe Graphics in processor; supports up to 3 independent displays via native display and two external monitors; supports external monitors via HDMI (up to 3840x2160@60Hz) or Thunderbolt™ (up to 7680x4320@30Hz)												
Chipset	Intel SoC (System on Chip) platform											Security	Power-on password, hard disk password, supervisor password, Kensington Nano security slot
Memory	8GB or 16GB / 4266MHz LPDDR4X, dual-channel capable, soldered to systemboard, no slots											Security chip	• Discrete TPM 2.0, TCG Certified • Firmware TPM 2.0, integrated in chipset
Display	Size	Resolution	Surface	Touch	Type	Brightness	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Fingerprint reader	Touch style fingerprint reader on smart power button	
	13.3"	WUXGA (1920x1200) Dolby Vision™	Anti-glare	-	IPS	300 nits	16:10	1000:1	100% sRGB	170°	Battery	Integrated Li-Polymer 56Wh battery, supports rapid charge (charge up to 80% in 1hr)	
	13.3"	WQXGA (2560x1600) Dolby Vision	Anti-glare	-	IPS	300 nits	16:10	1000:1	100% sRGB	170°	Max battery life	<i>MobileMark® 2014:</i> 16 hr <i>MobileMark 2018:</i> 12.1 hr <i>* Battery life varies significantly with hardware configurations, settings, usage, & other factors</i>	
	13.3"	WQXGA (2560x1600) Dolby Vision	Anti-glare	-	IPS	300 nits Low power	16:10	1500:1	100% sRGB	170°	AC adapter	65W USB-C AC adapter or 65W USB-C slim wall-mount AC adapter <i>(65W USB-C slim wall-mount AC adapter is only available in selected countries)</i>	
	13.3"	WQXGA (2560x1600) Dolby Vision	Glossy	Multi-touch	IPS	300 nits Low power	16:10	1500:1	100% sRGB	170°	Preload (opt)	<i>Preloaded operating system</i> • Windows® 10 Home 64 • Windows 10 Pro 64 <i>Preloaded applications (only some listed)</i> • Microsoft® 365 Personal • Microsoft 365 Family • Microsoft Office Home and Business 2019 • Microsoft Office Home and Student 2019 • Microsoft Office Professional 2019 • Microsoft Office Personal 2019 • Microsoft Office Trial (with 30-day license)	
Multi-touch(opt)	Capacitive-type multi-touch, supports 10-finger gesture											Limited warranty	<i>One of the following, configurable by model:</i> • 1-year depot repair service • 1-year with 2-year system board repair service • 2-year/1-yr battery depot repair service
Storage	<i>One of the following, configurable by model:</i> • M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 4 • M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4 or PCIe 4.0 x 4											Mil-Spec test	Work in progress
Optical	None											Other certifications	Intel Evo™ Platform <i>depends on models ordered</i>
Ethernet	None											Environment	EPEAT™ Silver; ENERGY STAR® 8.0; ErP lot3; TUV Low Blue Light certified; RoHS-compliant
WLAN + Bluetooth™	Intel Wi-Fi 6 AX201, Wi-Fi 2x2 802.11ax + Bluetooth 5.1, M.2 card <i>* Intel WiFi 6 full features might be limited by country level restrictions</i> <i>* BT5.1 is supported on Windows 10 version 2004 or above (limited to BT5.0 on earlier version)</i>												
Dimensions	WxDxH: 11.77" x 8.27" x 0.59"; 299mm x 210mm x 14.9mm												
Weight	Starting at 2.78 lbs / 1.26 kg												
Case color	Mineral grey, dual tone design												
Case material	<i>Top cover:</i> Aluminum <i>Bottom:</i> Aluminum												

The specifications above may not be available in all regions and might change by regions

Lenovo
December 2020

Lenovo™

ThinkBook 13s G2 ITL

