




# Planar HRO Complete Fine Pitch Outdoor LED Video Walls



Planar® HRO Complete outdoor LED video walls are high resolution, high brightness displays designed for close up viewing even in direct sunlight. These pre-packaged displays include everything needed for a beautiful outdoor video viewing experience.



## JUST THE RIGHT SIZE


Planar HRO Complete comes in four appealing diagonal sizes: 130\", 174\", 217\" or 260\". Each model features a 16:9 aspect ratio making it ideal for outdoor viewing of movies, live sports or presentations. Planar HRO Complete resolutions start at Full HD (1920 x 1080) on the 130\" model, increasing to 4K (3840 x 2160) on the 260\" model. These high resolutions ensure crisp visuals and comfortable viewing as close as 10' (3m).

Of course, if none of the pre-packaged video wall sizes is quite right, custom sizes of Planar® HRO Series are also available.

Model	Resolution	Size	Dimensions
HRO130	Full HD (1920 x 1080)	130"	9.45' x 5.31' 2419 x 1618mm
HRO174	2048 x 1152	174"	12.6' x 7.09' 3840 x 2161mm
HRO217	Quad HD (2560 x 1440)	217"	15.75' x 8.86' 4800 x 2700mm
HRO260	4K (3840 x 2160)	260"	18.9' x 10.63' 5760 x 3240mm
Custom sizes and resolution also available			

## WITHSTAND THE WEATHER

Planar HRO Complete is built to endure the weather with LED treatments that protect from ultraviolet rays, dust and water, without negatively impacting the viewing experience. Protective plates on the backside cover cables and mechanics, ensuring long life no matter the environmental factors. With Planar HRO Complete's 3,500-nit brightness, viewers can enjoy vibrant media even on the sunniest days.



## ONE POWERFUL PACKAGE

Planar HRO Complete comes with all elements ready to install, delivering faster deployment and time to use. Each package includes the display, controller, cables, trim and wall mount. Optional floor stands and hanging mounts are also available. Planar HRO Complete models start at \$127,995 (MSRP US).

PLANAR HRO COMPLETE SPECIFICATIONS				
Part Number	HRO130	HRO174	HRO217	HRO260
Display Technology	Direct View LED			
Display Resolution	1920 x 1080	2048 x 1152	2560 x 1440	3840 x 2160
Display Diagonal Size	130"	174"	217"	260"
Display Dimensions	9.45' x 5.31' 2880 x 1620mm	12.6' x 7.09' 3840 x 2161mm	15.75' x 8.86' 4800 x 2700mm	18.9' x 10.63' 5760 x 3240mm
Pixel Pitch	1.5mm	1.875mm	1.875mm	1.5mm
Brightness	> 3500 cd/m <sup>2</sup>			
Contrast Ratio	7,000:1			
LED Refresh Rate	3,840Hz			
Color Temperature, Adjustable (k)	6,500 - 10,000			
Video Inputs	1x HDMI 2.0 (HDCP 2.2), 4x DVI, 2x SDI-3G			
Control	USB, Serial, Network			
Frame Rate	50, 60Hz			
Viewing Angle	160° (H) / 160° (V)			
Service Access	Front, Rear			
Environment	Outdoor, IP65 (front) / IP54 (rear)			
Operating Temperature/ Humidity (degrees F/C, relative humidity)	-4° to 113° F, -20 to 45° C 10-80%			
Storage Temperature/ Humidity (degrees F/C, relative humidity)	-4° to 140° F, -20° to 60° C 10-85%			
Line Voltage	100-240V AC, 50/60Hz			
Power Consumption (max. watts)	3,173	5,640	8,813	12,690
Display Weight (approx)	483 kg 1064.8 lbs	858 kg 1,891.5 lbs	1,341 kg 2,956.4 lbs	1,931 kg 4,257.1 lbs
Solution Includes	Video Wall display, Video controller, signal cables, power cables, wall mount, trim and spare modules			

*Solution may change or not be offered in all regions*