



8MP H.265 IP Dome Camera with Analytics

O8VD1

2.8mm fixed lens, white housing



Features

- Captures up to 8MP @ 20fps
- Built-in standard PoE (IEEE 802.3af)
- H.265/H.264 compression supported
- True Day/Night operation (IR cut filter)
- IR range: Up to 100' (depending on scene reflection)
- Micro SD slot up to 128GB (card not included)
- Digital WDR
- Line crossing, region intrusion and video blurring detection
- Built-in microphone
- IP67 compliant, weather resistant
- IK10 compliant, vandal resistant
- Junction box included
- Conformance with ONVIF Profile T
- 5 year warranty



Included Junction Box



Camera Specifications

Image Sensor	Progressive scan 1/2.7" CMOS, 8MP
Maximum Resolution	3840 x 2160 (8MP)
Field of View (H)	112°
Minimum Illumination	0.09 lux @ F2.0, AGC ON, 0 lux with IR
Day/Night	Smart IR
White Balance	Auto, Indoor, Outdoor, Manual
Compensation	Digital WDR, BLC, HLC
Electronic Shutter Speed	1/25 - 1/100000 sec.
DNR	3D DNR
Angle Adjustments	Pan (0° - 355°), Tilt (0° - 67°), Rotation (0° - 355°)

Video Specifications

Main Resolution	8MP/6MP/5MP (1 ~ 20fps)
Sub Stream	720p/D1/CIF (1 ~ 20fps)
Third Stream	D1/CIF/480 x 240 (1 ~ 20fps)
Compression	H.265, H.264
Image Settings	Region of Interest, Saturation, Brightness, Chroma, Contrast, Wide Dynamic, Defog, Sharpen, Noise Reduction
Bitrate Control	VBR, CBR (64Kbps ~ 8Mbps)
Multiple Streaming	3 streams

Network Specifications

Protocols	UDP, DHCP, NTP, RTSP, PPPoE, DDNS, SMTP, FTP, 802.1x, UPnP, HTTP, HTTPS, QoS
DDNS support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP/Mac address filtering, digest authentication
User Access	Max. 3 simultaneous users (Actual number of users may vary depending on bandwidth)

Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up)
PC Application	SecureGuard® VMS, SecureGuard® CMS
Mobile	SecureGuard® Client, Speco Blue (iPhone® and Android™)
Other Platforms	Apple TV, Amazon Fire TV

Audio Specifications

Audio Codec	G.711A / G.711U
-------------	-----------------

Interfaces

Network	RJ45 jack
Power	DC jack
Microphone Input	3.5mm
Card Slot	MicroSD, up to 128GB (not included)
Alarm	No
Reset	Yes


System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Line crossing, object detection, region intrusion, and video blurring detection
Alarm Triggers	Motion, Analytics, SD card error
Image Settings	Watermark, IP address filtering, video mask, password protection, Corridor mode

Operating & Unit Specifications


Power	PoE, 12VDC (power supply not included)
Power Consumption	< 7.0W
Operating Temperature	-40°F ~ 140°F (40°C ~ 60°C)
Operating Humidity	Less than 95 % (non-condensing)
Unit Dimensions	4.68" (φ) x 3.45" (H); 119mm (φ) x 87.8mm (H)
Unit Weight	1.03 lb. (0.47kg)
Certifications	FCC, RoHS

Optional Accessories



NDA COMPLIANT

Camera Interfaces



ONVIF is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Amazon's trademark is used under license from Amazon.com, Inc. or its affiliates. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 2/3/21

Apps available from the following:

Download on the App Store | GET IT ON Google Play | amazon appstore | ONVIF® 800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com

