

ThinkCentre M75s Gen 2 11JB000HUS

Product

ThinkCentre M75s Gen 2

Region

NA

Country/Region

USA

Machine Type

11JB

TopSeller

TopSeller

Processor

AMD Ryzen 3 PRO 4350G (4C / 8T, 3.8 / 4.0GHz, 2MB L2 / 4MB L3)

Chipset

AMD PRO565 Chipset

Graphics

Integrated AMD Radeon Graphics

Memory

1x 8GB UDIMM DDR4-3200

Storage

256GB SSD M.2 2280 PCIe 3.0x4 NVMe Opal

Optical

DVD±RW

Card Reader

None

Speakers

1Wx1

Ethernet

Integrated 100/1000M

WLAN + Bluetooth

None

Optional Rear Ports

None

Chassis Intrusion Switch

Chassis Intrusion Switch

Chassis E-Lock

None

Smart Cable Clip

None

Case Color

Black

Stand

Stand

Keyboard

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Power Supply

260W 85%

Additional Certificates

ENERGY STAR 8.0, EPEAT Silver

System Management

DASH 1.1

Monitor Cable

None

Operating System

Windows 10 Pro 64, English

Bundled Software

None

Base Warranty

3-year, Onsite

Bundled Service

None

EAN / UPC / JAN

195348297677

End of Support

2027-05-20

Announce Date

2020-09-29

Recommended Services**Good**

3Y Premier Support Upgrade from 3Y Onsite (5WS0U26647)

Notes:**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

AMD

ThinkCentre M75s Gen 2 Platform Specifications

Product Specifications Reference (PSREF)

Processor	AMD Athlon, Ryzen 3 / 5 / 7 / 9 series processor						WLAN	Some: 11ac wireless, M.2 Card, Realtek RTL8822CE (dual band), Wi-Fi + Bluetooth 5.0 combo adapter, 2x2 Some: 11ac wireless, M.2 Card, Intel Wireless-AC 9560 (dual band), Wi-Fi + Bluetooth 5.0 combo adapter, 2x2
	Processor	Cores / Threads	Frequency (Base/Max)	L2 / L3 Cache	Memory Support (Up to)	Integrated Graphics	Bluetooth Ethernet (Opt.)	Some: Bluetooth 5.0 wireless, integrated in Wi-Fi + BT combo adapter Gigabit ethernet, Realtek RTL8111EPV, Wake on LAN® Some: Bitland BN8E88, gigabit ethernet, 1x RJ-45, PCIe x1 Some: Bitland RTL8111FP, gigabit ethernet, 1x RJ-45, PCIe x1
	Athlon Silver 3050GE	2 / 4	3.4 GHz	1 MB / 4MB	DDR4-2666	Radeon		
	Athlon Gold PRO 3150G	4 / 4	3.5 / 3.9 GHz	2MB / 4MB	DDR4-2933	Radeon		
	Ryzen 3 4300G	4 / 8	3.8 / 4.0 GHz	2MB / 4MB	DDR4-3200	Radeon		
	Ryzen 3 PRO 4350G	4 / 8	3.8 / 4.0 GHz	2MB / 4MB	DDR4-3200	Radeon		
	Ryzen 5 4600G	6 / 12	3.7 / 4.2 GHz	3 MB / 8MB	DDR4-3200	Radeon		
	Ryzen 5 PRO 3350G	4 / 8	3.6 / 4.0 GHz	2MB / 4MB	DDR4-2933	Radeon Vega 11		
	Ryzen 5 PRO 3400G	4 / 8	3.7 / 4.2 GHz	2MB / 4MB	DDR4-2933	Radeon Vega 11		
	Ryzen 5 PRO 3600	6 / 12	3.6 / 4.2 GHz	3MB / 32MB	DDR4-3200	None		
	Ryzen 5 PRO 4650G	6 / 12	3.7 / 4.2 GHz	3MB / 8MB	DDR4-3200	Radeon		
	Ryzen 7 4700G	8 / 16	3.6 / 4.4 GHz	4MB / 8MB	DDR4-3200	Radeon		
	Ryzen 7 PRO 3700	8 / 16	3.6 / 4.4 GHz	4MB / 32MB	DDR4-3200	None		
	Ryzen 7 PRO 4750G	8 / 16	3.6 / 4.4 GHz	4MB / 8MB	DDR4-3200	Radeon		
	Ryzen 9 PRO 3900	12 / 24	3.1 / 4.3 GHz	6MB / 64MB	DDR4-3200	None		
Memory	128GB max, DDR4-2666 / DDR4-2933 / DDR4-3200*, four 288-pin DIMM sockets, dual-channel capable * Installed memory is actually 3200MHz, but may run at 2666MHz, 2933MHz, or 3200MHz depending on the memory support capability of processor						Manageability Security chip	DASH 1.1 Discrete TPM 2.0, TCG Certified
Storage	Support up to 2x HDD ([2.5" + 3.5"] or [dual 2.5"]) and up to 1x M.2.SSD Some: Hard Drive / SATA 6.0Gb/s, 2.5" or 3.5", 7200 rpm Some: M.2 SSD (2242 / 2280) / PCIe NVMe, PCIe 3.0 x2 or PCIe 3.0 x4						Security features	- Security slot (for Kensington® lock) - Padlock loop - Optional Smart Cable Clip to physically lock keyboard and mouse - Optional chassis intrusion switch - Optional chassis E-Lock - Power-on password - Administrator password - Hard disk password - Boot sequence control - Boot without keyboard and mouse - Individual USB port disablement - Smart USB protection, allows keyboard/mouse only, blocks all storage devices
Optical	Some: DVD-ROM, SATA 1.5Gb/s Drive, slim (9.0mm) Some: DVD Burner (DVD±RW), SATA 1.5Gb/s Drive, slim (9.0mm)						Keyboard	Some: Lenovo Calliope Keyboard (USB connector), black Some: Lenovo Traditional Keyboard (USB connector), black Some: Lenovo Calliope Wireless Keyboard (2.4GHz via USB receiver), black
Onboard SATA Media reader	Three onboard SATA 6.0Gb/s connectors Optional 3-in-1 media reader (support SD, SDHC, and SDXC)						Mouse	Some: Lenovo Calliope Mouse (USB connector), black Some: Lenovo Fingerprint Mouse (USB connector), Windows Hello support, black Some: Lenovo Calliope Wireless Mouse (2.4GHz via USB receiver), black
Graphics	AMD Radeon™ Graphics in processor (only for some processors), uses main memory, DirectX® 12, two DisplayPort 1.4, one HDMI 1.4, supports up to 3 independent displays, more displays support via discrete graphics Max resolution: 4096x2160 (DP)@60Hz; 4096x2160 (HDMI)@24Hz Some: AMD Radeon™ 520 , DirectX 12, 2GB GDDR5, PCIe 3.0 x8, 30 watts, two DisplayPort 1.2 (up to 4096x2160@60Hz) Some: AMD Radeon RX 550X , DirectX 12, 4GB GDDR5, PCIe 3.0 x8, 50 watts, one DisplayPort 1.4 (up to 3840x2160@60Hz), one HDMI 2.0 (up to 4096x2160@60Hz), one VGA (up to 2048*1536@85Hz), occupies two slots						Mechanical	- SFF (8.2L), black color, metal case - Dimensions with bezel & PCI holder & rubber foot: (WxDxH) 3.6" X 11.7" X 13.4"; 93mm X 298mm X 340mm - Weight (approx.): 11.7 lb (5.3 kg), weight may vary by configuration
Monitor cable	Optional DP to VGA dongle, DP to DVI-D dongle, DP to dual DP dongle, DP to HDMI dongle, HDMI to VGA dongle, DP to VGA cable, or HDMI to HDMI cable						Bays	Bay 1: Slim ODD bay Bay 2: 3.5" HDD bay Bay 3: 2.5" HDD bay (bay comes with disk)
Chipset	AMD PRO 565						Slots	Slot 1: low-profile (length < 155mm, height < 68mm), PCIe 3.0 x16 Slot 2: low-profile (length < 155mm, height < 68mm), PCIe 3.0 x1 Slot 3: no slot, only bracket for optional port extension Slot 4: no slot, only bracket for optional port extension M.2 card slots: two (one for WLAN, one for SSD) Optional system floor stand for vertical orientation
Front ports* (Std.)	2x USB 3.2 Gen 2, 2x USB 3.2 Gen 1, 1x USB 3.2 Type-C Gen 1, 1x microphone (3.5mm), 1x headphone / microphone combo jack (3.5mm)						Floor Stand EOU design	None
Front ports* (Opt.)	Optional: 3-in-1 media reader						Power supply	Some: 180 watts, autosensing, 85% PSU Some: 260 watts, autosensing, 85% PSU Some: 310 watts, autosensing, 92% PSU
Rear ports* (Std.)	4x USB 2.0, 1x serial (9-pin), 1x ethernet (RJ-45), 2x DisplayPort**, 1x HDMI**, 1x line-out (3.5mm)						Limited warranty	Some: 1-year, depot service / service upgrades available Some: 1-year or 3-year, limited onsite service / service upgrades available
Rear ports* (Opt.)	Optional: 2x USB 3.2 Gen 1 via PCIe x1, 2x USB 3.2 Type-C Gen 2 via PCIe x4, 1x 2nd serial (9-pin), 1x parallel (25-pin), additional RJ-45 and video ports available on optional graphics or ethernet card * Depending on many factors, actual data transfer speed may be lower than theoretical speed ** Only available for the models with integrated graphics						Preload	Some: Windows® 10 Pro 64-bit Some: Windows 10 Home 64-bit Some: Windows 10 IoT Enterprise (only available via special bid model)
Audio support	High Definition (HD) Audio, Realtek ALC623-CG / internal speaker (1 watt)						Environment	ENERGY STAR® 8.0*, EPEAT™ Gold / Silver rating (on some models), ErP Lot 3, TCO 8.0, TUV low noise / ultra low noise verified (on some models), RoHS * Only available for MT 11JA/11JB
							Accessories	For compatible accessories, please go to http://smartfind.lenovo.com

Note: The specifications above may not be available in all regions.

Lenovo, November 2020

Lenovo

ThinkCentre M75s Gen 2



AMD



AMD



AMD



AMD



AMD



AMD