

|                            |   |
|----------------------------|---|
| Country                    | ca  |
| EAN                        | 0824142227749   |
| Operating System           | Windows 10 Home   |
| Chassis/ Color             | Black   |
| Chipset                    | Intel® B460   |
| Processor                  | Core i7-10700   |
| CPU Speed                  | 2.9GHz up to 4.8GHz   |
| CPU Cooler                 | Fan Cooler  |
| Graphic                    | RTX 3070 8GB GDDR6  |
| Graphic Memory             | 8GB GDDR6   |
| System Memory              | 16GB (16GB*1) DDR4 2666MHz  |
| Memory Total Slots         | 2x DDR4 2666MHz U-DIMMs, up to 64GB   |
| SSD / Hard Drive           | 1TB PCIE M.2 SSD  |
| Storage Slots (Total/Free) | 2x M.2 2280 SSD (1xSATA/PCIe Combo, 1x PCIe) 2x 2.5" Drive bays   |
| LAN                        | Realtek RTL8125B ethernet (10/100/1000M)  |
| Wireless LAN               | Intel® Wi-Fi 6 AX200  |
| Bluetooth                  | BT 5.1  |
| Audio                      | 7.1 Channel HD Audio with Nahimic audio enhancer  |
| Mic-in/Headphone-out       | Front: 1 x Mic-in, 1 x Headphone-out / Rear: 5x Audio jacks, 1x Optical S/PDIF out, 1x RJ45 (2.5 LAN)   |
| USB                        | Front: 1x USB 3.2 Gen 1 Type C, 1x USB 3.2 Gen 1 Type A, 1x USB 2.0 Type A Rear: 3x USB 3.2 Gen 1 Type A, 1x USB 3.2 Gen 1 Type C, 2x USB 2.0 |
| Video Port                 | 1x Display Port / 1x HDMI   |
| Video Port (Graphics Card) | 3 x Display port, 1 x HDMI out  |
| Other port                 | N/A   |
| Card Reader                | N/A   |
| KB/Mouse                   | GK 30 + GM11  |
| Vesa Mountable             | N/A   |
| Power Supply               | 650W 80 Plus Gold certified (SFX)   |
| Dimension                  | 129.74 x 382.73 x 396.39 mm / 5.1 x 15.06 x 15.6 inches   |
| Chassis (liters)           | 10.36L /21.89pt   |
| Weight (LB)                | 6.55 Kg / 14.44 lbs   |
| UPC                        | 824142227749  |
| UCC-14                     | 10824142227746  |
| Warranty                   | 1 Year Warranty   |