

Lenovo G24-10 65FDGCC2US

Product

Lenovo G24-10

Machine Type

65FD

Region

NA

Display Size

23.6"

View Area

521.28x293.22 mm

Panel

Twisted Nematic

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.2715x0.2715 mm

Dot / Pixel Per Inch

93 dpi

View Angle (H / V)

170 / 160

Pixel Response Time

1 ms (Extreme mode) / 3 ms (Typical mode) / 5 ms (off mode)

Refresh Rate

144 Hz

Brightness

300 nits

Contrast Ratio

1000:1

Color Gamut

72% NTSC

Multiple Input

HDMI, DP

USB Port

None

Camera

None

Speaker

None

Power Consumption (Typical / Maximum)

21W / 34W

Power Adapter

Integrated

Stand

Tilt Stand

Color

Raven Black

Side Bezel Width

17.58 mm

Dimensions with Stand (HxWxD)

419.34x557.2x190.49 mm

Weight (Including Stand)

8.22 lb / 3.73 kg

Monitor Cable

HDMI

ENERGY STAR

None

TCO

None

EPEAT

None

Low Blue Light / Eye Comfort / Eyesafe Display

Eye Comfort

Base Warranty

1-year

Operating System Support

Support Windows 7, Windows 10

Sync Technology

AMD FreeSync Premium / G-SYNC Compatible

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

EAN / UPC / JAN

0193638811275

Announce Date

2019-10-31

Notes:**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2021. All rights reserved.



Lenovo™

Lenovo G24-10 Monitor

DISPLAY

Panel Size

23.6-inch

Screen Dimensions

521.28 mm x 293.22 mm

Panel Type

TN

Backlight

WLED

Aspect Ratio

16:9

Resolution

1920 x 1080

Pixel Pitch

0.2715 x 0.2715 mm

Dot/Pixel Per Inch (DPI/PPI)

93

Viewing angle (H x V @ CR 10:1)

170° / 160°

Response Time

1ms (extreme mode)

Refresh Rate

144 Hz

Brightness (typical)

240 cd/m²

Brightness (peak)

300 cd/m²

Contrast Ratio (typical)

1000:1

Dynamic Contrast Ratio (typical)

3M:1

Color Gamut

72%

Color Support (typical)

16.7 Million

Anti-glare

Yes

CONNECTIVITY

Video Signal

1 x HDMI 1.4

1 x DP 1.2

Audio Signal

1 x Audio Out (3.5 mm)

SPECIAL FEATURES

Sync Technology

NVIDIA® G-SYNC® Compatible*

POWER

Power Consumption (typical/max)

21W / 34W

Power Consumption Sleep/Off Mode

< 0.5W

Power Consumption Switch-off Mode

< 0.3W

Voltage Required

AC 90 to 264 V (47/63 Hz)

MECHANICAL

Tilt Angle (front/back)

-5° / 22°

VESA Mount Capability

Yes (100 x 100 mm)

Kensington™ Lock Slot

Yes

Cable Management

Yes

Bezel color

Raven Black

Bezel Width (side)

17.58 mm

Bezel Width (top/bottom)

19.13 / 24.23 mm

DIMENSION

Size Packed (D x H x W, mm/inch)

620 x 410 x 130 mm /

24.41 x 16.14 x 5.12 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest point)

190.49 x 419.34 x 557.2 mm /

7.5 x 16.51 x 21.94 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest point)

190.49 x 419.34 x 557.2 mm /

7.5 x 16.51 x 21.94 inches

Weight Packed (kg/lb)

4.95 kg / 10.91 lbs.

Weight Unpacked (kg/lb)

3.73 kg / 8.22 lbs.

WHAT'S IN THE BOX

Monitor with stand

1 x Power cable (1.8 m)

1 x HDMI cable (1.8 m)

Quick setup guide

CERTIFICATION

CCC

Yes

RoHS (EU 2002/95/EC)

Yes

Windows Certification

Window 7, Windows 10

China Energy Efficiency Standard

Tier 2

TÜV Rheinland Eye Comfort

Yes



*NVIDIA® G-SYNC® works through NVIDIA® GeForce® graphics cards

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Lenovo G24-10

