

# SLA-C-I3910

4K Varifocal Lens



## SLA-C-I3910

IMAGING	
Focal Length	3.9-10mm, 108.1°-41.1° Angle of View, 1/1.8" format
Resolution	Up to 4K, / 8MP
F-Stop	F/1.5 to close
IR Correction	IR Corrected for true Day/Night operation
Lens Type	Stepping Motor Iris, iCS control with compatible camera
Mount Type	CS Mount,
Operating Temperature / Humidity	-20°C ~ +60°C (-4°F ~ +140°F) <70% humidity, non-condensing
Storage Temperature / Humidity	-30°C ~ +60°C (-22°F ~ +158°F) <90% humidity, non-condensing

\* The latest product information / specification can be found at [hanwhasecurity.com](http://hanwhasecurity.com)

\* Design and specifications are subject to change without notice.

## Key Features

- High resolution optics
- Supports up to 4K resolution
- 3.9-10mm varifocal lens
- Stepping Motor Iris
- IR corrected for true Day/Night operation
- CS-mount with iCS control with compatible cameras