


HP Elite Slice G2 with Zoom Rooms (2U5A7AW)



How conferencing should be

Simplify meetings and seamlessly connect[2] with the HP Elite Slice G2 with Zoom Rooms.



Ready to go

Simplify your Zoom Room deployment with a compute device pre-imaged with Zoom Room software packaged with a moveable 12.3-inch diagonal Center of Room Control display, HDMI adapters, and a port cover.

One-touch collaboration

Enjoy on-demand calling and flexible accessibility. Easily add attendees and share content with one touch of the anti-glare screen on the Center of Room Control with dual viewing angles and the familiar Zoom Rooms interface.[2]

Crisp, clear audio

Isolate voices with advanced noise cancellation for clear communication.

Specifications

Form factor	Ultra-small form factor
Operating system	Windows 10 IoT Enterprise 64
Processor family	7th Generation Intel® Core™ i5 processor
Processor	Intel® Core™ i5-7500T (2.7 GHz base frequency, up to 3.3 GHz with Intel® Turbo Boost Technology, 6 MB L3 cache, 4 cores) ^[6,7]
Chipset	Intel® Q170 ^[28]
Memory	8 GB DDR4-2400 MHz RAM (2 x 4 GB)
Memory Slots	2 DIMM
Internal Storage	128 GB PCIe® NVMe™ M.2 SSD
Graphics	Integrated
Graphics (integrated)	Intel® HD Graphics 630
Audio	Conexant CX7501 codec, 4 x 2 W internal speakers, universal audio jack that is retaskable, HP Audio Module 2.0
Minimum dimensions (W x D x H)	16.5 x 16.5 x 11.2 cm
Minimum dimensions (W x D x H)	6.5 x 6.5 x 4.4 in
Weight	1.52 kg (Exact weight depends on configuration.)
Weight	3.36 lb (Exact weight depends on configuration.)
Pointing device	HP USB wired optical mouse
Ports	1 audio-in/out; 1 SuperSpeed USB Type-C® 5Gbps signaling rate
Expansion slots	1 M.2 2230; 1 M.2 2280 ^[8]
Ports	1 DisplayPort™; 1 HDMI; 1 power connector; 1 RJ-45; 1 SuperSpeed USB Type-C® 5Gbps signaling rate (alternate mode DisplayPort™); 2 SuperSpeed USB 5Gbps signaling rate
Package dimensions (W x D x H)	59.6 x 27.3 x 20.3 cm
Package weight	6.67 kg
Network interface	Intel® Dual Band Wireless-AC 8260 802.11ac (2x2) and Bluetooth® 4.2 Combo
Network interface type	WLAN
Wireless	Intel® Dual Band Wireless-AC 8260 802.11ac (2x2) Wi-Fi® and Bluetooth® 4.2 Combo
Power	90 W external power adapter ^[24]
Management features	HP Image Assistant
Sustainable impact specifications	Low halogen
Security management	HP Active Health; HP Dual Head Keyed Cable Lock Kit; Sure Start 3.0; Trusted Platform Module TPM 2.0 Embedded Security Chip shipped with Windows 10 (Common Criteria EAL4+ Certified)(FIPS 140-2 Level 2 Certified) ^[20]
UPC number	195161870293
Manufacturer Warranty	3 year (3/3/3) limited warranty includes 3 years of parts, labor and on-site repair. Terms and conditions vary by country. Certain restrictions and exclusions apply.
What's in the box	HP Cable and Port Cover; HP Center of Room Control; HP DisplayPort™ to HDMI True 4K Adapter; HP Elite Slice G2 with Zoom Rooms; HP VESA Plate; HP Video Ingest Module ^[27]

Top Recommended Displays, Accessories and Services

Keyboards

HP USB Premium Keyboard	Z9N40AA
HP USB Slim Business Keyboard	N3R87AA

Mice

HP USB Optical Scroll Mouse	QY777AA
-----------------------------	---------

PC Locks

HP Keyed Cable Lock 10 mm	T1A62AA
HP Master Keyed Cable Lock 10mm	T1A63AA

Personal Systems Hardware Support Onsite Service

HP 4 years Next Business Day Onsite Hardware Support for Desktops (unitonly)	U7897E
HP 5 years Next Business Day Onsite Hardware Support for Desktops (unitonly)	U7899E
HP 4 years Next Business Day Onsite Hardware Support with DefectiveMedia Retention Desktops only	UE333E

Messaging Footnotes

[2] Internet connection required and sold separately.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance. Intel, Pentium, Intel Core, Celeron, Intel logo and the Intel Inside logo are trademarks of Intel Corporation in the U.S. and other countries.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[8] (1) M.2 2230 PCIe for WLAN; (1) M.2 2280 PCIe for NVMe SSD.

[20] Firmware TPM is version 2.0. Hardware TPM is v1.2, which is a subset of the TPM 2.0 specification version v0.89 as implemented by Intel Platform Trust Technology (PTT). TPM is version 2.0. Hardware TPM is v1.2, which is a subset of the TPM 2.0 specification version v0.89 as implemented by Intel Platform Trust Technology (PTT).

[24] All power supplies are not available in every region.

[27] HP Video Ingest Module: Sold separately or as an optional feature.

[28] For full Intel® vPro™ functionality, Windows, a vPro supported processor, vPro enabled chipset, vPro enabled wired LAN card and discrete TPM 2.0 are required. See <http://intel.com/vpro>

Learn more at
hp.com

© Copyright 2021 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. Bluetooth is a trademark of its proprietor used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Intel, Core, vPro, and Intel Unite are trademarks of Intel Corporation in the U.S. and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. All other trademarks are the property of their respective owners.

