



## Help save time with Smart Tasks.[1] Get automatic two-sided printing and ink savings.[3]

The productive smart printer that gets work done. Help save time with Smart Tasks shortcuts,[1] and get automatic two-sided printing. Print and scan from your phone.[1] Save up to 50% on ink with HP Instant Ink.[3]



### Designed to save you time

Eliminate steps in repetitive tasks, using Smart Tasks.[1] Scan to the cloud, email, and more – in a tap.[1]

### Freedom to work anywhere

Connect to cloud-based printing with Wi-Fi™ or your cellular network to print from anywhere.[1]

### Never run out and save up to 50% with Instant Ink [3,5]

When ink levels are low, a new cartridge is automatically dispatched at no extra cost. Enjoy total flexibility, because you can change or cancel your plan anytime.[10]

### Featuring

Customizable shortcuts on your phone or printer [1]

Hands-free. Auto-fed

Ready when you are [1]

Printing just got more productive [1]

Amazing scanning, now on your smartphone [1]

Your reliable connection [2]



## Specifications

<b>Print Resolution Technologies</b>	HP Thermal Inkjet
<b>Print quality black (best)</b>	1200 x 1200 rendered dpi
<b>Print quality color (best)</b>	Up to 4800 x 1200 optimized dpi on HP Advance Photo Paper 1200 x 1200 dpi input
<b>Print speed black (ISO, A4)</b>	Up to 20 ppm
<b>Print speed black (ISO, letter)</b>	Up to 20 ppm
<b>Print Speed Color (ISO)</b>	Up to 10 ppm
<b>Print speed color (ISO)</b>	Up to 10 ppm
<b>Print speed</b>	Print speed up to 20 ppm (black) and 10 ppm (color)
<b>Functions</b>	Print, copy, scan, fax
<b>Duplex printing</b>	Automatic (standard)
<b>Duty cycle (monthly, A4)</b>	Up to 20,000 pages
<b>Duty cycle (monthly, letter)</b>	Up to 20,000 pages <sup>[7]</sup>
<b>Printer smart software features</b>	Orientation: Portrait/Landscape; Print on Both Sides: None/Flip on Long Edge/Flip on Short Edge; Page Order: Front to Back/Back to Front; Pages per Sheet: 1, 2, 4, 6, 9, 16; Quality Settings: Draft/Normal/Best; Printing Shortcuts; Print in Grayscale: Off/High Quality Grayscale/Black Ink Only; Pages per Sheet Layout: Right then Down/Down then Right/Left then Down/Down then Left; Print in Max DPI: No/Yes; HP Real Life Technologies: Off/On; Booklet: None/Booklet-Left Binding/Booklet-Right Binding; Pages to Print: Print All Pages/Print Odd Pages Only/Print Even Pages Only; Borderless Printing: Off/On; Page Borders: Off/On
<b>Fax smart software features</b>	Digital Fax - Fax to PC is available with Windows (Please use: Visit <a href="http://www.hp.com/support">http://www.hp.com/support</a> to download the latest software.
<b>Energy savings feature technology</b>	Schedule On and Schedule Off
<b>Replacement cartridges</b>	HP 910 Black Original Ink Cartridge (~300 pages) 3YL61AN; HP 910 Cyan Original Ink Cartridge 3YL58AN; HP 910 Magenta Original Ink Cartridge 3YL59AN; HP 910 Yellow Original Ink Cartridge 3YL60AN (CMY composite ~315 pages); HP 910XL Black Original Ink Cartridge (~825 pages) 3YL65AN; HP 910XL Cyan Original Ink Cartridge 3YL62A; HP 910XL Magenta Original Ink Cartridge 3YL63A; HP 910XL Yellow Original Ink Cartridge 3YL64AN (CMY composite pages ~825); HP 916XL Black Original Ink Cartridge 3YL66AN (~1,500 pages). Actual yield varies considerably based on content of printed pages and other factors. For details see <a href="http://www.hp.com/go/learnaboutrsupplies">http://www.hp.com/go/learnaboutrsupplies</a>
<b>Supplies feature</b>	HP Instant Ink eligible
<b>Connectivity, standard</b>	1 USB 2.0; 1 Ethernet; 1 Wireless 802.11 a/b/g/n; 1 RJ-11 Fax
<b>Network capabilities</b>	Yes, via built-in Ethernet; Wireless 802.11 a/b/g/n
<b>Wireless capability</b>	Yes, built-in WiFi 802.11 a/b/g/n
<b>Mobile printing capability</b>	Apple AirPrint™; Wi-Fi® Direct Printing; Mopria™ Certified; HP Smart
<b>Network protocols, supported</b>	9100; LPR; SNMP; SLP; Internet Printing Protocol (IPP); WS-Print; Wireless
<b>Software included</b>	HP Printer Software, Shop for Supplies Online
<b>Compatible Operating Systems</b>	Windows 10, 8.1, 8, 7, Windows Server 2008 R2 64-bit, Windows Server 2008 R2 64-bit (SP1), Windows Server 2012 64-bit, Windows Server 2012 R2 64-bit, Windows Server 2016 (Windows XP and Windows Vista not supported)
<b>Energy star certified</b>	Yes
<b>Energy efficiency</b>	EPEAT® Silver
<b>Copy speed black (best, A4)</b>	Up to 3 cpm
<b>Copy speed black (best, letter)</b>	Up to 3 cpm
<b>Copy speed color (best, A4)</b>	Up to 2 cpm
<b>Copy speed color (best, letter)</b>	Up to 2 cpm
<b>Digital sending standard features</b>	Scan to PC
<b>Fax Resolution Black (best)</b>	Up to 300 x 300 dpi
<b>Faxing</b>	Yes, color
<b>Scan speed (normal, A4)</b>	Up to 8 ppm (200 ppi, b&w), Up to 3.5 ppm (200 ppi, color)
<b>Scan speed (normal, letter)</b>	Up to 8 ppm (200 ppi, b&w), Up to 3.5 ppm (200 ppi, color)
<b>Scan file format</b>	JPG, BMP, TIFF, PDF, RTF, TXT, PNG
<b>Scan input modes</b>	Front-panel scan, copy, HP Software, EWS, Mobile apps
<b>Scan technology</b>	Contact Image Sensor (CIS)

<b>Scanner type</b>	Flatbed, ADF
<b>Display</b>	2.7" (6.86 cm) Capacitive Touchscreen CGD
<b>Minimum dimensions (W x D x H)</b>	460 x 341.2 x 234 mm
<b>Minimum dimensions (W x D x H)</b>	18.11 x 13.43 x 9.21 in
<b>Weight</b>	8.2 kg
<b>Weight</b>	18.04 lb
<b>Power consumption</b>	Up to 21 watts (printing), 5.80 watts (ready), 1.00 watts (sleep), 0.08 watts (manual-off) <sup>[3]</sup>
<b>Power supply type</b>	Internal (Built-in) Universal Power Supply
<b>What's in the box</b>	HP OfficeJet Pro 8025 All-in-One Printer; HP 910 Setup Black Ink Cartridge; HP 912 Setup Cyan Ink Cartridge, HP 910 Setup Magenta Ink Cartridge, HP 910 Setup Yellow Ink Cartridge; User Guide; Setup poster; Power cord [For ink volume and page yield information, visit <a href="http://hp.com/go/learnaboutrsupplies">hp.com/go/learnaboutrsupplies</a> ] <sup>[8]</sup>
<b>Warranty</b>	One-year limited hardware warranty; 24-hour, 7 days a week Web support; business hour phone support within warranty period

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] Requires the HP Smart app download. For details on local printing requirements see <http://hp.com/go/mobileprinting>.

[2] Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at <http://hp.com/go/mobileprinting>. Wi-Fi is a registered trademark of Wi-Fi Alliance®.

[3] Based on monthly subscription cost of HP+ Instant Ink 700-page plans without purchase of additional sets of pages compared to cost per page to print ISO/IEC 24711 pages on most in-class, traditional A4 color inkjet cartridge printers & MFPs using original standard capacity cartridges priced for: Australia <299 AUD; New Zealand <349 NZD; Canada <=399 CAD & United States <399 USD. Sale prices not considered for this study. HP Ink Advantage printers excluded due to non-standard hardware & supplies model. Buyers Lab July 2020 study commissioned by HP, based on publicly available information as of June 1, 2020. Printers selected by market share in IDC Quarterly Hardcopy Peripherals Tracker - Final Historical 2020Q1. For details: [www.keypointintelligence.com/HPIstantInk](http://www.keypointintelligence.com/HPIstantInk)

[5] Based on plan usage, Internet connection to eligible HP printer, valid credit/debit card, email address, and delivery service in your geographic area.

[10] Change or cancel your plan at any time online. If you decide to cancel your HP Instant Ink plan you can go back to using HP original Standard or XL cartridges. Plan upgrades are effective immediately and the charges will be applied retrospectively or in the next billing cycle, depending on user choice. Plan downgrades and cancellations are effective after the last day of the current billing period. For full details go to <https://instantink.hpconnected.com/us/en/terms>.

## Technical Specifications Footnotes

[3] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.

[7] HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement

[8] For more information about page yields for replacement cartridges see <http://hp.com/go/learnaboutsupplies> for setup cartridges click on Setup supplies link on the same page.

---

© Copyright 2020 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

