




\*\*PoE Injector is not Included.




## PoE32BD-AS-4000

PoE is a technology that lets network cables carry electrical power and delivery is intelligent, and designed to protect network equipment from overload, underpowering. GVision's Full HD 32" PoE monitors are design for run 24 / 7 / 365 operating.

### DIMENSION

Unit: Inch



### FEATURES

- 32-Inch Screen Size / 1920 x 1080 Full HD Resolution
- Ethernet 10/100 RJ45 PoE Port Input Interface
- Video Signals: HDMI / Display Port (DP)
- 300 nit High Brightness
- Built-In Two 3W Speakers (Left / Right)
- Direct LED Backlight Unit
- 178° / 178° Wide Viewing Angle
- 24 / 7 Operation Design / 3-Year Warranty

1080P  
FULL HD

### SPECIFICATIONS

PoE32BD-AS-4000

DISPLAY	PoE32BD-AS-4000
Screen Size	32 In
Resolution	1920 x 1080
Backlight	Direct LED
Aspect Ratio	16 : 9
Viewing Angle	178° / 178°
Response Time	6.5ms (G2G)
Brightness	300cd/m <sup>2</sup>
Contrast Ratio	3000 : 1
Color Depth	16.7M
INTERFACE	
RJ45	1
HDMI	2
DisplayPort	1
Audio	1
AUDIO	
Speaker	3W x 2
CABINET	
Material	Plastic
Color	Black
POWER	
Input Voltage	PoE 60W
Electrical Rating	40W
INJECTOR TYPE	...
Type	Type 3 PoE++ standard
Power Available at PD	51W
Max. Power Delivered by PSE	60W
Voltage Range (at PSE)	50.0-57.0 V
Voltage Range (at PD)	42.5-57.0 V
Max. Current	600 mA per pair
Max. Cable Resistance Per Pairset	12.5 ohm
FEATURES	
Remote Control	Yes (Battery is not included)
Language	Multi Languages
TEMPERATURE	
Operating	32° F ~ 122° F (0° C ~ 50° C)
Storage	-4° F ~ 140° F (-20° C ~ 60° C)
DIMENSIONS (WxHxD)	
Inch (in) w/o Stand	28.9 x 19.1 x 8.2
Millimeter (mm) w/o Stand	735.1 x 487.2 x 209.7
WEIGHT	
Net Weight	24 lbs (10.88 kg)
VESA™	
Mount Size (mm)	100 x 100

\*\*Injector is not included.

Specifications subject to change without any notice