

Lenovo 100e Chromebook 2nd Gen MTK 81QB000MUS

Product

Lenovo 100e Chromebook 2nd Gen MTK

Region

NA

Country/Region

USA

Machine Type

81QB

TopSeller

TopSeller

Processor

MediaTek MT8173C (4C, 2x A72 @2.1GHz + 2x A53 @1.7GHz)

Graphics

Integrated PowerVR GX6250

Chipset

MediaTek SoC Platform

Memory

4GB Soldered LPDDR3-1866

Storage

32GB eMMC 5.1

Display

11.6" HD (1366x768) TN 250nits Anti-glare

Touchscreen

None

Optical

None

Card Reader

4-in-1 Card Reader

Ethernet

None

WLAN + Bluetooth

Marvell 88W8897 11ac, 2x2 + BT4.1

Camera

720p

Microphone

Mono

Surface Treatment

Texture

Case Color

Black

Case Material

PC / ABS

Keyboard

Non-backlit, English

Fingerprint Reader

None

Security Chip

Discrete TPM 1.2

Battery

Integrated 42Wh

Power Adapter

45W USB-C

Operating System

Chrome OS

Bundled Software

None

Base Warranty

1-year, Mail-in

Bundled Service

None

EAN / UPC / JAN

195477559356

End of Support

2025-02-10

Announce Date

2020-11-10

Recommended Services**Best**

3Y Depot + Accidental Damage Protection (School Year Term)
(5PS0N75610)

Better

3Y Depot + Accidental Damage Protection One (School Year Term)
(5PS0Z44683)

Good

3Y Depot (School Year Term) (5WS0N75691)

Notes:**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

Lenovo 100e Chromebook 2nd Gen MTK Platform Specifications

Product Specifications Reference (PSREF)

Processor	MediaTek® MT8173C, 64-bit Quad-Core Processor (ARM Big.LITTLE architecture), two Efficiency cores (Cortex-A53, up to 1.7GHz), two Performance cores (Cortex-A72, up to 2.1GHz), integrated Imagination PowerVR GX6250 graphics, supports LPDDR3 at up to 933MHz.	Camera	720p HD, single microphone
Graphics	Integrated Graphics in processor	Audio support	Realtek® ALC5650 CGT, Stereo speakers, 2W x 2, combo microphone / headphone jack
Chipset	MTK SoC (System on Chip) platform	Keyboard	6-row, spill-resistant, Anti-pry Key Caps
Memory	4GB / 1866MHz LPDDR3 / soldered to systemboard, no sockets <i>* System clocks down for processors with lower memory controller</i>	Touchpad	One-piece touchpad
Display	11.6" (295mm) HD (1366x768), anti-glare, LED backlight, 250 nits, 16:9 aspect ratio	Security	Security keyhole
Multi-touch	None	Security chip	Discrete TPM 1.2
Storage	16GB or 32GB eMMC 5.1 (embedded Multi Media Card) flash memory on board	Fingerprint reader	None
Optical	None	Battery type	Integrated Li-ion 42Wh battery
Ethernet	None	Max battery life	10 hrs <i>* Battery life varies significantly with hardware configurations, settings, usage, & other factors</i>
WLAN	Marvell® 88W8897, 802.11ac 2x2 Wi-Fi + Bluetooth 4.1	AC adapter	45W USB Type-C AC adapter
WWAN	None	Preload	Google Chrome OS
Bluetooth™	Bluetooth 4.1 wireless, integrated in Wi-Fi + Bluetooth combo adapter	Limited warranty	<i>One of the following, configurable by model:</i> <ul style="list-style-type: none"> • 1-year depot repair service • 1-year mail-in repair service • 2-year/1-yr battery depot repair service
Dimensions	<i>WxDxH:</i> 11.42" x 8.01" x 0.80"; 290mm x 204mm x 20.4mm	Mil-Spec test	MIL-STD-810G military testing
Weight	1.21 kg (2.68 lb)	Environment	EPEAT™ Silver; TCO Certified; RoHS-compliant
Case color	Black		
Case material	PC/ABS plastic		
Media reader	4-in-1 media reader (MMC, SD, SDHC, SDXC)		
Ports	One USB-C 3.1 Gen 1 (with the function of power delivery and data transfer), one USB-A 3.1 Gen 1, HDMI, 4-in-1 media reader (MMC, SD, SDHC, SDXC), combo microphone / headphone jack, security keyhole <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed.</i>		

Note: The specifications above may not be available in all regions.

Lenovo
October 2020



Lenovo 100e Chromebook 2nd Gen MTK

