

# Product Sheet

## Meshify 2



# Index

|     |                        |
|-----|------------------------|
| 3   | Overview               |
| 4   | Key features           |
| 5-6 | General specifications |
| 7   | Package contents       |
|     | Additional information |

# Meshify 2

## A classic evolved.

The Meshify 2 is a high-performance case with a bold, stealth-inspired aesthetic. Its striking exterior features bolt-free, flush tempered glass, a fully removable top granting excellent interior access, and a fully redesigned front with USB-C, hinged mesh panel and removable nylon filter. The flexible dual-layout interior supports large storage arrays and multi-radiator setups that makes cooling a breeze.



# Key features

- Iconic angular mesh design provides filtered airflow with a bold, stealth-inspired aesthetic
- Spacious and extensively adaptable dual-layout interior easily accommodates large motherboards up to and including 285 mm E-ATX
- Support for radiators up to 360 mm in front, 420 mm up top, or 280 mm in the base in the default Open Layout
- Includes 6 HDD/SSD trays, 2 SSD brackets, and 12 universal Multibrackets for mounting up to 10 drives
- Expandable to 14 trays and 4 SSD brackets with 3 Multibrackets installed in the top and bottom for a max of up to 21 drives in Storage Layout
- New chassis design opens up to fully expose the case interior on three sides for totally unhindered installation and cable routing
- New front nylon filter that can be removed for increased airflow
- New front panel design with hinged removable mesh and tether-free bezel for easier access to front fan mounts
- Three front USB ports including one USB 3.1 Gen 2 Type-C with fast charging support and speeds up to 10Gbps
- Ultra-slim Nexus+ 2 fan hub connects up to three PWM fans and six 3-pin fans directly in line with cable channels along the edge of the case
- Outstanding cooling capacity with a total of nine 120/140 mm fan mounts and three preinstalled Dynamic X2 GP-14 fans
- Detachable PSU cable shield and integrated cable guides with velcro straps further simplify cable management behind the board
- Versatile Multibracket that converts any unused fan position to an HDD, SSD or pump mount
- Two vertical GPU slots for use with the Flex VRC-25 PCIe riser, available separately
- Easy-to-clean high airflow nylon filters on the front, top and base with full PSU coverage and convenient front access
- Ventilated PSU shroud with two-part removable cover for optimal cable concealment and front radiator support
- Tool-less, top-latching side panels allow quick access while preventing accidental drops
- Bridgeless expansion slots ensure obstruction-free connections for easier installation and hookup

# General specifications

|                             |                                                                                  |
|-----------------------------|----------------------------------------------------------------------------------|
| 3.5"/2.5" drive mounts      | • 6 included, 14 positions total + 1 Multibracket                                |
| Dedicated 2.5" drive mounts | • 2 included, 4 positions total                                                  |
| 5.25" drive mounts          | • 0                                                                              |
| Expansion slots             | • 7 + 2                                                                          |
| Motherboard compatibility   | • E-ATX (max 285 mm)/ ATX / mATX / Mini-ITX                                      |
| Power supply type           | • ATX                                                                            |
| Front interface             | • 1x USB 3.1 Gen 2 Type-C, 2 x USB 3.0,<br>Audio I/O, Power button, Reset button |
| Total fan mounts            | • 9x 120/140 mm                                                                  |
| Front fan                   | • 3x 120/140 mm (2x Dynamic X2 GP-14 included)                                   |
| Top fan                     | • 3x 120/140 mm                                                                  |
| Rear fan                    | • 1x 120/140 mm (1x Dynamic X2 GP-14 included)                                   |
| Bottom fan                  | • 2x 120/140 mm                                                                  |
| Dust filters                | • Top, front, and bottom                                                         |
| Front radiator              | • Up to 360/280 mm                                                               |
| Top radiator                | • Up to 360/420 mm                                                               |
| Rear radiator               | • 120 mm                                                                         |
| Bottom radiator             | • Up to 240/280 mm                                                               |
| PSU max length              | • 250 mm (with HDD cage installed)                                               |
| GPU max length              | • Storage layout: 315 mm<br>• Open layout: 491 mm (467 mm w/ front fan)          |

# General specifications

|                                             |                             |
|---------------------------------------------|-----------------------------|
| CPU cooler max height                       | • 185 mm                    |
| Cable routing space                         | • 30 mm                     |
| Cable routing grommets                      | • Yes                       |
| Fixed velcro straps                         | • Yes                       |
| Tool-less push-to-lock                      | • Top front and side panels |
| Captive thumbscrews                         | • HDD, SSD and PSU brackets |
| Left side panel                             | • Steel or tempered glass   |
| Right side panel                            | • Steel                     |
| Case dimensions (LxWxH)                     | • 542 x 240 x 474 mm        |
| Case dimensions w/o feet/protrusions/screws | • 541 x 240 x 454 mm        |
| Net weight                                  | • Solid: 10.1 kg            |
|                                             | • TG: 10.5 kg               |
| Package dimensions (LxWxH)                  | • 634 x 542 x 324           |
| Gross weight                                | • Solid: 12.8 kg            |
|                                             | • TG: 13.2 kg               |

# Package contents

- Meshify 2 Case
- User manual
- Large accessory box – HDD trays
- Small accessory box

# Additional information

| Product                       | SKU           | EAN           | UPC          | JAN           | ASIN       |
|-------------------------------|---------------|---------------|--------------|---------------|------------|
| Meshify 2 Black Solid         | FD-C-MES2A-01 | 7340172702429 | 843276102425 | 4537694277112 | B0822Y6H34 |
| Meshify 2 Black TG Dark Tint  | FD-C-MES2A-02 | 7340172702436 | 843276102432 | 4537694277129 | B0822XXF2V |
| Meshify 2 Black TG Light Tint | FD-C-MES2A-03 | 7340172702443 | 843276102449 | 4537694277136 | B0822ZD9NP |
| Meshify 2 Gray TG Light Tint  | FD-C-MES2A-04 | 7340172702450 | 843276102456 | 4537694277143 | B0822YZ3VS |
| Meshify 2 White TG Clear Tint | FD-C-MES2A-05 | 7340172702467 | 843276102463 | 4537694277150 | B0822ZBCD8 |