

Product Sheet

Meshify 2



Index

3	Overview
4	Key features
5-6	General specifications
7	Package contents
	Additional information

Meshify 2

A classic evolved.

The Meshify 2 is a high-performance case with a bold, stealth-inspired aesthetic. Its striking exterior features bolt-free, flush tempered glass, a fully removable top granting excellent interior access, and a fully redesigned front with USB-C, hinged mesh panel and removable nylon filter. The flexible dual-layout interior supports large storage arrays and multi-radiator setups that makes cooling a breeze.



Key features

- Iconic angular mesh design provides filtered airflow with a bold, stealth-inspired aesthetic
- Spacious and extensively adaptable dual-layout interior easily accommodates large motherboards up to and including 285 mm E-ATX
- Support for radiators up to 360 mm in front, 420 mm up top, or 280 mm in the base in the default Open Layout
- Includes 6 HDD/SSD trays, 2 SSD brackets, and 12 universal Multibrackets for mounting up to 10 drives
- Expandable to 14 trays and 4 SSD brackets with 3 Multibrackets installed in the top and bottom for a max of up to 21 drives in Storage Layout
- New chassis design opens up to fully expose the case interior on three sides for totally unhindered installation and cable routing
- New front nylon filter that can be removed for increased airflow
- New front panel design with hinged removable mesh and tether-free bezel for easier access to front fan mounts
- Three front USB ports including one USB 3.1 Gen 2 Type-C with fast charging support and speeds up to 10Gbps
- Ultra-slim Nexus+ 2 fan hub connects up to three PWM fans and six 3-pin fans directly in line with cable channels along the edge of the case
- Outstanding cooling capacity with a total of nine 120/140 mm fan mounts and three preinstalled Dynamic X2 GP-14 fans
- Detachable PSU cable shield and integrated cable guides with velcro straps further simplify cable management behind the board
- Versatile Multibracket that converts any unused fan position to an HDD, SSD or pump mount
- Two vertical GPU slots for use with the Flex VRC-25 PCIe riser, available separately
- Easy-to-clean high airflow nylon filters on the front, top and base with full PSU coverage and convenient front access
- Ventilated PSU shroud with two-part removable cover for optimal cable concealment and front radiator support
- Tool-less, top-latching side panels allow quick access while preventing accidental drops
- Bridgeless expansion slots ensure obstruction-free connections for easier installation and hookup

General specifications

3.5"/2.5" drive mounts	• 6 included, 14 positions total + 1 Multibracket
Dedicated 2.5" drive mounts	• 2 included, 4 positions total
5.25" drive mounts	• 0
Expansion slots	• 7 + 2
Motherboard compatibility	• E-ATX (max 285 mm)/ ATX / mATX / Mini-ITX
Power supply type	• ATX
Front interface	• 1x USB 3.1 Gen 2 Type-C, 2 x USB 3.0, Audio I/O, Power button, Reset button
Total fan mounts	• 9x 120/140 mm
Front fan	• 3x 120/140 mm (2x Dynamic X2 GP-14 included)
Top fan	• 3x 120/140 mm
Rear fan	• 1x 120/140 mm (1x Dynamic X2 GP-14 included)
Bottom fan	• 2x 120/140 mm
Dust filters	• Top, front, and bottom
Front radiator	• Up to 360/280 mm
Top radiator	• Up to 360/420 mm
Rear radiator	• 120 mm
Bottom radiator	• Up to 240/280 mm
PSU max length	• 250 mm (with HDD cage installed)
GPU max length	• Storage layout: 315 mm • Open layout: 491 mm (467 mm w/ front fan)

General specifications

CPU cooler max height	• 185 mm
Cable routing space	• 30 mm
Cable routing grommets	• Yes
Fixed velcro straps	• Yes
Tool-less push-to-lock	• Top front and side panels
Captive thumbscrews	• HDD, SSD and PSU brackets
Left side panel	• Steel or tempered glass
Right side panel	• Steel
Case dimensions (LxWxH)	• 542 x 240 x 474 mm
Case dimensions w/o feet/protrusions/screws	• 541 x 240 x 454 mm
Net weight	• Solid: 10.1 kg
	• TG: 10.5 kg
Package dimensions (LxWxH)	• 634 x 542 x 324
Gross weight	• Solid: 12.8 kg
	• TG: 13.2 kg

Package contents

- Meshify 2 Case
- User manual
- Large accessory box – HDD trays
- Small accessory box

Additional information

Product	SKU	EAN	UPC	JAN	ASIN
Meshify 2 Black Solid	FD-C-MES2A-01	7340172702429	843276102425	4537694277112	B0822Y6H34
Meshify 2 Black TG Dark Tint	FD-C-MES2A-02	7340172702436	843276102432	4537694277129	B0822XXF2V
Meshify 2 Black TG Light Tint	FD-C-MES2A-03	7340172702443	843276102449	4537694277136	B0822ZD9NP
Meshify 2 Gray TG Light Tint	FD-C-MES2A-04	7340172702450	843276102456	4537694277143	B0822YZ3VS
Meshify 2 White TG Clear Tint	FD-C-MES2A-05	7340172702467	843276102463	4537694277150	B0822ZBCD8