


DATA SHEET

KVXLCDP-100, KVXLCDPF-100, KVXLCDP-200, KVXLCDPF-200

KVX SERIES 4K DP KVM EXTENDERS

24/7 TECHNICAL SUPPORT AT 877.877.2269 OR VISIT BLACKBOX.COM



BLACK BOX

OVERVIEW

KVX SERIES DISPLAYPORT KVM EXTENDERS DATA SHEET

INTRODUCTION

The KVX Series are the Black Box® low-cost DisplayPort KVM extenders. In a point-to-point configuration, they enable you to locally use one or two DisplayPort monitors, USB keyboard/mouse/other devices, speaker, and microphone to operate a remote computer, server, or other IT device. Operation is plug-and-play.

Four versions are available:

- KVX Series DisplayPort KVM CATx Extender (KVXLCDP-100)
- KVX Series DisplayPort KVM Fiber Extender (KVXLCDPF-100)
- KVX Series Dual-Head DisplayPort KVM CATx Extender (KVXLCDP-200)
- KVX Series Dual-Head DisplayPort KVM Fiber Extender (KVXLCDPF-200)

FEATURES

- OFFERS DISPLAYPORT INPUT/OUTPUT VIDEO QUALITY UP TO 4K @ 30 HZ
- VIDEO/USB/RS-232/AUDIO BASIC EXTENSION DISTANCE IS 330 FEET (100 METERS) OVER CAT5E/6/7
- VIDEO/USB/RS-232/AUDIO BASIC EXTENSION DISTANCE IS UP TO 18.6 MILES (30 KM) USING A SINGLE-MODE SFP TRANSCEIVER MODULE OR MULTIMODE SFP FOR SHORTER DISTANCES
- THE DISPLAYPORT KVM CONSOLE EXTENDER LETS YOU CONTROL A SERVER, OR COMPUTER OVER SINGLE-MODE OR MULTIMODE FIBER OPTIC CABLE AT DISTANCES OF UP TO 30 KM (DEPENDING ON THE SFP USED, FIBER TYPE, AND FIBER BANDWIDTH*)
- SUPPORTS TRANSPARENT USB EXTENSION VIA TWO USB 2.0 PORTS PLUS TWO USB 1.1 PORTS FOR USB HUBS OR USB HIDS SUCH AS TOUCHSCREENS, PRINTERS, BARCODE READERS, KEYBOARDS, AND MICE
- SUPPLIES BIDIRECTIONAL ANALOG LINE-IN/LINE-OUT EXTENSION AND SERIAL RS-232 EXTENSION
- SUPPORTS DISPLAYPORT LOCAL VIDEO OUTPUT

*NOTE: Reference the supported SFP chart on page 4.

COMPARISON CHART

FEATURES COMPARISON CHART				
	KVXLCDP-100	KVXLCDPF-100	KVXLCDP-200	KVXLCDPF-200
AUDIO	YES	YES	YES	YES
RS-232	YES	YES	YES	YES
TX LOCAL OUT DP CONNECTORS	(1) DISPLAYPORT	(1) DISPLAYPORT	(2) DISPLAYPORT	(2) DISPLAYPORT
TX INPUT DP CONNECTORS	(1) DISPLAYPORT	(1) DISPLAYPORT	(2) DISPLAYPORT	(2) DISPLAYPORT
RX OUTPUT DP CONNECTORS	(1) DISPLAYPORT	(1) DISPLAYPORT	(2) DISPLAYPORT	(2) DISPLAYPORT
MEDIA	TWISTED-PAIR	FIBEROPTIC	TWISTED-PAIR	FIBEROPTIC
MAXIMUM DISTANCE	328 FEET (100 M)	UP TO 18.6 MILES (30 KM), DEPENDING ON SFP USED	328 FEET (100 M)	UP TO 18.6 MILES (30 KM), DEPENDING ON SFP USED
LEVEL	ENTRY-LEVEL	ENTRY-LEVEL	ENTRY-LEVEL	ENTRY-LEVEL



SPECIFICATIONS

KVX SERIES DISPLAYPORT KVM CATX EXTENDERS (KVXLCDP-100)

FRONT VIEW



CATx Transmitter

BACK VIEW



CATx Transmitter

FRONT VIEW



CATx Receiver

BACK VIEW



CATx Receiver

WHAT'S INCLUDED WITH THE KVXLCDP-100

- (1) TRANSMITTER
- (1) RECEIVER
- (2) 5V, 2A POWER SUPPLIES (INCLUDES US, EU, AND UK PLUG TYPES)
- (1) DISPLAYPORT CABLE, M/M 1.2M (4 FT.)
- (1) USB TYPE A TO B CABLE, M/M 1.8M (6 FT.)
- (1) 3.5MM DUAL AUDIO/MIC CABLE, M/M 1.8M (6 FT.)
- (2) DESKMOUNT KITS WITH SCREWS (KVXLC-DMK)

SPECIFICATIONS FOR KVX SERIES DISPLAYPORT KVM CATX EXTENDER (KVXLCDP-100)

SPECIFICATION	CATX TRANSMITTER	CATX RECEIVER
CONNECTORS	Host connection: Video Input: (1) DisplayPort female Serial Control Port: (1) DB9 female Link Port: (1) RJ-45 female USB: (1) USB Type B female Audio: (1) Line in, (1) Line out; Local Video Output: (1) DisplayPort female	Console connection: Video Output: (1) DisplayPort female Serial Control Port: (1) DB9 male Link Port: (1) RJ-45 female USB 2.0: (4) USB Type A female Audio: (1) Mic In, (1) Speaker Out
DISTANCE	CATx cable: Up to 328 ft. (100 m)	CATx cable: Up to 328 ft. (100 m)
INDICATORS	(1) Power LED (red), (1) Link LED (green)	(1) Power LED (red), (1) Link LED (green)
MAXIMUM RESOLUTION	4K @ 30 Hz, 3840 x 2160 @ 30 Hz (8-, 10-bit input)	4K @ 30 Hz, 3840 x 2160 @ 30 Hz (8-bit output only)
DDC SUPPORTED	DDC, DDC2, DDC2B	DDC, DDC2, DDC2B
HOUSING MATERIAL	Metal chassis	Metal chassis
OPERATING SYSTEM	OS independent	OS independent
ENVIRONMENTAL	Operating Temperature: 32 to 122° F (0 to 50° C); Storage Temperature: -4 to +140° F (-20 to +60° C); Operating Humidity: 0 to 80%, noncondensing	Operating Temperature: 32 to 122° F (0 to 50° C); Storage Temperature: -4 to +140° F (-20 to +60° C); Operating Humidity: 0 to 80%, noncondensing
POWER	External 5-VDC, 2-A power supply	External 5-VDC, 2-A power supply
DIMENSIONS	0.83" H x 7.09" W x 3.27" D (2.1 x 18 x 8.3 cm)	0.83" H x 7.09" W x 3.27" D (2.1 x 18 x 8.3 cm)
WEIGHT	0.82 lb. (0.372 kg)	0.83 lb. (0.378 kg)

SPECIFICATIONS

KVX SERIES DISPLAYPORT KVM FIBER EXTENDERS (KVXLCDPF-100)



WHAT'S INCLUDED WITH THE KVXLCDPF-100

- (1) TRANSMITTER
- (1) RECEIVER
- (2) 5V, 2A POWER SUPPLIES (INCLUDES US, EU, AND UK PLUG TYPES)
- (1) DISPLAYPORT CABLE, M/M 1.2M (4 FT.)
- (1) USB TYPE A TO B CABLE, M/M 1.8M (6 FT.)
- (1) 3.5MM DUAL AUDIO/MIC CABLE, M/M 1.8M (6 FT.)
- (2) DESKMOUNT KITS WITH SCREWS (KVXLC-DMK)
- NOTE: SFP not included, must be ordered separately. See chart below.

SPECIFICATIONS FOR KVX SERIES DISPLAYPORT KVM FIBER EXTENDER (KVXLCDPF-100)		
SPECIFICATION	FIBER TRANSMITTER	FIBER RECEIVER
CONNECTORS	Host connection: Video Input: (1) DisplayPort female Serial Control Port: (1) DB9 female Link Port: (1) SFP cage USB: (1) USB Type B female Audio: (1) Line in, (1) Line out; Local Video Output: (1) DisplayPort female	Console connection: Video Output: (1) DisplayPort female Serial Control Port: (1) DB9 male Link Port: (1) SFP cage USB 2.0: (4) USB Type A female Audio: (1) Mic In, (1) Speaker Out
DISTANCE	Fiberoptic cable: Up to 18.6 miles (30 km), depending on SFP used	Fiberoptic cable: Up to 18.6 miles (30 km), depending on SFP used
INDICATORS	(1) Power LED	(1) Power LED
MAXIMUM RESOLUTION	4K @ 30 Hz, 3840 x 2160 @ 30 Hz (8-, 10-bit input)	4K @ 30 Hz, 3840 x 2160 @ 30 Hz (8-bit output only)
DDC SUPPORTED	DDC, DDC2, DDC2B	DDC, DDC2, DDC2B
HOUSING MATERIAL	Metal chassis	Metal chassis
OPERATING SYSTEM	OS independent	OS independent
ENVIRONMENTAL	Operating Temperature: 32 to 122° F (0 to 50° C); Storage Temperature: -4 to +140° F (-20 to +60° C); Operating Humidity: 0 to 80%, noncondensing	Operating Temperature: 32 to 122° F (0 to 50° C); Storage Temperature: -4 to +140° F (-20 to +60° C); Operating Humidity: 0 to 80%, noncondensing
POWER	External 5-VDC, 2-A power supply	External 5-VDC, 2-A power supply
DIMENSIONS	0.83" H x 7.09" W x 3.27" D (2.1 x 18 x 8.3 cm)	0.83" H x 7.09" W x 3.27" D (2.1 x 18 x 8.3 cm)
WEIGHT	0.82 lb. (0.372 kg) (no SFP)	0.83 lb. (0.378 kg) (no SFP)

NOTE: SFP modules are not included and must be ordered separately. See the chart below.

COMPATIBLE SFP MODULES		
PART NUMBER	DESCRIPTION	DISTANCE
1-GBPS CONNECTIONS		
LFP441	SFP 1.25-Gb, 850-nm Multimode Fiber, LC	550 m
LFP442	SFP 1.25-Gb, 1310-nm Single-mode Fiber, LC	20 km
LFP412	SFP with Extended Diagnostics - 1250-Mbps Multimode Fiber, 1310-nm	2 km
LFP413	SFP with Extended Diagnostics - 1250-Mbps Single-Mode Fiber, 1310-nm	10 km
LFP414	SFP with Extended Diagnostics - 1250-Mbps, Singlemode Fiber, 1310-nm	30 km
LFP416	SFP 1250-Mbps, Extended Diagnostics, 10/100/1000BASE-T, SGMII Interface, RJ-45	100 m

NOTE: Other SFPs may work but have not been validated by Black Box, we recommend you use the suggested SFPs to avoid technical incompatibilities.



SPECIFICATIONS

KVX SERIES DISPLAYPORT DUAL-HEAD KVM CATX EXTENDERS (KVXLCDP-200)



CATx Transmitter



CATx Transmitter



CATx Receiver



CATx Receiver

WHAT'S INCLUDED WITH THE KVXLCDP-200

- (1) TRANSMITTER
- (1) RECEIVER
- (2) 5V, 2A POWER SUPPLIES (INCLUDES US, EU, AND UK PLUG TYPES)
- (2) DISPLAYPORT CABLES, 1.2M (4 FT.)
- (1) USB TYPE A TO B CABLE, M/M 1.8M (6 FT.)
- (1) 3.5MM DUAL AUDIO/MIC CABLE, M/M 1.8M (6 FT.)
- (2) DESKMOUNT KITS WITH SCREWS (KVXLC-DMK)

SPECIFICATIONS FOR KVX SERIES DISPLAYPORT DUAL-HEAD KVM CATX EXTENDER (KVXLCDP-200)

SPECIFICATION	CATX TRANSMITTER	CATX RECEIVER
CONNECTORS	Host connection: Video Input: (2) DisplayPort female Serial Control Port: (1) DB9 female Link Port: (2) RJ-45 female USB: (1) USB Type B female Audio: (1) Line in, (1) Line out; Local Video Output: (2) DisplayPort female	Console connection: Video Output: (2) DisplayPort female Serial Control Port: (1) DB9 male Link Port: (2) RJ-45 female USB 2.0: (4) USB Type A female Audio: (1) Mic In, (1) Speaker Out
DISTANCE	CATx cable: Up to 328 ft. (100 m)	CATx cable: Up to 328 ft. (100 m)
INDICATORS	(1) Power LED (red), (1) Link LED (green)	(1) Power LED (red), (1) Link LED (green)
MAXIMUM RESOLUTION	4K @ 30 Hz, 3840 x 2160 @ 30 Hz (8-, 10-bit input)	4K @ 30 Hz, 3840 x 2160 @ 30 Hz (8-bit output only)
DDC SUPPORTED	DDC, DDC2, DDC2B	DDC, DDC2, DDC2B
HOUSING MATERIAL	Metal chassis	Metal chassis
OPERATING SYSTEM	OS independent	OS independent
ENVIRONMENTAL	Operating Temperature: 32 to 122° F (0 to 50° C); Storage Temperature: -4 to +140° F (-20 to +60° C); Operating Humidity: 0 to 80%, noncondensing	Operating Temperature: 32 to 122° F (0 to 50° C); Storage Temperature: -4 to +140° F (-20 to +60° C); Operating Humidity: 0 to 80%, noncondensing
POWER	External 5-VDC, 2-A power supply	External 5-VDC, 2-A power supply
DIMENSIONS	1.71" H x 7.09" W x 3.27" D (4.4 x 18.0 x 8.3 cm)	1.71" H x 7.09" W x 3.27" D (4.4 x 18.0 x 8.3 cm)
WEIGHT	0.84 lb. (0.381 kg)	0.85 lb. (0.386 kg)



SPECIFICATIONS

KVX SERIES DISPLAYPORT DUAL-HEAD KVM FIBER EXTENDERS (KVXLCDPF-200)



WHAT'S INCLUDED WITH THE KVXLCDPF-200

- (1) TRANSMITTER
- (1) RECEIVER
- (2) 5V, 2A POWER SUPPLIES (INCLUDES US, EU, AND UK PLUG TYPES)
- (2) DISPLAYPORT CABLES 1.2M (4 FT.)
- (1) USB TYPE A TO B CABLE, M/M 1.8M (6 FT.)
- (1) 3.5MM DUAL AUDIO/MIC CABLE, M/M 1.8M (6 FT.)
- (2) DESKMOUNT KITS WITH SCREWS (KVXLC-DMK)

NOTE: SFP not included, must be ordered separately. See chart below.

SPECIFICATIONS FOR KVX SERIES DISPLAYPORT DUAL-HEAD KVM FIBER EXTENDER (KVXLCDPF-200)		
SPECIFICATION	FIBER TRANSMITTER	FIBER RECEIVER
CONNECTORS	Host connection: Video Input: (2) DisplayPort female Serial Control Port: (1) DB9 female Link Port: (2) SFP cage USB: (1) USB Type B female Audio: (1) Line in, (1) Line out; Local Video Output: (2) DisplayPort female	Console connection: Video Output: (2) DisplayPort female Serial Control Port: (1) DB9 male Link Port: (2) SFP cage USB 2.0: (4) USB Type A female Audio: (1) Mic In, (1) Speaker Out
DISTANCE	Fiberoptic cable: Up to 18.6 miles (30 km), depending on SFP used	Fiberoptic cable: Up to 18.6 miles (30 km), depending on SFP used
INDICATORS	(1) Power LED	(1) Power LED
MAXIMUM RESOLUTION	4K @ 30 Hz, 3840 x 2160 @ 30 Hz (8-, 10-bit input)	4K @ 30 Hz, 3840 x 2160 @ 30 Hz (8-bit output only)
DDC SUPPORTED	DDC, DDC2, DDC2B	DDC, DDC2, DDC2B
HOUSING MATERIAL	Metal chassis	Metal chassis
OPERATING SYSTEM	OS independent	OS independent
ENVIRONMENTAL	Operating Temperature: 32 to 122° F (0 to 50° C); Storage Temperature: -4 to +140° F (-20 to +60° C); Operating Humidity: 0 to 80%, noncondensing	Operating Temperature: 32 to 122° F (0 to 50° C); Storage Temperature: -4 to +140° F (-20 to +60° C); Operating Humidity: 0 to 80%, noncondensing
POWER	External 5-VDC, 2-A power supply	External 5-VDC, 2-A power supply
DIMENSIONS	1.71" H x 7.09" W x 3.27" D (4.4 x 18.0 x 8.3 cm)	1.71" H x 7.09" W x 3.27" D (4.4 x 18.0 x 8.3 cm)
WEIGHT	0.85 lb. (0.386 kg) (no SFP)	0.85 lb. (0.386 kg) (no SFP)

NOTE: SFP modules are not included and must be ordered separately. See the chart below.

COMPATIBLE SFP MODULES		
PART NUMBER	DESCRIPTION	DISTANCE
1-Gbps CONNECTIONS		
LFP441	SFP 1.25-Gb, 850-nm Multimode Fiber, LC	550 m
LFP442	SFP 1.25-Gb, 1310-nm Single-mode Fiber, LC	20 km
LFP412	SFP with Extended Diagnostics - 1250-Mbps Multimode Fiber, 1310-nm	2 km
LFP413	SFP with Extended Diagnostics - 1250-Mbps Single-Mode Fiber, 1310-nm	10 km
LFP414	SFP with Extended Diagnostics - 1250-Mbps, Singlemode Fiber, 1310-nm	30 km
LFP416	SFP 1250-Mbps, Extended Diagnostics, 10/100/1000BASE-T, SGMII Interface, RJ-45	100 m

NOTE: Other SFPs may work but have not been validated by Black Box, we recommend you use the suggested SFPs to avoid technical incompatibilities.

ORDERING INFORMATION

ITEM	CODE
KVX DisplayPort KVM CATx Extenders	
Single-Head Transmitter and Receiver Kit	KVXLCDP-100
Dual-Head Transmitter and Receiver Kit	KVXLCDP-200
KVX DisplayPort KVM Fiber Extenders	
Single-Head Transmitter and Receiver Kit	KVXLCDPF-100
Dual-Head Transmitter and Receiver Kit	KVXLCDPF-200
Accessories	
Rackmount Kit	KVXLC-RMK
Desktop Mounting Bracket Kit	KVXLC-DMK
DIN Rail Mounting Bracket	KVXLC-DRM
Spare Power Supply	KVXLC-PS
NOTE: Extender kits contain (1) Transmitter and (1) Receiver	

NOTES _____

DISCLAIMER

Black Box Corporation shall not be liable for damages of any kind, including, but not limited to, punitive, consequential or cost of cover damages, resulting from any errors in the product information or specifications set forth in this document and Black Box Corporation may revise this document at any time without notice.

ABOUT BLACK BOX

Black Box® is a trusted IT solutions provider delivering cutting-edge technology solutions and world-class consulting services to businesses on every continent. The breadth of our global reach and depth of expertise accelerate customer success by bringing people, ideas, and technology together to solve real-world business problems. Our IT infrastructure solutions, services, and products enable secure, flawless connectivity and meaningful collaboration across town or around the globe. To learn more, visit the Black Box website at <https://www.blackbox.com>. Follow the company on Twitter @BlackBox_ns.

TRADEMARKS

Black Box and the Black Box logo type and mark are registered trademarks of BB Technologies, Inc.

Any other trademarks mentioned in this document are acknowledged to be the property of the trademark owners.