

Product data sheet

Specifications



APC Rack PDU 9000 Switched, ZeroU, 16A, 100-240V, (21) C13/C15 & (3) C19/C21, Japan

APDU9959J

Overview

Lead time Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Provided Equipment	Installation guide Rack Mounting brackets Safety guide

Complementary

Input Voltage	200 V
Height	70.7 in (179.7 cm)
Width	2.2 in (5.5 cm)
Output Voltage	200 V
Depth	1.8 in (4.6 cm)
Net Weight	12.24 lb(US) (5.55 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	IEC 60320 L6-20P
Mounting Mode	Not rack-mountable
Rack units	0U
USB compatible	No
Mounting position	Vertical
Communication Port Protocol	SNMP Redfish
Line Rated Current	16 A
Acceptable Input Voltage	100...240 V
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz
Outlet type and quantity	21C13/C15 3C19/C21

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Communication Network Type	10/100/1000BASE-T
----------------------------	-------------------

Environment

Product Certifications	FCC part 15 class A PSE
------------------------	----------------------------

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
---------------------------------------	--------------------------

Relative Humidity	5...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
-------------------------------------	----------------------------

Storage Relative Humidity	5...95 %
---------------------------	----------

Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
------------------	--

Ordering and shipping details

GTIN	731304412922
------	--------------

Country of origin	IN
-------------------	----

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	78.8 in (200.2 cm)
------------------	--------------------

Package 1 Width	4.5 in (11.4 cm)
-----------------	------------------

Package 1 Length	6.5 in (16.5 cm)
------------------	------------------

Package 1 Weight	17.33 lb(US) (7.86 kg)
------------------	------------------------

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile [End of Life Information](#)