

# Product data sheet

Specifications



## APC Rack PDU 9000 Switched, ZeroU, 17.3kW, 208V, (20) C13/C15, (12) C19/C21

APDU9966

### Overview

Lead time Usually in Stock

### Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Cord length	6 ft (1.8 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Safety guide

### Complementary

Input Voltage	208 V 3 phase
Height	72.2 in (183.3 cm)
Width	4.4 in (11.1 cm)
Output Voltage	208 V
Depth	3.0 in (7.6 cm)
Net Weight	30.9 lb(US) (14 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 60 A 3P+PE
Mounting Mode	Rack-mounted
Communication Port Protocol	SNMP Redfish
Line Rated Current	48 A
Max line current	48 A
Input current limits	60 A
Load Capacity	17300 VA
Input Frequency	50/60 Hz
Outlet type and quantity	20C13/C15 12C19/C21
Communication Network Type	10/100/1000BASE-T

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

<b>Product Certifications</b>	cUL Listed FCC part 15 class A
<b>Standards</b>	IEC 62368-1
<b>Ambient Air Temperature for Operation</b>	23...140 °F (-5...60 °C)
<b>Relative Humidity</b>	5...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient Air Temperature for Storage</b>	-13...149 °F (-25...65 °C)
<b>Storage Relative Humidity</b>	5...95 %
<b>Storage altitude</b>	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

<b>GTIN</b>	731304356332
-------------	--------------

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	84.6 in (214.9 cm)
<b>Package 1 Width</b>	4.4 in (11.2 cm)
<b>Package 1 Length</b>	8.7 in (22.1 cm)
<b>Package 1 Weight</b>	44.004 lb(US) (19.96 kg)

## Contractual warranty

<b>Warranty</b>	3 years repair or replace
-----------------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

RoHS Exemption Information Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	<a href="#">End of Life Information</a>