

Product data sheet

Specifications



APC Rack PDU, 9000 switched, 0U, 17.3kW, 208V, 42 C13 and C15, 6 C19 and C21 sockets

APDU9967

Overview

Lead time Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Cord length	6 ft (1.8 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Safety guide

Complementary

Input Voltage	208 V 3 phase
Height	72.2 in (183.3 cm)
Width	4.4 in (11.1 cm)
Output Voltage	208 V
Depth	3.0 in (7.6 cm)
Net Weight	32.06 lb(US) (14.54 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 60 A 3P+PE
Mounting Mode	Not rack-mountable
Rack units	0U
Mounting position	Vertical
Communication Port Protocol	SNMP Redfish
Line Rated Current	48 A
Max line current	48 A
Input current limits	60 A
Load Capacity	17300 VA
Input Frequency	50/60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Outlet type and quantity	42C13/C15 6C19/C21
Communication Network Type	10/100/1000BASE-T

Environment

Product Certifications	cUL Listed FCC part 15 class A UL Listed VCCI Class A
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304356349
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	84.6 in (214.9 cm)
Package 1 Width	4.4 in (11.2 cm)
Package 1 Length	8.7 in (22.1 cm)
Package 1 Weight	44.004 lb(US) (19.96 kg)

Contractual warranty

Warranty	3 years repair or replace
-----------------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Compliant with Exemptions

China RoHS Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile [End of Life Information](#)