



Stealth 15M A11SEK-210

Manufacturer Part #	Stealth15M210
OS	Windows 10 Home
CPU	Core i7-1185G7
CPU Speed	1.2 - 4.8GHz
Chipset	-
Color	White
Screen Size	15.6" FHD (1920*1080), IPS-Level 144Hz 45%NTSC Thin Bezel
Resolution	1920x1080 (16:9)
GPU	NVIDIA® GeForce RTX™ 2060 (Max-Q)
Video Memory	6G GDDR6
Keyboard	Steel Series single zone RGB keyboard with Anti-Ghost key (84 Key)
Audio	Nahimic 3 / Hi-Res Audio
Speaker	Dynaudio Tech Speakers 2W *2
Memory	16GB (8G*2) DDR4 3200MHz
HDD Capacity	512GB NVMe SSD
HDD Interface	NVMe
Optical Drive Type	–
LAN	USB Dongle
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
Bluetooth	BT 5.1
Card Reader	Micro SD (UHS-III)
Webcam	720p HD Webcam
USB	2x USB 3.2 Gen1
Type-C Port	1x Thunderbolt 4
Video Port	HDMI (supports 4K @ 60Hz)
Audio Port	1/1
AC Power Adaptor	150W Slim
Battery Pack	3 cell (52Whr)
Dimension	14.10"x9.76"x0.63"
Weight	3.73 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)