



# SD4850P USB-C 10Gbps Dual Video Driverless Docking Station - 100W PD - DP++/HDMI - Windows

Part Number: K34115NA/EU/AP/JP

UPC Code: Each: 085896 34115 4 | Case: 50 085896 34115 9 | Pallet: 70 085896 34115 3

## Ultimate driverless USB-C dock performance

The SD4850P USB-C 10Gbps Dual Video Driverless Docking Station - 100W PD - DP++/HDMI - Windows is the top-of-the-line USB-C driverless dock for any Windows OS laptop with a USB-C port supporting DisplayPort Alt Mode and Power Delivery. One connection expands your Windows 7 or above laptop into a fully powered yet streamlined desktop setup supporting up to Dual 4K via a 13-in-1 design complete with 6 USB ports.

Features include:

- Driverless, USB-C Connectivity with 10Gbps Data Transfer Speed and 100W Power Delivery (PD 3.0)
- Numerous Video Ports
- Dynamic Video Support
- Universal Windows Compatibility
- 13-in-1 design with 6 USB-ports
- UHS II SD 4.0 Memory Card Reader
- Free Kensington DockWorks™ Software and 3-Year Warranty



All specifications are subject to change without notice. Products may not be available in all markets. Kensington and the ACCO name and design are registered trademarks of ACCO Brands. Kensington The Professionals' Choice is a trademark of ACCO Brands. All other registered and unregistered trademarks are the property of their respective owners. © 2020 Kensington Computer Products Group, a division of ACCO Brands. All rights reserved. k20-9084p

**Kensington**  
The Professionals' Choice™

FOR MORE INFORMATION CONTACT: 1-855-692-0054 | sales@kensington.com

## SD4850P USB-C 10Gbps Dual Video Driverless Docking Station - 100W PD - DP++/HDMI - Windows

Part Number: K34115NA/EU/AP/JP

UPC Code: Each: 085896 34115 4 | Case: 50 085896 34115 9 | Pallet: 70 085896 34115 3



**Driverless, USB-C Connectivity with 10Gbps Data Transfer Speed and 100W Power Delivery (PD 3.0)** for all Windows OS laptops with a USB-C port supporting DisplayPort Alt Mode and Power Delivery



**Numerous Video Ports** with two DisplayPort++ ports and one HDMI port, the user can select the right connections and resolutions for their needs — an optional USB-C Alt Mode can be used in place of one DP++ port.



**Dynamic Video Support** through the docking station's dynamic 4K switch allowing you to toggle between modes, prioritizing resolution over USB, Ethernet, and SD Card speeds.



**Universal Windows Compatibility** connecting seamlessly to any laptop running Windows 7 and above



**13-in-1 design** with 6 USB-ports and built-in UHS II SD 4.0 Memory Card Reader gives full power to your laptop and devices, eliminating the need for additional adapters and accessories.



**Free Kensington DockWorks™ Software and 3-Year Warranty** lets you rest assured, you're covered by Kensington.

## SD4850P USB-C 10Gbps Dual Video Driverless Docking Station - 100W PD - DP++/HDMI - Windows

Part Number: K34115NA/EU/AP/JP

UPC Code: Each: 085896 34115 4 | Case: 50 085896 34115 9 | Pallet: 70 085896 34115 3

### System Requirement

Supported Systems	All Laptops with USB-C port with USB-C Alt mode
Supported Operating System	Windows 7 or above
Plug & Play	Yes
System Resource Requirement	CPU: Intel® Core™ i5 6th generation or above Memory: 8GB or above GPU: Intel® HD Graphics 620 or above
Additional Software Information	DockWorks

### USB Interface

Type of USB Connector	USB-C Connector
USB-C Power Delivery	5V/ 9V/ 12V/ 15V @ 3A (up to 100W, 20V @ 5A)
Host Connector	Support USB-C 3.2 Gen1/Gen2 with USB-C Alt mode
Ports (Front)	1 x USB-A 3.2 Gen2, support BC1.2 (5V/1.5A) & Apple Charging (5V/2.4A) 1 x USB-C 3.2 Gen2 support PDO 5V/3A, & BC1.2 (5V/1.5A) & Apple Charging (5V/2.4A) 1 x SD card slot (SD4.0, UHS-II)
Ports (Back)	4 x USB-A 3.2 Gen1 (5V/0.9A)

### Network Connections

Ethernet Port	RJ45 (10/100/1000 Mbps)
---------------	-------------------------

### Host Connectivity

Host Docking Connector	USB-C with Power Delivery up to 100W
------------------------	--------------------------------------

### Audio Connections

Audio Connectors	1 x 3.5mm audio combo jack (stereo L/R)
------------------	---

### Other Features

LED Indicator	Blue Power indicator
Security	Kensington Security Slot / Nano Slot
VESA Mount Compatible	Yes

### Material Specifications

Exterior	Enclosure: PC ABS with texture
Bottom	Enclosure: PC ABS with texture and TPU
Product Color	PMS Black

## SD4850P USB-C 10Gbps Dual Video Driverless Docking Station - 100W PD - DP++/HDMI - Windows

Part Number: K34115NA/EU/AP/JP | UPC Code: 8 5896 3411 5

### Video Connections

Video Connectors












1 x USB-C DP Alt Mode, 2 x DisplayPort++ v1.4, 1 x HDMI v2.0













Minimum Resolution (DP1.2/HBR2)













Single 4K@30Hz  
Dual 1080p@60Hz  
Triple 1600 x 900@60Hz


Maximum Resolution (DP1.4/HBR3)

Single 4K@60Hz  
Dual 4K@60Hz  
Triple 4K@60Hz

		1X 					
							
<b>4K 30Hz</b>	HBR2(DP1.2)	<b>3840*2160@30Hz</b>		USB 3.2 Gen2 (10Gbps)	USB 3.2 Gen1 (5Gbps)		1000Mbps
	HBR3(DP1.4)	<b>3840*2160@60Hz</b>					
<b>4K 60Hz</b>	HBR2(DP1.2)	<b>3840*2160@60Hz</b>		USB 2.0 (480Mbps)	USB 2.0 (480Mbps)		100Mbps
	HBR3(DP1.4)	<b>3840*2160@60Hz</b>					

		3X 						
								
<b>4K 30Hz</b>	HBR2 (DP1.2)	<b>1600*900@60Hz</b>			USB 3.2 Gen2 (10Gbps)	USB 3.2 Gen1 (5Gbps)		1000Mbps
	HBR3 (DP1.4)	<b>3840*2160@30Hz</b>						
<b>4K 60Hz</b>	HBR2 (DP1.2)	<b>1920*1080@60Hz</b>			USB 2.0 (480Mbps)	USB 2.0 (480Mbps)		100Mbps
	HBR3 (DP1.4)	<b>3840*2160@60Hz</b>						

		2X 						
								
<b>4K 30Hz</b>	HBR2 (DP1.2)	<b>1920*1080@60Hz</b>			USB 3.1 Gen2 (10Gbps)	USB 3.1 Gen1 (5Gbps)		1000 Mbps
	HBR3 (DP1.4)	<b>3840*2160@60Hz</b>						
<b>4K 60Hz</b>	HBR2 (DP1.2)	<b>3840*2160@30Hz</b>			USB 2.0 (480Mbps)	USB 2.0 (480Mbps)		100 Mbps
	HBR3 (DP1.4)	<b>3840*2160@60Hz</b>						



## SD4850P USB-C 10Gbps Dual Video Driverless Docking Station - 100W PD - DP++/HDMI - Windows

Part Number: K34115NA/EU/AP/JP | UPC Code: 8 5896 3411 5

### Product Dimensions

Unit Weight	0.64lbs (0.294kg)
Unit Dimensions without Peripherals	Width: 8.26in (210mm) Depth: 3.54in (90mm) Height: 1.23in (31.3mm)
Enclosure Color & Material	PMS Black, PC ABS
Desktop Footprint	29.29in <sup>2</sup> (189cm <sup>2</sup> )

### Packaging Dimensions

Packaging Style	Bulk Package (K34115NA/EU) Retail Package (K34115 AP/JP)
Packaging Dimensions	Width: 9.25in (235mm) Depth: 5.86in (149mm) Height: 3.58in (91mm)
Packaging Weight	3.0lbs (1.396 kg)
Packaging Content	SD4850P Dock, 1m USB-C 3.2 Gen2 Cable, Power Supply, Instruction Guide, Warranty Card, Compliance Sheet, Welcome Card Insert (NA SKU)
Master Carton	4

### Power & Environmental

Power Adapter Rating	Input: 100-240V; 1.8A / Output: 20V DC 8.5A (170W)
Relative Humidity	55% operating temperature @ 73°F (25°C)
Operating Temperature	32 to 104°F (0 to 40°C)
Storage Temperature	-0.4 to 140°F (-18 to 60°C)

### Country of Origin, Regulatory, & Warranty

Country of Origin	Thailand
Certification & Compliance	FCC, IC, CE, RCM, VCCI, BSMI, NOM, CB, RoHS, ACCO RSL
Warranty	3-Year Limited - worldwide



All specifications are subject to change without notice. Products may not be available in all markets. Kensington and the ACCO name and design are registered trademarks of ACCO Brands. Kensington The Professionals' Choice is a trademark of ACCO Brands. All other registered and unregistered trademarks are the property of their respective owners. © 2020 Kensington Computer Products Group, a division of ACCO Brands. All rights reserved. k20-9084p

# Kensington

The Professionals' Choice™