

Country	ca
Ean	0824142236093
OS	Windows 10 Home
Color	Carbon Gray
Screen Size / Type	15.6" FHD, IPS-Level 60Hz 45%NTSCThin Bezel
Resolution/ Ratio	1920x1080 16:9
CPU/Processor	Core i5-1135G7
CPU Frequency	0.9 - 4.2GHz
Graphics	Iris Xe Graphics
System Memroy	DDR IV 8GB*2 3200MHz
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	512GB NVMe PCIe SSD
HDD Interface	NVMe
SSD	1x M.2 SSD NVMe PCIe Gen3x4 1x M.2 SSD PCIe Gen4x4
LAN	-
WLAN	Intel Harrison Peak (2x2 802.11 ax)
BT	BT 5.1
Card Reader	Micro SD
HDMI-out	4K @ 30Hz
USB Type C	USB 3.2 Gen 2 Type C *1
USB	USB 3.2 Gen1*2
Keyboard	White backlight 84 Key
Touch Pad	Multi Touch
Mic-in/ Headphone-out	Mic-in/Headphone-out Combo
Speaker	Speakers 2W * 2
Webcam	720p HD Webcam
Battery Pack	3 cell (52Whr) Li-Polymer
AC Adapter	65W
Unit weight	3.53 lbs
Unit Dimension	14.05" x 9.20" x 0.67"
UPC	824142236093
UCC-14	10824142236090
Warranty	1 year Limited warranty (Include 1 Year Global)