



Modern 14 B11MO-038

Manufacturer Part #	Modern14B038
OS	Windows 10 Home
CPU	Core i7-1165G7
CPU Speed	0.9 - 4.2GHz
Chipset	-
Color	Beige Mousse
Screen Size	14" THIN BEZEL Full HD IPS-Level 60Hz 45%NTSC
Resolution	1920x1080 (16:9)
GPU	Intel® Iris® Xe
Keyboard	White backlight 84 Key
Audio	Nahimic 3 / Hi-Res Audio
Speaker	Speakers 2W * 2
Memory	8GB (8GB*1) DDR4 3200MHz
HDD Capacity	512GB NVMe SSD
HDD Interface	NVMe
Optical Drive Type	-
LAN	-
WLAN	Intel 9560 Jefferson Peak (2x2 802.11 ac)
Bluetooth	BT 5
Card Reader	SD (XC/HC)
Webcam	720p HD Webcam
USB	2x Type A USB 2.0
Type-C Port	1x USB 3.2 Gen 2 Type C
Video Port	HDMI (supports 4K @ 30Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	65W
Battery Pack	3 cell (52Whr)
Dimension	12.68" x 8.74" x 0.63"
Weight	2.62 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)