

SPECIFICATIONS

Model Name	H410I PRO WIFI
CPU Support	Supports 10th Gen Intel® Core™ and Pentium® Gold / Celeron® processors
CPU Socket	LGA 1200
Chipset	Intel® H410 Chipset
Graphics Interface	1x PCI-E 3.0 x16 slot
Display Interface	DisplayPort, HDMI - Requires Processor Graphics
Memory Support	2 DIMMs, Dual Channel DDR4-2933 MHz (Max)
Storage	1x Turbo M.2 32Gb/s slot, 4x SATA 6Gb/s
USB ports	4x USB 3.2 Gen 1 5Gbps (Type-A) + 4x USB 2.0
LAN	Intel® I219V Gigabit LAN
Wireless / Bluetooth	Intel® Wireless-AC 3168, Bluetooth 4.2
Audio	8-Channel (7.1) HD Audio with Audio Boost

FEATURES



Core Boost

With premium layout and fully digital power design to support more cores and provide better performance.



DDR4 Boost

Advanced technology to deliver pure data signals for the best gaming performance and stability.



EZ Debug LED

Easiest way to troubleshoot.



PCI-E Steel Armor

Protecting VGA cards against bending and EMI



Audio Boost


Reward your ears with studio grade sound quality for the most immersive audio experience.



Intel WiFi solution

Build in Intel® Wi-Fi / Bluetooth, delivering AC speeds up to 433Mbps without any cable limitation.

CONNECTIONS



- | | |
|-------------------------------|-----------------------|
| 1. DisplayPort | 2. LAN |
| 3. Wireless / Bluetooth | 4. Audio Connectors |
| 5. USB 2.0 | 6. HDMI |
| 7. USB 3.2 Gen 1 5Gbps Type-A | 8. Optical S/PDIF OUT |