

Key Features

Built for Video Conferencing | Adjustability and Privacy |

Full HD 1080p resolution | Ergonomic Design | Compatible

with Multiple Operating Systems



Product Description

Featuring a built-in 2MP camera, the ViewSonic® VG2440V monitor is perfect for collaboration and video conferencing right from your desktop. The integrated camera captures high-definition video and features 5-degree adjustability so you can find the perfect angle for your video conference. The camera also features a privacy shutter that ensures the camera is on only when you want it to be on. An integrated microphone and speakers round out the full video conferencing capabilities of this monitor. The 24" (23.8" viewable) monitor itself features a Full HD SuperClear® IPS panel for vivid visuals, and a full ergonomic stand for comfort and productivity. Integrated HDMI, DisplayPort and VGA ports make it easy to connect whether you are set up at home or at the office.




01. Menu Controls
02. VESA Compatible Mount 100 x 100mm
03. AC In


04. 3.5mm Audio In
05. 3.5mm Audio Out
06. USB Type A (x2)
07. Kensington® Lock Slot

08. VGA
09. USB Type B
10. USB Type A
11. HDMI 1.4


12. DisplayPort In



24"
DISPLAY



IPS
PANEL



1920 x 1080
RESOLUTION

Contact Sales

call: 888.881.8/81

email: salesinfo@viewsonic.com

visit: viewsonic.com

Display:

Display Size (in.):	24
Viewable Area (in.):	23.8
Panel Type:	IPS
Resolution:	1920 x 1080
Resolution Type:	Full HD (1920x1080)
Static Contrast Ratio:	1,000:1
Dynamic Contrast Ratio:	50,000,000:1
Light Source:	LED
Brightness:	250 cd/m ²
Colors:	16.7M
Color Space Support:	8 bits
Aspect Ratio:	16:9
Response Time (Typical GtG):	5ms
Viewing Angles:	178° horizontal, 178° vertical
Panel Surface:	Anti-glare, Hard coating (3H)

Compatibility:

PC Resolution (max):	1920x1080
Mac® Resolution (max):	1920x1080

Connector:

USB Type A(3), USB Type B(1), 3.5mm Audio In(1), 3.5mm Audio Out(1), VGA(1), HDMI 1.4 In(1), DisplayPort(1)

Audio:

Internal Speakers:	2W (x2)
--------------------	---------

Power:

Eco Mode (Conserve):	10.3W
Eco Mode (Optimized):	11.7W
Consumption (typical):	13.7W
Consumption (max):	16.5W
Voltage:	AC: 100-240V (universal), 50-60Hz
Stand-by:	0.5W
Power Supply:	Internal

Additional Hardware:

Kensington Lock Slot:	1
Webcam:	2MP

Operating Conditions:

Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	20-90%

Video Signal:

Frequency Horizontal:	15 - 90 KHz
Frequency Vertical:	49 - 75 Hz

Video Input:

Digital Sync:	IMDS for HDMI (v1.4), PCI-E for DisplayPort
---------------	---

Ergonomics:

Height Adjust:	130 mm / 5.1 in
Swivel:	60°
Pivot (Right/Left):	90° / 90°
Tilt (Forward/Back):	5° / 40°

Weight (imperial):

Net (lbs):	13.3
Net Without Stand (lbs):	7.9
Gross (lbs):	19.2

Weight (metric):

Net (kg):	6.0
Net Without Stand (kg):	3.6
Gross (kg):	8.7

Dimensions (imperial) (WxHxD):

Packaging (in.):	24.0 x 15.9 x 8.3
Physical (in.):	21.6 x 16.0-21.1 x 8.1
Physical Without Stand (in.):	21.6 x 13.8 x 2.0

Dimensions (metric) (WxHxD):

Packaging (mm):	609.0 x 405.0 x 210.0
Physical (mm):	549.0 x 407.0 - 537.0 x 206.0
Physical Without Stand (mm):	549.0 x 352.0 x 50.0

General:

Regulations: cULVus, FCC-B, ICES003, Energy Star Certified, EPEAT Certified, MX-CeC, Mexico Energy

PACKAGE CONTENTS: VG2440V, Power Cable, HDMI Cable, USB Type B Uplink Cable, 3.5mm Audio Cable, Quick Start Guide

Recycle/Disposal: Please dispose of in accordance with local, state or federal laws.

Warranty: Three-year limited warranty on parts, labor and backlight

UPC: 766907009644

Accessories:

IC13-CMK-001, IC13-DMA-001, VMP10B_KM1U505, V5PI 2380