

ProductSheet
HP Z24f G3 FHD Display (3G828AA)



Exquisitely crafted for every detail

Meticulously crafted to surpass every design standard, the HP Z24f G3 FHD Display is composed of authentic aluminum and delivers an impressive, frameless viewing experience. Bring your ideas to life with remarkable color accuracy in precise Full HD resolution. Refine your work experience and transform your PC into a powerhouse with this 23.8-inch diagonal screen monitor.



Universally consistent colors

Out of the box, you get remarkable color accuracy from screen to screen^[1]. Achieve precise, vibrant detail with 99% sRGB color gamut and Full HD resolution.

Design pushed to the edge

This stunning 23.8-inch diagonal screen monitor is meticulously crafted with a razor thin profile and frameless design. Get ultimate comfort with 4-way ergonomic adjustability.

Always on low blue light

Experience exceptional vibrancy with HP Eye Ease, the always on low blue light filter that reduces blue light exposure with zero impact to true color accuracy.

Featuring

Easily connect multiple monitors

Declutter your desk and connect a series of displays by daisy chaining with a single DisplayPort™ cable.^[5]

All the ports you need

Connect to a Workstation, a PC and additional displays.

Easily mount a Mini

Mount your HPZ2 Mini or HP Desktop Mini directly to the monitor for a clean workspace.^[6]

HP Zero BrightDot Guarantee

Even if just a third of a pixel fails or is stuck in one position, HP will replace the entire display.^[7]

Optional integrated audio

Easily attach the Z Display Conferencing Speaker Bar for stereo quality audio and dual microphones.^[8]

Specifications

Display size (diagonal)	23.8"
Panel technology	IPS
Display size (diagonal)	60.45 cm (23.8")
Aspect ratio	16:9 ^[1]
Native resolution	FHD (1920 x 1080) ^[1]
Resolutions supported	640 x 480; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080
Pixel pitch	0.274 mm
Brightness	300 nits ^[1]
Contrast ratio	1000:1 ^[1]
Response time (typical)	5ms GtG (with overdrive) ^[1]
Minimum dimensions (W x D x H)	53.84 x 3.85 x 31.37 cm (Without stand.)
Minimum dimensions (W x D x H)	21.2 x 1.52 x 12.35 in (Without stand.)
Dimensions With Stand (W x D x H)	53.84 x 19.5 x 48.93 cm
Weight	4.7 kg (With stand.)
Weight	10.4 lb (With stand.)
Display features	Language selection; On-screen controls; Pivot rotation; Anti-glare; Height adjustable
Display Input Type	1 DisplayPort™ 1.2-out; 1 HDMI 1.4; 4 USB-A 3.2 Gen 1; 1 DisplayPort™ 1.2-in
Onscreen controls	Exit; Information; Management; Power control; Input control; Menu control; Brightness+; Image; Color
Display scan frequency (horizontal)	30-75 KHz
Display scan frequency (vertical)	50-60 Hz
Webcam	No integrated camera
Power	100 - 240 VAC 50/60 Hz
Power consumption	58 W (maximum), 26 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% non-condensing
Sustainable impact specifications	Arsenic-free display glass; Low halogen; Mercury-free display backlights; TCO Certified; TCO Certified Edge
Certifications and compliances	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CECP; CEL; cTUVus; EAC; ENERGY STAR®; ErP; FCC; GS Mark; ISO 9241-307; KC/KCC; NOM; PSB; SEPA; TCO Certified; TCO Certified Edge; TUV-S; VCCI; Vietnam MEPS; WEEE; ISC; Low blue light; Ukraine Energy label; WW application; UAE
Physical security	Security lock-ready ^[2]
Management software	HP Display Center
UPC number	(A2K) 195122290863; (A2N) 195122290887; (AB0) 195122290894; (AB1) 195122290900; (AB2) 195122290917; (AB4) 195122290924; (ABA) 195122290931; (ABB) 195122290948; (ABG) 195122290955; (ABT) 195122290962; (ABU) 195122290979; (ABV) 195122290986; (ABY) 195122290993; (ACJ) 195122291006; (ACQ) 195122291013; (AKL) 195122291037; (AR6) 195122291044; (UUF) 195122291051; (UUZ) 195122291068
What's in the box	Monitor; Documentation; VESA Mount adapter; USB Type-A to B cable; Cable manager; AC power cord; DisplayPort™ 1.4 cable ^[4]

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[5] Requires an additional DisplayPort™ cable to daisy chain.

[6] Z2 Mini and Desktop mini and B550 Z Display G3 PC Mounting Bracket sold separately.

[7] The HP Pixel Policy allows no bright sub-pixel defects for this display. For complete details, see <http://support.hp.com/us-en/document/c00288895>.

[8] Z Display Conferencing Speaker Bar Sold Separately.

Technical Specifications Footnotes

[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[2] Lock sold separately.

[4] Included cables may vary by country.

© Copyright 2020 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

USB-C® is a registered trademark of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Missing Mac (Apple) ENERGY STAR. For trademark comments, see: <https://legal.int.hp.com/legal/pages/tradeack.aspx>.

