



SPECIFICATIONS

Panel Size	27" (69cm)
Panel Resolution	2560 x 1440 (WQHD)
Refresh Rate	165Hz
Response time	1ms GTG
DYNAMIC REFRESH RATE TECHNOLOGY	G-sync Compatible
ACTIVATED RANGE	48 to 165Hz
Panel Type	Rapid IPS
Brightness (nits)	300 nits
Viewing Angle	178° (H) / 178° (V)
Aspect Ratio	16:9
Contrast Ratio	1000:1
DCR	100000000:1
Pixel Pitch (H x V)	0.2331(H) x 0.2331(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
DCI-P3 / sRGB	93% / 125%
Video ports	1x Display Port (1.2) 2x HDMI (2.0)
Audio ports	1x Earphone out
Active Display Area (mm)	596.736(H) x 335.664(V)
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Control	5-way OSD navigation joystick
Power Type	External Adaptor 19V 3.42A
Power Input	100~240V, 50~60Hz
Signal Frequency	90.9 to 242.4KHz (H) 30 to 165Hz (V)
Adjustment (Tilt)	-5° ~ 20°
Power consumption	32W
Carton Dimension (W X H X D)	745 x 490 x 225 mm / 29.33 x 19.29 x 8.86 inch
Dimension (W x H x D)	614.9 x 444.6 x 228.38 mm / 24.21 x 17.50 x 8.99 inch
Weight (NW / GW)	4.5kg / 7.5kg 9.92lbs / 16.53lbs
Frameless Design	Yes

FEATURES



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Ultra Slim

The slimmest portable monitor in world. This design allows you easily bring it everywhere.



165Hz High Refresh Rate

Experience smooth gaming with a blazing fast 165Hz refresh rate, that gives you the upperhand in fast moving games



Night Vision

See every detail clearly in the dark, helping you find and attack enemies before they notice.



Provides 1ms GTG fast response time, optimizes screen colors and brightness.



WQHD High Resolution

Game titles will even look better, displaying more details due to the WQHD resolution.



Note

Display Port: 2560 x 1440 (Up to 165Hz)
HDMI: 2560 x 1440 (Up to 144Hz)
The color gamut follows the CIE 1976 testing standard.

CONNECTIONS



1. 5-way joystick navigator
2. 1x Display Port (1.2)
3. 2x HDMI (2.0b)
4. Earphone out
5. DC jack
6. Kensington lock