

VL644T

3.6mm fixed lens, black housing

2
MP

Features

- Full HD resolution over coax
- Easy installation & adjustment
- Compact & lightweight 3 axis design
- Manual 360° rotation & pan/tilt mechanism
- 12VDC power supply required (power supply not included)
- 5 year warranty



Camera Specifications

Image Sensor	1/2.7" 2MP CMOS Sensor
Resolution	1920x1080
Minimum Illumination	0.01 lux @ F=0.12
Electronic Shutter	Auto
S/N Ratio	>60dB
Backlight Compensation	Auto
Synchronization	Internal
Gamma	0.45 typ.
Video Signal Output	1.0Vp-p / 75 ohms
Operating Temperature/ Humidity	14°F - 122°F / less than 80% RH
Storage Temperature	-4°F - 140°F
Power Consumption	90mA
Power Supply	12VDC (power supply not included)
Dimensions	4.7" (H) x 3.5" (Dia.)
Weight	10.5 oz.

Optional Accessories



PSW5
12VDC
Power Supply



TVIUTPPT
HD Video
Transceiver with
Pigtail (Balun)



TVIUPT
HD Video
Transceiver