4XEM
Problem solved.

4XEM's USB 3.0 Universal Docking Station B

4XEM Part- 4XUG39DK4

     Streamline your workspace with our USB 3.0 Slim Universal Docking Station. This sleek and compact device is packed with features, including built-in audio (Mic in and Line out), DVI-I, HDMI, VGA, built-in USB3.0 Gigabit Ethernet Adapter, 2 x USB3.0 ports, and 4 x USB2.0 ports.

     Connect all your devices and peripherals in one place, and easily switch between your laptop and desktop, while still having access to all your peripherals. The built-in USB3.0 Gigabit Ethernet Adapter ensures stable internet connection, while the audio ports provide enhanced audio quality.

     The slim and compact design makes it easy to take on the go, making it perfect for on-the-go professionals and travelers. Optimize your workflow and elevate your travel experience with our USB 3.0 Slim Universal Docking Station - the ultimate in portability and connectivity.

4XEM Products Are Available At Your Favorite Online Retailers

WWW.4XEM.COM

Contact Todd Schaus 4XEM sales Rep
1-866-999-4936 Ext.104   tschaus@4xem.com

Features

- USB 3.1 Gen 1 Host Connector – Detachable
- 1x HDMI 1.1 port
- 1x DVI-SL (Single Link) port
- 1x USB Type-A (5 Gbps - Fast Charging)
- 1x USB Type-A (5 Gbps)
- 4x USB Type-A (480 Mbps)
- 1x RJ-45 (10/100/1000 Mbps)
- 1x 3-pole TRS 3.5mm Phono Jack – Audio In
- 1x 3-pole TRS 3.5mm Phono Jack – Audio Out
- AC Adapter Included

Application

- Home theatre
- Small business
- Home Office
- Business Presentations

4XEM Products Are Available At Your Favorite Online Retailers

Warranty Information	Warranty	2 Years
Features/Hardware	4K Support	No
	Displays Supported	2
	USB Ports	6
	Fast-Charge Port(s)	Yes
	Network	Yes
	SD Card Reader	No
	Audio	Yes
	Power Delivery	No
	Lock Slot	No
	Industry Standards	HDMI 1.1
		DVI-I SL
		HDCP 1.4
		Battery Charging (BC 1.2)
	Chipset ID	DisplayLink - DL3900
		VIA - VL82B2
		FE1.1S
Connector(s)	Host Bus Type	USB 3.1 Gen 1 (5Gbps)
	Host Connector	USB Type-B (SuperSpeed)
	Host Connector Cable	Detatchable
	Connector Type(s)	1x HDMI 1.1 (4.95Gbps)
		1x DVI-I SL (4.95Gbps)
		1x USB Type-A (5Gbps - Fast Charging)
		1x USB Type-A (5Gbps)
		4x USB Type-A (480Mbps)
		1x RJ-45 (10/100/1000Mbps)
		1x 3-pole TRS 3.5mm Phono Jack - Audio In
		1x 3-pole TRS 3.5mm Phono Jack - Audio Out
Performance	Maximum Digital Resolutions	2048 x 1152 @ 60Hz
	Maximum Analog Resolutions	2048 x 1152 @ 60Hz (Analog via DVI->VGA Adaptor)
	Audio Specification	2-ch Stereo
Software	OS Compatibility	Windows Vista, 7, 8, 8.1, 10
		Mac OS 10.2 or Later
		Linux
Power	Power Source	Included AC Adaptor (100-240VAC, 50/60Hz, 0.1A Max , CLASS Ⅱ)
	Power Adaptor Style	Wall Wart
	Power Consumption	24W
	Input Voltage	12V DC @ 2A
	Power Delivery	N/A
Physical Characteristics	Colour	Black
	Shell Material	ABS Plastic
	Host Cable Length	2.33 ft [0.71 m]
	Buttons/Switches	None
	LED Indicators	Power: Blue
	Power Cable Length	3.83 ft [1.17 m]
	Product Height	1.3 in [33.0 mm]
	Product Width	8.82 in [224 mm]
	Product Length	3.43 in [87.0 mm]
	Weight of Product	9.67 oz [274 g]
Environmental	Operating Temperature	32°F to 104°F [0°C to 40°C] @ 10%-90% RH (Non-Condnesing)
	Storage Temperature	14°F to 158°F [-10°C to 70°C] @ 10%-90% RH (Non-Condnesing)
Packaging Information	Shipping (Package) Weight	1.46 lbs [0.66 kg]
	Package Height	2.44 in [62 mm]
	Package Width	13.62 in [346 mm]
	Package Length	6.02 in [153 mm]
What's in the Box	Included in Package	1x USB 3.0 Universal Docking Station
		1x USB 3.0 Type-B to Type-A Cable
		1x DVI to VGA Adaptor
		1x 12V/2A Power Adaptor
		1x Quick Start Guide
Notes / Special Requirements	Notes	HDCP not supported on Mac OS or Linux

* Product appearance and specifications are subject to change without notice.

* Same day shipping is only available for orders shipping within the United States.