



4XEM Thunderbolt 3 4K Display Universal Docking Station

4XEM Part- 4XUTD01H



Introducing the ultimate solution for high-speed connectivity and multi-tasking – the Thunderbolt 3 4K DisplayPort Universal Multi Port Docking Station. With its powerful 40 Gbps Thunderbolt 3 host connector and 1x DisplayPort 1.2 port, this docking station provides lightning-fast data transfer speeds and supports resolutions up to 4K.

The Thunderbolt 3 4K DisplayPort Universal Multi Port Docking Station boasts an impressive array of ports that make it a one-stop-shop for all your connectivity needs. With 1x Thunderbolt 3 port, 4x USB 3.0 Type-A ports, 1x SD card reader SD 3.0, 1x micro SD card reader 3.0, 1x RJ45 Gigabit port, and 1x 4-pole mic/audio port, you can easily connect multiple devices at once, making it the perfect solution for anyone who needs to work more efficiently.

Crafted from sleek and durable materials, the Thunderbolt 3 4K DisplayPort Universal Multi Port Docking Station is engineered to deliver unparalleled performance, perfect for creative professionals, gamers, and anyone seeking a superior user experience. The docking station's multiple ports allow you to connect multiple devices, including displays, hard drives, and more, without the need for additional cables or adapters.

4XEM Products Are Available At Your Favorite Online Retailers

WWW.4XEM.COM

Contact Todd Schaus 4XEM sales Rep 1-866-999-4936 Ext.104 tschaus@4xem.com





DATA SHEET

Features

- Powerful 40 Gbps Thunderbolt 3 host connector
- 85W Upstream (to Host) Power Delivery and 95W Downstream (to peripheral) Power Delivery
- 1x DisplayPort 1.2 port with support for 4K resolution
- 1x Thunderbolt 3 port (40 Gbps DP Alt Mode USB Mode: Max 10 Gbps)
- 4x USB 3.0 Type-A ports for 5 Gbps data transfer
- 1x SD card reader SD 3.0
- 1x micro SD card reader 3.0
- 1x RJ45 Gigabit port for reliable network connectivity
- 1x 4-pole mic/audio port for connecting headphones or a microphone

Benefits

- Lightning-fast data transfer speeds with Thunderbolt 3 technology
- Connect up to two 4K displays for a high-quality visual experience
- Multi-port connectivity with 4x USB 3.0 Type-A ports and 2x card readers for added convenience and productivity
- Plug-and-play design for easy setup and use
- Durable and sleek design for long-lasting performance
- Perfect for creative professionals, gamers, and anyone who needs to connect multiple devices for work or entertainment
- Single docking station eliminates the need for additional cables or adapters
- Simplifies and declutters your workspace for increased productivity and a better user experience
- Provides reliable network connectivity with the RJ45 Gigabit port
- High-quality audio output and input with the 4-pole mic/audio port

Application

- Home theatre
- Small business
- · Multi-Screen Display
- · Business Presentations

4XEM Products Are Available At Your Favorite Online Retailers

WWW.4XEM.COM

Contact Todd Schaus 4XEM sales Rep 1-866-999-4936 Ext.104 tschaus@4xem.com





DATA SHEET

Warranty Information Warranty 2 Years

Yes Features/Hardware 4K Support Displays Supported

USB Ports 4 Fast-Charge Port(s) No Yes Network SD Card Reader Yes Audio

85W Upstream + 95W Downstream Power Delivery Kensington Standard Slot (K-Slot) Lock Slot Industry Standards DisplayPort 1.2 (HBR2)

HDMI 2.0

HDCP (Version depends on host GPU) Power Delivery (PD3.0)

Secure Digital (SD v3.01) Alpine Ridge - JHL6540 Chipset ID Texas Instruments - TPS65983

Fresco Logic - FL1100 Fresco Logic - FL5000 Realtek - RTL8153 Genesys Logic - GL3224 Realtek - ALC4040

Connector(s) Host Bus Type Thunderbolt 3 (40Gbps) USB Type-C Host Connector

Host Connector Cable Detachable

1 x DisplayPort 1.2 (HBR2: 5.4Gbps x4) Connector Type(s)/Rate(s)

1 x Thunderbolt 3 (40Gbps - DP Alt Mode - USB Mode: Max 10Gbps)

4 x USB Type-A (5Gbps) 1 x SD Card Reader Slot (104 MB/s) 1 x Micro SD Card Reader Slot (104 MB/s)

1 x RJ45 (10/100/1000Mbps)

1 x 4-Pole TRRS 3.5mm Phono Jack (Stereo/Mic Combo)

Single Monitor: 5K (5120 x 2880 @ 60Hz) Maximum Digital Resolutions Performance Dual Monitors: 4K UHD (3840 x 2160 @ 60Hz) each

Audio Specifications Up to 8-ch via DP/HDMI

2-ch Stereo via 3.5mm Phono Jack

Software OS Compatibility Microsoft Windows 10 Apple Mac OS X

Power Power Source AC Adapter Included (100-240VAC, 50/60Hz, 3A Max, CLASS II)

Brick 180W Power Adapter Style Power Consumption 20V DC @ 9A Input Voltage

Power Delivery 85W Upstream (to Host device) 95W Downstream (to Peripheral)

Physical Characteristics Color

Shell Material ABS Plastic 24.02 in [610 mm] Power Button Host Cable Length **Buttons/Switches** Power: Blue LED Indicators AC In: 4.58 ft [1.40 m] DC Out: 3.83 ft [1.17 m] Power Cable Length

1.10 in [28.0 mm] Product Height Product Width 8.27 in [210 mm] Product Length 3.27 in [83.0 mm] 12.35 oz [350 q] Weight of Product

Environmental Operating Temperature 32°F to 104°F [0°C to 40°C] @ 10%-90% RH (Non-Condnesing)

14°F to 158°F [-10°C to 70°C] @ 10%-90% RH (Non-Condnesing) Storage Temperature

Packaging Information Package Type 4.02 in [102.0 mm] 10.55 in [268 mm] Package Height

Package Width 5.35 in [136 mm] Package Length Shipping (Package) Weight 3.26 lbs [1.48 kg]

1 x Thunderbolt™ 3 Universal Docking Station Included in Package 1 x Thunderbolt™ 3 40Gbps cable 0.6 meter

1 x Quick Start Guide

1 x Active DP1.2 to HDMI2.0 Adapter 1 x DC20V/9A 180W Power Adapter 1x NEMA 5-15P to IEC 320 C13 Power Cable

To display 5K resolution, both DP & TB3 connection are required. Notes / Special Requirements Notes



What's in the Box

^{*} Product appearance and specifications are subject to change without notice.

^{*} Same day shipping is only available for orders shipping within the United States.