

Features

- Simple Installation
Easy to install with a joint mount
- Anti-interference Performance
In order to reduce less signal interference , the innovative spread spec trum technology makes the transmission stable
- Non-Setting
Innovative IP function, easiest way to setup a wireless link by switching buttons
- Thunderproof and Windproof
The streamlined body design can protect the AP from strong wind and storm



Specification

Model	GX-WAP3008
Output Power	27dBm
Transmission Speed	300Mbps
Chipset	AR9344
Operating Frequency	5180~5240MHz/5745~5825MHz
Polarization	Vertical, Horizontal
Memory	DDR264M
Antenna Gain	16dBi
Ethernet Port	10/100Mbps
Standard	IEEE802.11a, IEEE802.11n, IEEE802.3u
Operating Temperature	-40~70°C
Power Supply	PoE 24V 1A
Dial Switch	YES