




Features

Material	Aluminum & SUS304
Dimension(WxHxD)	125.6mmx114mmx20mm (4.94"x4.49"x0.79")
Mast Diameter	Dia.80~150mm(Dia.3.15"~5.91")
Pipe Thread	N/A
Operating Temperature	-40°C~+60°C (-40°F~+140°F)
Humidity	<90% RH
Load Bearing	3.0kg(6.61lb)
Weight	0.27kg(0.6lb)
Color	White