


ProductSheet
t430ThinClientBundle (282A1AA)



The versatile cloud-first device that's intuitive for IT admins and users

Optimized for desktop virtualization and cloud-based applications, the intuitive HP t430 Thin Client is easy for end users to understand and simple for IT administrators to maintain.



Refined from the inside out

Everything from the user interface to the compact design and processing power delivers a modern computing experience.

Better connected

Although small in size, the HP t430 Thin Client is full of possibilities with USB-C™ for power and transfer of audio and data, a variety of video outputs, and Ethernet and Wi-Fi[1] connections.

Administration made easy

Simplify the complexity of setting up a virtual desktop or cloud device with a thin client pre-configured with your choice of the Linux®-based HP ThinPro or Windows 10 IoT Enterprise operating system and HP manageability software.

Featuring

New, user-friendly experience

Whether you choose the Linux®-based HP ThinPro or Windows 10 IoT option, users will get an intuitive, natural interface and familiar navigation.

Nimble design to blend in or stand out

Designed with a sleeker profile and built-in VESA mount, the HP t430 Thin Client can be mounted on the back of a display or placed discreetly on or under a desk or in a kiosk. [2]

Plenty of power and high-definition graphics

Get more than enough performance for all your tasks with the latest-generation Intel® Celeron® processor with speeds up to 2.8 GHz, DDR4 memory, solid-state storage, and support for a 4K display. [3]

Powerful connections that do more

Connect instantly with Citrix®, VMware®, Microsoft® RDP, and default web browsers right out of the box. Communicate and collaborate with support for Skype for Business® and Cisco VXME.

Provide flexibility with a full range of connectivity

Add your devices and displays and connect to your network with input/output ports that include USB-C™, DisplayPort™, HDMI, and LAN or optional Wi-Fi[1] with integrated adapters and antennas. [1]

Specifications

Operating system	Windows 10 IoT Enterprise for Thin Clients
Memory	4 GB DDR4-1600 MHz RAM (onboard)
Internal Storage	64 GB eMMC
Audio	Headphone/microphone mini-jack
Minimum dimensions (W x D x H)	13.5 x 13.5 x 3.2 cm
Minimum dimensions (W x D x H)	5.3 x 5.3 x 1.3 in
Weight	0.74 kg (Weight will vary depending on configuration.)
Weight	1.63 lb (Weight will vary depending on configuration.)
Keyboard	HP USB Slim Business Keyboard
Pointing device	HP USB wired mouse
Ports	1 headset connector; 1 USB 3.1 Gen 1; 1 USB Type-C™ (DisplayPort™ 1.2, USB 3.1, charging)
Ports	1 DisplayPort™; 1 RJ-45; 2 USB 3.1 Gen 1; 1 HDMI port
Protocols	Citrix® HDX; Citrix® ICA; Microsoft RDP; Microsoft RFX; VMware Horizon® View™ through RDP/PCoIP, and Blast Extreme
Power	45 W, worldwide auto-sensing, 100-240 VAC, 50-60 Hz, energy saving automatic power-down, surge tolerant external adapter
Ecolabels	EPEAT® registered
Energy star certified	ENERGY STAR® certified
Sustainable impact specifications	Low halogen
Software included	HP Device Manager; HP Easy Shell; HP Smart Zero Client Services; HP ThinState; HP ThinUpdate ^[8]
Browser supported	Internet Explorer 11 (for models with Windows IoT Enterprise for Thin Clients); Mozilla Firefox 32
UPC number	(A2K) 195161090318; (A2N) 195161092664; (A2Q) 196188750599; (AB0) 195161090325; (AB1) 195161090332; (AB2) 195161090370; (AB4) 195161090363; (AB5) 195161090394; (AB6) 195161092657; (AB7) 195161092688; (AB8) 195161092671; (AB9) 195161089954; (ABA) 195161092619; (ABB) 195161091414; (ABC) 195161092626; (ABD) 195161089978; (ABE) 195161089985; (ABF) 195161090011; (ABG) 195161089466; (ABH) 195161090028; (ABJ) 4580511789718; (ABM) 195161092633; (ABN) 195161090042; (ABT) 195161090035; (ABU) 195161090073; (ABV) 195161090080; (ABY) 195161090103; (ABZ) 195161090127; (AC4) 195161092640; (ACB) 195161090158; (ACF) 4580511789725; (ACJ) 195161089497; (ACQ) 195161090165; (AK8) 195161090196; (AKC) 195161090189; (AKL) 195161089480; (AKS) 195161090233; (AR6) 195161089510; (BCM) 195161090219; (UUG) 195161090240; (UUZ) 195161090288
Manufacturer Warranty	3 year (3-3-0) limited warranty and service offering includes 3 year of unit exchange with no on-site repair. Terms and conditions vary by country. Certain restrictions and exclusions apply.

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] All wireless options are sold separately or as optional features. For all 802.11 wireless, wireless access point and Internet service is required and is not included. Availability of public wireless access points is limited.

[2] Display and mounting hardware sold separately.

[3] Sold as a configurable option.

Technical Specifications Footnotes

[8] HP ThinUpdate available as an add-on only for configurations using Windows Embedded operating systems.

Learn more at
hp.com

Copyright © 2018 HP Development Company, L.P. The only warranties for HP products are set forth in the express limited warranty statements accompanying such products. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR® and the ENERGY STAR® mark are registered trademarks of the U.S. Environmental Protection Agency. Bluetooth is a trademark of its proprietor used by HP Inc. under license. Microsoft and Windows are U.S. trademarks of the Microsoft group of companies. AMD is a trademark of Advanced Micro Devices, Inc. Citrix® is a registered trademark of Citrix Systems, Inc. and/or one more of its subsidiaries, and may be registered in the United States Patent and Trademark Office and in other countries.

