


# ASUS E410

Move with style



## Move with style

Life is all about finding the right balance, and the ASUS E410 laptop delivers just that. Lightweight and compact, it fits right in with your dynamic, on-the-go lifestyle. Its lid is available in Dreamy White, Peacock Blue, Rose Gold and features the unique ASUS motif, and these aesthetics are further complemented by a color-blocked Enter key with yellow edges and text. Designed for daily computing and productivity tasks, and boasting innovative features such as ASUS NumberPad, an all-day battery and 180° lay-flat hinge, ASUS E410 gives you everything you need for work or play.




Powered by Intel® Pentium® Processor.

Learn more at: <https://www.asus.com/Laptops/ASUS-Laptop-E410MA/>

starting at \$ xxxxxxxx

\* Specification may vary by model.



## See the difference

ASUS E410 has a youthful vibe that sets it apart. The lid is detailed with modern slashes that are accompanied by a unique motif made up of a deconstructed ASUS badge. The bold look continues inside, where a bright yellow Enterkey takes center stage. It's something never seen before in laptop design.

## Get it done, anywhere

With the compact and lightweight ASUS E410, productivity is always within reach. It easily slips into your backpack or small bag so you can get schoolwork done or create content wherever you are.

1.3kg  
light



## Go for your goals

With Windows 10 Home, up to a quad-core Intel processor, and up to a 512GB PCIe SSD, ASUS E410 is well-equipped to help you achieve your goals. With ASUS E410, you can leave the heavy power adaptor at home. Its 12hrs battery life gives you the flexibility to work or play anywhere.

## Enhanced productivity

The new ASUS NumberPad makes number-crunching a whole lot easier. Everything you need from a physical keypad is printed on the touchpad, simply tap the icon to turn it on. A cleverly designed 180° lay-flat hinge makes it easy to share content or collaborate with friends. The fanless design keeps noise levels down, so you won't be distracted when working on a spreadsheet or watching a movie.

## ASUS E410

- Windows 10 Pro / Home
- Unique **ASUS motif** and **yellow color-blocking Enter Key** design
- Available in **three stylish colors** : Peacock Blue, Dreamy White, Rose Gold
- Compact and lightweight **1.3kg** chassis
- Up to Intel® Pentium® Silver N5030 Processor
- Up to **8GB 2400MHz RAM** and **512GB PCIe SSD** storage
- Innovative **NumberPad** for enhanced productivity
- Up to **12hrs** battery life
- **180-degree lay-flat hinge** for idea sharing
- **NanoEdge display** with **78% screen-to-body ratio**
- 1.4mm key travel with optional **backlit keyboard**
- Quiet **fanless design**
- MyASUS software for useful ASUS apps
- 1 x USB 3.1 Gen1 Type-C / 1 x USB 3.1 Gen1 Type-A / 1 x USB 2.0 / 1 x HDMI / 1 x Audio jack combo / 1 x MicroSD Card reader
- 325.4 x 217.4 x 18.45 mm
- 3-year global warranty

\* Product weight may vary according to device configuration.

\* Please note that all versions of NumberPad only work with the Microsoft Windows operating system.

\* Battery life test configuration: Intel® Celeron® N4000, 4GB RAM, FHD display, 64GB eMMC, 42Whr. Battery tests conducted by ASUS in January 2020 using the MobileMark® 2014 Office Productivity scenario. Test settings: Wi-Fi enabled, display brightness set to 150nits. Actual battery life may vary depending on product configuration, usage, operational conditions and power management settings. Battery life will decrease over the lifetime of the battery.

## ASUS Laptop



## E410

CPU	Intel® Pentium® Silver N5030 Processor (4MB cache, up to 3.10GHz) Intel® Pentium® Silver N5000 Processor (4MB cache, up to 2.70GHz) Intel® Celeron® Processor N4020 (4MB cache, up to 2.80GHz)
Operating System	Windows 10 Home Windows 10 S mode Windows 10 Pro (ASUS recommends Windows 10 Pro)
On Board Memory	DDR4 2400MHz 4GB / 8GB
Memory Slot	NA
Memory Max.	DDR4 2400MHz 8GB
Storage	PCIe SSD : 128GB, 256GB, 512GB
EMMC / ISSD	EMMC : 64GB, 128GB
Display	14", HD 1366x768 / FHD 1920x1080, NanoEdge display, 6.5mm thin bezel, 78% screen to body ratio, IPS-level (optional), Anti-Glare
External Video Display Modes	NA
Discrete GPU	NA
Integrated GPU	Intel UHD Graphics 605 / 600
Video Memory	NA
FingerPrint	NA
Wireless	Intel Wi-Fi 5 (802.11ac, 1x1/ 2x2) Bluetooth 4.2
Card Reader	Type : MicroSD
Interface	1 x USB 3.1 Type-C (Gen1) / 1 x USB 3.1 Type-A (Gen1) / 1 x USB 2.0 1x HDMI / 1 x Headphone-out & Audio-in / 1 x microSD card reader
Audio	Built-in speaker Built-in microphone with Cortana ASUS SonicMaster stereo audio system
Camera	VGA camera
Weight (kg)	1.3kg
Dimension (cm)	32.54 (W) x 21.74 (D) x1.845 (H) cm
AC Adapter	33W AC Adapter : Output : 19V DC, 1.75A Input : 100~240V AC, 50/60Hz universal
Battery	42Wh 3-cell lithium-polymer battery
Touchpad	NumberPad
Keyboard Type	Illuminated Chiclet Keyboard (optional)
Security	BIOS Booting User Password Protection Firmware TPM (fTPM)
Warranty	
Price	