


DATA SHEET

ICRP-HD-QR-N, ICRP-HD-QR-W

ICOMPEL® FULL HD SINGLE-ZONE MEDIA PLAYER— 32 GB

24/7 TECHNICAL SUPPORT AT 877.877.2269 OR VISIT BLACKBOX.COM



OVERVIEW

ICOMPEL DIGITAL SIGNAGE FULL HD SINGLE-ZONE MEDIA PLAYER, 32 GB (OPTIONAL WI-FI) DATA SHEET

INTRODUCTION

The iCompel® Digital Signage Full HD Single-zone Media Player, 32 GB is an ultra slim, single-zone player designed specifically for the retail industry. It is ideal for cost-sensitive or space-restricted applications.

Two models are available:

- ICRP-HD-QR-N: iCompel Digital Signage Full HD Single-zone Media Player, 32 GB
- ICRP-HD-QR-W: iCompel Digital Signage Full HD Single-zone Media Player, 32 GB, Wi-Fi Enabled

FEATURES

- SUPPORTS RESOLUTIONS OF 1920 X 1080 P60 H.265 VIDEO
- SLIM PROFILE FOR BACK OF SCREEN MOUNTING
- HD STREAM-IN, DUAL-BAND WI-FI AND TOUCH OPTIONS
- INTEL CELERON PROCESSOR
- VIDEO, HTML5, IMAGES, TEXT AND AUDIO
- USE AS STANDALONE OR AS A SUBSCRIBER UNIT

COMPARISON CHART

MODEL OPTIONS		
	ICRP-HD-QR-N	ICRP-HD-QR-W
WI-FI	NO	YES
ZONES	1	1
MAX. VIDEO ZONES	1	1
ROLE	PLAYER	PLAYER WITH WI-FI

ORDERING INFORMATION

ITEM	CODE
iCompel® Digital Signage Full HD Single-zone Media Player, 32 GB	
No Wi-Fi	ICRP-HD-QR-N
Wi-Fi Enabled	ICRP-HD-QR-W

DISCLAIMER

Black Box Corporation shall not be liable for damages of any kind, including, but not limited to, punitive, consequential or cost of cover damages, resulting from any errors in the product information or specifications set forth in this document and Black Box Corporation may revise this document at any time without notice.



SPECIFICATIONS

ICOMPEL DIGITAL SIGNAGE FULL HD SINGLE-ZONE MEDIA PLAYER, 32 GB (OPTIONAL WI-FI) DATA SHEET

SPECIFICATIONS FOR ICOMPEL DIGITAL SIGNAGE FULL HD SINGLE-ZONE MEDIA PLAYER, 32 GB (ICRP-HD-QR-N AND ICRP-HD-QR-W)	
MEMORY	
PROCESSOR	Intel Celeron
RAM	4 GB
DISC	32 GB Solid State Drive (SSD)
AUDIO/VIDEO CONNECTORS	
VIDEO	HDMI, VGA (DVI-I with adapters)
AUDIO	3.5 mm stereo mini-jack socket and HDMI
MEDIA	
VIDEO	H.265, MPEG-1, MPEG-2, MPEG-4 (ASP and AVC), QuickTime®, WMV 9, video cropping
ANIMATION	HTML (with JavaScript), HTML cropping and zoom, HTML
IMAGES	JPEG, TIFF, GIF, PNG, BMP
AUDIO	MPEG-1 (layers 1, 2, and 3), MPEG-2 (AAC), MPEG-4 (AAC), AC3, MP3, WAV
TEXT	Multiple fonts, speeds, colors, and directions. RSS newsfeeds.
CLOCKS	Digital (multilingual and localizable date and time formats)
SOURCE	
INTERNET	HTML (web pages), RSS feeds (with multilingual support), XML files
VIDEO IN	Optional IP video stream-in license, MPEG/UDP
NETWORK	
ETHERNET	10/100/1000BASE-T (RJ-45)
WIRELESS	Optional internal PCIe card supporting 802.11 a, b, g, and n (2.4 and 5 GHz)
PORTS	
USB	(2) USB 3.0
RS-232	Optional USB to RS-232 adapter
PHYSICAL	
DIMENSIONS	0.9" H x 6.6" W x 5.9" D (2.4 x 16.8 x 14.9 cm)
WEIGHT	2.471 lb. (1.123 kg) (including PSU and cable)
POWER	24.5 W (typical consumption) supplied by 65 W external 19 V DC PSU
TEMPERATURE	32 to 104° F (0 to 40° C)
COOLING	Active (fanned)
MOUNTING	Optional screen mounting plate