

# Lenovo L24e-30 66BCKCC2US

**Product**  
Lenovo L24e-30

**Machine Type**  
66BC

**Region**  
NA

**Display Size**  
23.8"

**View Area**  
527.04x296.46 mm

**Panel**  
VA

**Aspect Ratio**  
16:9

**Resolution**  
1920x1080

**Pixel Pitch**  
0.2745x0.2745 mm

**Dot / Pixel Per Inch**  
93 dpi

**View Angle (H / V)**  
178 / 178

**Pixel Response Time**  
4 ms (Extreme mode) / 6 ms (Typical mode)

**Color Support**  
16.7 Million

**Refresh Rate**  
75 Hz (Only for HDMI input)

**Brightness**  
250 nits

**Contrast Ratio**  
3000:1

**Color Gamut**  
72% NTSC

**Curvature**  
None

**Anti-glare**  
Yes

**Video Connector**  
HDMI, VGA

**USB Port**  
None

**Camera**  
None

**Microphone**  
None

**Speakers**  
None

## Power Consumption (Typical / Maximum)

17.5W / 23.5W

## Power Adapter

Integrated

## Stand

Tilt Stand

## Color

Raven Black

## Side Bezel Width

2.5 mm

## Dimensions with Stand (HxWxD)

434.9x540.4x165.0 mm / 17.12x21.28x6.5 inches

## Weight (Including Stand)

3.82 kg / 8.42 lbs.

## Cables Included

HDMI cable

## Environmental Certification

RoHS

## Ergonomic Certification

TÜV Rheinland Eye Comfort

## Base Warranty

1-year

## Operating System Support

Support Windows 7, Windows 10

## Sync Technology

AMD FreeSync

## Tiny Support / CPU / Platform

Tiny Support, Nano Support / None / None

## Ethernet / Bluetooth / Wireless

None / None / None

## Touch Screen / Digitizer Pen / Battery

None / None / None

## Display Ram / Storage / Card Slot

None / None / None

## EAN / UPC / JAN

0195348151740 / 195348151740 / None

## Announce Date

2020-01-14

## Notes:

### California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:  
<https://www.calrecycle.ca.gov/Electronics/Consumer>



[WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.  
© Lenovo, 2022. All rights reserved.



# Lenovo L24e-30

## DISPLAY

### Panel Size

23.8-inch

### Screen Dimensions

531.73 mm x 340.80 mm

### Active Area

527.04 mm x 296.46 mm

### Panel Type

3-side NearEdgeless, VA

### Backlight

WLED

### Aspect Ratio

16:9

### Resolution

1920 x 1080

### Pixel Pitch

0.2745 x 0.2745 mm

### Dot/Pixel Per Inch (DPI/PPI)

93

### Viewing Angle (H x V @ CR 10:1)

178° / 178°

### Response Time

4ms (Extreme Mode)

6ms (Normal Mode)

### Refresh Rate

75 Hz<sup>2</sup>

### Brightness (typical)

250 cd/m<sup>2</sup>

### Contrast Ratio (typical)

3000:1

### Dynamic Contrast Ratio (typical)

3M:1

## Color Gamut

72% NTSC (CIE 1931)

## Color Support (typical)

16.7 Million

## Anti-Glare

Yes

## CONNECTIVITY

### Video Signal

1 x HDMI 1.4

1 x VGA

### Audio Signal

1 x Audio Out (3.5 mm)

## MULTI-MEDIA

### Optional Soundbar Support

Yes (PN number: OA36190)

## SPECIAL FEATURES

### Sync Technology

AMD FreeSync™<sup>1</sup>

### Software

Yes<sup>3</sup> (Lenovo Artery,  
Lenovo Display Control Center)

## POWER

### Power Consumption (typical/max)

17.5W / 23.5W

### Power Consumption Sleep/Off Mode

< 0.5W

### Power Consumption Switch-off Mode

< 0.3W

### Power Supply

Internal

### Voltage Required

AC 100 to 240 V (50–60 Hz)

## MECHANICAL

### Tilt Angle (front/back)

-5° / 22°

### VESA Mount Capability

Yes (100 x 100 mm)

### ThinkCentre M Series Tiny support

Yes, by Tiny/Nano monitor clamp II (PN: 4XHOZ42451) & Tiny VESA mount II (PN: 4XFONO3161)

### ThinkCentre M Series Nano support

Yes, by Tiny/Nano monitor clamp II (PN: 4XHOZ42451) & Nano VESA mount (PN: 4XFOV81630)

### Kensington Lock Slot

Yes

### Cable Management

Yes

### Bezel Color

Raven Black

### Bezel Width (side)

2.5 mm

### Bezel Width (top/bottom)

2.5 mm / 22.4 mm

## DIMENSIONS

### Size Packed (D x H x W, mm/inch)

624.0 x 124.0 x 415.0 mm

24.57 X 4.88 X16.34 inches

### Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)

165.0 x 434.9 x 540.4 mm

6.50 x 17.10 x 21.28 inches

### Size Unpacked w/ Stand (D x H x W, mm/inch) (Highest position)

165.0 x 434.9 x 540.4 mm

6.50 x 17.10 x 21.28 inches

### Size Unpacked w/o stand (Head Only) (D x H x W)(mm/inch)

45.5 x 327.2 x 540.4 mm

1.79 x 12.88 x 21.28 inches

### Weight Packed (kg/lbs.)

5.42 kg / 11.95 lbs.

### Weight Unpacked (kg/lbs.)

3.82 kg / 8.42 lbs.

### Weight (Monitor Head Only) (kg/lbs.)

3.08 kg / 6.79 lbs.

## WHAT'S IN THE BOX

Monitor with stand

1 x Power cable (1.8 m)

1 x HDMI cable (1.8 m)

Quick setup guide

## CERTIFICATION

### CCC

Yes

### RoHS (EU 2002/95/EC)

Yes

### Windows Certification

Windows 7, Windows 10

### China Energy Efficiency Standard

Tier 2

### TÜV Rheinland Eye Comfort

Yes



<sup>1</sup>AMD Freesync™ is enabled for AMD Radeon™ Series graphics cards. <sup>2</sup>75 Hz only for HDMI input <sup>3</sup>This software can only be used with Windows 10.

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27701, U.S.A. Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others. Specifications may vary depending upon region.

# Lenovo L24e-30

Lenovo

