



PDU33108 | MONITORED PDU SERIES



Deliver and manage reliable power to electronic equipment, servers, and network/telecom devices

Stay informed about your power with the CyberPower PDU33108 monitored 3-Phase PDU. Ideal for data centers and network closets, this unit provides power monitoring in real time over the network by using the CyberPower management console and the RJ45 Ethernet port for network connection or locally by using the LCD.

The PDU33108 supports inputs between 200-240V and includes 42 IEC-320 outlets. Other features include an interactive digital display with selectable background color, high operating temperature range, built-in web interface, and power event notifications. The CyberPower PDU33108 is protected by a three-year limited warranty.

Typical Applications

- Corporate Servers
- Network Closets
- Data Centers

Features

- Phase: 3-Phase
- Notifications: Email, SMS Text, and SNMP Trap
- Amps: 50A (Derated to 35A)
- Volts: 200V-240V
- Frequency: 50/60Hz
- Input plug type: IEC-309 60A Blue (3P+E)
- Outlets: (36) IEC-320 C13 + (6) IEC-320 C19
- Size: 0U Rackmount
- Cord Length (ft): 10
- Dimensions (in): 2.2W x 70.5H x 2.2D
- Warranty: 3 year

SPECIFICATIONS

GENERAL

Type	Monitored
------	-----------

INPUT

Nominal Input Voltage	200 - 240 VAC
-----------------------	---------------

Input Frequency Range	50 Hz - 60 Hz
-----------------------	---------------

Input Plug Type	Hubbell CS8365C
-----------------	-----------------

Cord Length	10 ft (3m)
-------------	------------

Maximum Input Current	50A
-----------------------	-----

Derated Input Current	35 A
-----------------------	------

Phase	3-Phase
-------	---------

OUTPUT

Overload Protection	20A X 3
---------------------	---------

Nominal Output Voltage	200 - 240 VAC
------------------------	---------------

Outlet Types	36 - IEC-320 C13 + 6 - IEC-320 C19
--------------	------------------------------------

Outlets - # of Banks	3
----------------------	---

Outlets - Total	42
-----------------	----

PHYSICAL

Rack Height	0U
-------------	----

Physical Dimensions - (WxHxD) (cm)	5.59 x 179.07 x 5.59 (cm)
------------------------------------	---------------------------

Physical Dimensions - (WxHxD) (in)	2.2 x 70.5 x 2.2 (in)
------------------------------------	-----------------------

Physical Dimensions - (WxHxD) (mm)	56 x 1791 x 56 (mm)
------------------------------------	---------------------

Material of Construction	Metal
--------------------------	-------

Cord Retention Tray/Cord Organizers	Yes
-------------------------------------	-----

Adjustable Mounting Brackets	1 set
------------------------------	-------

Color	Black
-------	-------

PDU33108 | MONITORED PDU SERIES



SPECIFICATIONS CONT.

MANAGEMENT & COMMUNICATION

Monitoring Level	Input, Per Circuit
Software (Free Download)	PowerPanel® Business
Modular Expandability (Cascading)	Yes, via RJ45
Protocols	IPv4, TCP/IP, UDP, SNMPv1, HTTP, NTP, DNS, Telnet, DHCP, SMTP, FTP, IPv6, SNMPv3, HTTPs, SSH, SSL, TLS, LDAP(S), RADIUS, Syslog, CLI, Windows AD
Environmental Sensor	Optional, via RJ45
LED Indicators	Tx/Rx, LINK, Normal/Warning/Critical Status
Upgradeable firmware	Yes
LCD	Multifunction LCD

ENVIRONMENTAL

Operating Temperature	23 - 140 °F (-5 - 60 °C)
Operating Elevation	0 - 11480 ft (0 - 3499 m)
Operating Relative Humidity	0 - 95 % (non-condensing)

CERTIFICATIONS

Environmental	RoHS Compliant
Safety	UL60950-1 UL62368-1 FCC Class A

WARRANTY

Product Warranty	3 Year Limited Warranty
------------------	-------------------------