# BenQ

# MOBIUZ™

## Immersion Beyond Imagination

## BenQ MOBIUZ Gaming Curved SimRacing Monitor EX3415R

Maximizing enjoyment of the latest HDR gaming content, EX3415R leverages 1900R 21:9 ultrawide IPS panel with HDRi and superior visual features to deliver immersive gaming experience. Featuring BenQ proprietary HDRi technology, plus 1ms MPRT, 144Hz, and AMD Freesync™ Premium, EX3415R takes your gaming enjoyment to the next level.

## Intensity like never before

With MOBIUZ monitors, your worlds come to life. Frontrunner status is within reach and no trophy is beyond imagining. Take the driver's seat and get going—glory at the finish line awaits!

190 MPH 2nd
1900R

### EXpanded for Better Immersion

Get a panoramic view out of the 1900R ultrawide and make a solid judgement to get past your opponents when you're down on the track. Hear the engine rev as you take the lead. Drive forward into the next challenge.

1900R

without HDRi
with HDRi

HDRi
144Hz
1ms MPRT
AMD FreeSync Premium

### EXtraordinary Performance

Top-notch performance is a combination of skill and the right gear. Race against beautiful, smooth imagery and enjoy the utmost speed. Leave your opponents in the dust as you go the full distance.

Resolution
Sound Field
Fidelity
Positioning
Balance

EX3415R — Others

**Treble** Crisp — Sweet
**Midrange** Clear — Smooth
**Bass** Full — Warm

FPS    Cinema    RCG    SPG    Pop / Live

### EXpansive Sound

Get up to speed and immerse in the sound of your screeching tires. Feel the engine rev, the roar of the crowd, and the scream of your machine as you take the lead. The waving checkered flag cannot be far ahead!

## MOBIUZ Gaming Monitor EX3415R

| | |
|---|---|
| Product Color | Metallic Gray |
| **Panel** | |
| LCD≥ Size (inch) | 34 |
| Aspect Ratio | 21 : 9 |
| Curvature | 1900R |
| Resolution (max.) | 3440x1440 |
| Display Area | 799.8 x 334.8 mm (31.4x13.23 inch) |
| Pixel Pitch (mm) | 0.2325 |
| Brightness (SDR mode) | 200 |
| Brightness (HDR mode) | 400 |
| Native Contrast (typ.) | 1000 :1 |
| Panel Type | IPS |
| Viewing Angle (L/R;U/D) (CR≥10) | 178/178 |
| Response time | 1ms (MPRT) |
| Refresh rate | 144Hz |
| Display Colors | 1.07 billion colors |
| Color Gamut | 98% DCI-P3 |
| Backlight | LED backlight |
| **Dimension & Weight** | |
| Dimensions (H x W x D) | H: 525x815.2x269.7mm (20.7x32.1x10.6 inch) L: 425.1x815.2x269.7mm (16.7x32.1x10.6 inch) |
| Net Weight | 8.5kg (18.7lb) |
| Gross Weight | 13.2kg (29.1 lb) |
| **Special feature** | |
| Video Format Support | Yes |
| AMA | Yes |
| Flicker-free Technology | Yes |
| Color Mode | Cinema HDRi | Custom | DisplayHDR ePaper | FPS | Game HDRi | HDR M-Book | Racing game | RPG | sRGB |
| Brightness Intelligence Plus (B.I.+) | Yes |
| Color Weakness | Yes |
| ePaper mode | Yes |
| Low Blue Light | Yes |
| Light Tuner | Yes |
| Color Vibrance | Yes |
| Black eQualizer | Yes |
| VESA Wall Mounting | 100 x 100 mm (3.94x3.94 inch) |
| Tilt (down/up) | -5° ~ -15° |
| Swivel | 15°/ 15° |
| High adjustment | 100 mm (3.94 inch) |
| K Locker | Yes |
| HDR Mode | HDR10 | VESA DisplayHDR400 |
| **I/O** | |
| Speaker | 2.1 Channel (2Wx2 + 5W woofer) |
| HDMI | v2.0 x 2 |
| DP Input | v1.4 x 1 |
| USB 3.0 | 2 |
| Headphone Jack | Yes |
| **Power** | |
| Power Supply (90~264 AC) | Adapter |
| Power Consumption (On mode) | 85W |
| Power Consumption (Power saving mode) | <0.5W |
| **Certification** | |
| FreeSync certification | FreeSync Premium |
| TUV Certificate | Flicker-free | Low Blue Light |
| Mac Compatible | Yes |
| Windows® Compatible | Windows®10 | Windows®7 Windows®8 | Windows®8.1 |

BenQ