



# Planar URX85

## 85" 4K LCD Display

The Planar® UltraRes™ X URX85 is a TAA Compliant, 4K, HDR, professional 85" LCD display with on-board processing for viewing up to four content sources simultaneously. It features an OPS slot for additional connectivity, and a redundant power supply. With the optional Planar® Profile™ Mounting System it can achieve ADA compliance opening it to use in more environments ranging from meeting spaces to high impact digital signage and media rooms.



SPECIFICATION	DETAIL
Product Name	URX85
Planar Part Number	998-2164-00
Display Resolution	Ultra HD (3840 x 2160)
Screen Size	85 in. (diagonal)
Aspect Ratio	16:9
Display Technology	Direct-lit LED LCD
Haze	45%
Surface Treatment	AG
Display Active Area	73.7" x 41.5" (1872.0mm x 1053.0mm)
Viewing Angle (typ)	178°
Backlight	LED
Backlight life (1/2 brightness)	70,000 hrs (min)
Brightness (typ)	700 nits
Response Time (typ)	8.5 ms
Frame Rate	60Hz
Contrast Ratio (typ)	4000:1
Contrast Ratio - Dynamic	20,000:1
Pixel Pitch	0.4875 mm
Color Gamut	88% NTSC

<b>HDR (High Dynamic Range)</b>	Yes
<b>Display Color</b>	>1 billion colors. Full 10 bit data path
<b>External Connections</b>	DisplayPort 1.2 x 1, HDMI 2.0 x 2 (HDCP 2.2), HDMI 1.4 x 2, OPS x 1
<b>Modes</b>	1x 3840x2160 @ 24/25/30/60Hz, 4x 1920x1080 @ 24/25/30/50/60Hz; 2x 1920x2160 @ 60Hz; 480p, 576p, 720p @ 50/60 Hz; 1080p @ 24/25/30/50/60Hz; 1080i @ 50/60 Hz
<b>Display Control</b>	IR, RS-232, LAN, HDMI-CEC, HDMI-CEC, Keypad, Web Brower Interface, Mobile App
<b>Cabinet Dimensions (W x H x D)</b>	75.6" x 43.3" x 3.7" (1919.0mm x 1100.0mm x 94.3mm)
<b>Dimensions including wall mount</b>	75.6" x 43.3" x 3.8" (1919.0mm x 1100.0mm x 95.8mm)
<b>Orientation</b>	Landscape/Portrait
<b>Bezel Width</b>	0.9" (23mm)
<b>Display Edge to Active Area</b>	0.9" (23.5mm)
<b>Weight</b>	190 lb (86.2 kg)
<b>Weight (Shipping)</b>	TBD lb (TBD kg)
<b>Audio Input</b>	PC Line In
<b>Audio Output</b>	PC Line Out, S/PDIF
<b>Speakers</b>	10W x 2 built-in
<b>Enclosure</b>	Metal
<b>Mounting</b>	Planar Profile Mounting System or VESA: 600 x 400 mm
<b>Fanless</b>	Yes
<b>Line Voltage</b>	100-240V; 50/60Hz
<b>Power Consumption (typ)</b>	270W (standby: <0.5W)
<b>Operating Temperature</b>	0° to +40°C (32° to 104°F) at up to 1500m, 0° to +35°C (32° to 95°F) at up to 3000m
<b>Humidity</b>	20 - 85% RH (non-condensing)
<b>Options / Features</b>	MediaPlex Plus Processing, Scheduling, Presets, Redundant power supply
<b>Multi-Source Views</b>	PiP, Dual, Triple, Quad
<b>Approvals</b>	FCC Class A, CE, cTUVus, RoHS
<b>TAA Compliance</b>	Yes
<b>Warranty</b>	3 years Advance Exchange
<b>Recommended Usage</b>	Up to 24x7
<b>In the Box</b>	URX85 display, US power cord, HDMI cable, IR sensor, remote control, lifting straps x2, QuickStart Guide
<b>UPC</b>	8 10689 00810 1

For more information, please visit [www.planar.com](http://www.planar.com)

*Specifications are subject to change without notice.*

*Specification Report Date: 4/2/2021*

*© Copyright 2021 Planar Systems, Inc. All rights reserved*