



# Planar URX85-ERO-T

## 85" 4K LCD Touch Display

The Planar® UltraRes™ X URX85-ERO-T is a TAA Compliant, 4K, HDR, professional 85" LCD touch display with on-board processing for viewing up to four content sources simultaneously. It offers an OPS slot for additional connectivity, and a redundant power supply. With the optional Planar® Profile™ Mounting System it can achieve ADA compliance. It also features Planar® ERO-LCD™ protection technology for use in high-traffic and public environments. It offers high brightness, superior color performance with exceptional 4K clarity and multi-point touch for applications ranging from interactive meeting spaces to high impact touch-based digital signage.



SPECIFICATION	DETAIL
Product Name	URX85-ERO-T
Planar Part Number	998-2166-00
Protective Glass	ERO optically-bonded glass technology featuring Corning Gorilla Glass, 2mm AG
Touch Technology	IR touch: 32 points with driver; 12 points without driver
OS Compatibility	Windows 8, 10, Mac OSX and Linux
Display Resolution	Ultra HD (3840 x 2160)
Screen Size	85 in. (diagonal)
Aspect Ratio	16:9
Display Technology	Direct-lit LED LCD
Display Active Area	73.7" x 41.5" (1872.0mm x 1053.0mm)
Viewing Angle (typ)	178°
Backlight	LED
Backlight life (1/2 brightness)	70,000 hrs (min)
Brightness (w/protective glass)	630 nits
Response Time (typ)	8.5 ms
Frame Rate	60Hz
Contrast Ratio (typ)	4000:1
Contrast Ratio - Dynamic	20,000:1
Pixel Pitch	0.4875 mm

<b>Color Gamut</b>	88% NTSC
<b>HDR (High Dynamic Range)</b>	HDR10
<b>Display Color</b>	>1 billion colors. Full 10 bit data path
<b>External Connections</b>	DisplayPort 1.2 x 1, HDMI 2.0 x 2 (HDCP 2.2), HDMI 1.4 x 2, OPS x 1, USB-B (for touch controller)
<b>Modes</b>	1x 3840x2160 @ 24/25/30/60Hz, 4x 1920x1080 @ 24/25/30/50/60Hz; 2x 1920x2160 @ 60Hz; 480p, 576p, 720p @ 50/60 Hz; 1080p @ 24/25/30/50/60Hz; 1080i @ 50/60 Hz
<b>Display Control</b>	IR, RS-232, LAN, HDMI-CEC, Keypad, Web Brower Interface, Mobile App
<b>Cabinet Dimensions (W x H x D)</b>	76.3" x 44.1" x 4.0" (1939.0mm x 1120.0mm x 100.1mm)
<b>Dimensions including wall mount</b>	76.3" x 44.1" x 4.1" (1938.9mm x 1119.9mm x 104.3mm)
<b>Orientation</b>	Landscape/Portrait
<b>Bezel Width</b>	0.4" (10.3mm)
<b>Display Edge to Active Area</b>	1.3" (33.5mm)
<b>Weight</b>	235 lb (106.6 kg)
<b>Audio Input</b>	PC Line In
<b>Audio Output</b>	PC Line Out, S/PDIF
<b>Speakers</b>	10W x 2 built-in
<b>Enclosure</b>	Metal
<b>Mounting</b>	Planar Profile Mounting System or VESA: 600 x 400 mm
<b>Fanless</b>	Yes
<b>Line Voltage</b>	100-240V; 50/60Hz
<b>Power Consumption (typ)</b>	270W (standby: <0.5W)
<b>Operating Temperature</b>	0° to +40°C (32° to 104°F) at up to 1500m, 0° to +35°C (32° to 95°F) at up to 3000m
<b>Humidity</b>	20 - 85% RH (non-condensing)
<b>Options / Features</b>	MediaPlex Plus Processing, Scheduling, Presets, Redundant power supply, TouchMark license key
<b>Multi-Source Views</b>	PiP, Dual, Triple, Quad
<b>Approvals</b>	FCC Class A, CE, cTUVus, RoHS
<b>TAA Compliance</b>	Yes
<b>Warranty</b>	3 years Advance Exchange
<b>Recommended Usage</b>	Up to 24x7 operation
<b>In the Box</b>	URX85-ERO-T display, US power cord, HDMI cable, USB (A to B) cable, IR sensor, remote control, lifting straps x2, TouchMark license key (one time download), QuickStart Guide
<b>UPC</b>	8 10689 00812 5

For more information, please visit [www.planar.com](http://www.planar.com)

*Specifications are subject to change without notice.*

*Specification Report Date: 6/18/2021*

*© Copyright 2021 Planar Systems, Inc. All rights reserved*