

The LG DVLED Ultimate Business Display

One display. Brilliantly simple. Utterly Breathtaking.

2K FULLHD

81" - 217" (5 SIZES)

dual2K Ultra Stretch

147" - 393" (5 SIZES)

4K ULTRAHD

163" - 325" (4 SIZES)

dual4K Ultra Stretch

294" - 589" (4 SIZES)

8K ULTRAHD

325" (1 SIZES)

OUTDOOR 16:9

230" - 578" (4 SIZES)

SCOREBOARDS

230" - 445" (2 SIZES)



dual2K Ultra Stretch 147" MAGNIT (2 x 81") shown

THE DISPLAY

All parts and components in one ready-to-assemble bundle*

- LG direct view LED panels
- 4K LG controller
- 5% Spare modules
- Spare boards and parts
- Service tool

LG webOS™

- Intuitive on-screen user interface
- Remote control for easy setup
- Ambient-light sensor and automatic brightness adjustment

Screen sharing

- Miracast
- WiDi

Onboard CMS

- 3.6GB flash storage
- Store, schedule, playback

* Mounting brackets sold separately

THE SERVICES

In-Field Training

- Hosted by an LG Field Engineer
- Educational webinar prior to installation
- Be ready for installation with complete support from LG

3 years LG TotalCare Health Checks

- 2x per year on-site display health check by LG
- Priority on any needed RMA services

3 Years LG ConnectedCare System Surveillance

- ConnectedCare Solution Software subscription
- Optional LG professional remote monitoring service

Warranty Service

- 3 year limited manufacturer warranty
- Optional LG ExtendedCare warranty for up to 5 years
- Optional LG White Glove replacement service

THE PACKAGING

LG Branded Flight Case

- Every LG direct view LED display ships in a new, branded, wheeled flight case
- Premium-grade protection for each stunning display
- No more searching to make sure you received every box
- No forklifts or pallet jacks required, simply roll the cases in to your space



LG DVLED Ultimate Business Display Size	SKU	Pixel Pitch	Max Brightness	LED Package	Dimensions (W x H)
2K FullHD 81" Ultimate Business Display	LSAB-F081C	0.9mm	1,200 Nits	COB	5.9 x 3.3 ft 70.8 x 39.9 in 1,800 x 1,013 mm
2K FullHD 108" Ultimate Business Display	LSAA-F108C	1.2mm	1,200 Nits	IMB	7.9 x 4.4 ft 94.4 x 53.1 in 2,400 x 1,350 mm
2K FullHD 136" Ultimate Business Display	LSCB-F136C	1.56mm	800 Nits	SMB	9.8 x 5.5 ft 118.1 x 66.4 in 3,000 x 1,687 mm
2K FullHD 163" Ultimate Business Display	LSCB-F163C	1.8mm	800 Nits	SMB	12 x 6.6 ft 141.7 x 79.7 in 3,600 x 2,025 mm
2K FullHD 217" Ultimate Business Display	LSCB-F217C	2.5mm	800 Nits	SMB	16 x 8.9 ft 189 x 106.3 in 4,800 x 2,700 mm
dual2K Ultra Stretch 147" (2 x 81") Ultimate Business Display	LSAB-G147C	0.9mm	1,200 Nits	COB	12 x 3.3 ft 141.7 x 39.9 in 3,600 x 1,013 mm
dual2K Ultra Stretch 196" (2 x 108") Ultimate Business Display	LSAA-G196C	1.2mm	1,200 Nits	IMB	16 x 4.4 ft 189 x 53.1 in 4,800 x 1,350 mm
dual2K Ultra Stretch 245" (2 x 136") Ultimate Business Display	LSCB-G245C	1.56mm	800 Nits	SMD	20 x 5.5 ft 236.2 x 66.4 in 6,000 x 1,688 mm
dual2K Ultra Stretch 294" (2 x 163") Ultimate Business Display	LSCB-G294C	1.8mm	800 Nits	SMD	24 x 6.6 ft 283.4 x 79.7 in 7,200 x 2,025 mm
dual2K Ultra Stretch 393" (2 x 217") Ultimate Business Display	LSCB-G393C	2.5mm	800 Nits	SMD	31 x 8.9 ft 377.9 x 106.3 in 9,600 x 2,700 mm
4K UltraHD 163" Ultimate Business Display	LSAB-U163C	0.9mm	1,200 Nits	COB	12 x 6.6 ft 141.7 x 79.7 in 3,600 x 2,025 mm
4K UltraHD 217" Ultimate Business Display	LSAA-U217C	1.2mm	1,200 Nits	IMD	16 x 8.9 ft 189 x 106.3 in 4,800 x 2,700 mm
4K UltraHD 271" Ultimate Business Display	LSCB-U271C	1.56mm	800 Nits	SMD	20 x 11 ft 236.2 x 132.9 in 6,000 x 3,375 mm
4K UltraHD 325" Ultimate Business Display	LSCB-U325C	1.8mm	800 Nits	SMD	24 x 13 ft 283.5 x 159.3 in 7,200 x 4,050 mm
dual4K Ultra Stretch 294" (2 x 163") Ultimate Business Display	LSAB-V294C	0.9mm	1,200 Nits	COB	24 x 6.6 ft 283.5 x 79.7 in 7,200 x 2,025 mm
dual4K Ultra Stretch 393" (2 x 217") Ultimate Business Display	LSAA-V393C	1.2mm	1,200 Nits	IMD	31 x 8.9 ft 378 x 106.3 in 9,600 x 2,700 mm
dual4K Ultra Stretch 490" (2 x 271") Ultimate Business Display	LSCB-V490C	1.56mm	1,200 Nits	SMD	39 x 11 ft 472.4 x 132.9 in 12,000 x 3,375 mm
dual4K Ultra Stretch 589" (2 x 325") Ultimate Business Display	LSCB-V589C	1.8mm	800 Nits	SMD	47 x 13 ft 566.9 x 159.4 in 14,400 x 4,050 mm
8K UltraHD 325" Ultimate Business Display	LSAB-U325C	0.9mm	1,200 Nits	COB	24 x 13 ft 283.5 x 159.4 in 7,200 x 4,050 mm
Outdoor 230" Ultimate Business Display	GSCA-H230C	3.9mm	5,000 Nits	SMB	16 x 9.8 ft 196.9 x 118.1 in 5,000 x 3,000 mm
Outdoor 335" Ultimate Business Display	GSCA-F335C	3.9mm	5,000 Nits	SMB	25 x 13 ft 283.5 x 157.5 in 7,500 x 4,000 mm
Outdoor 405" Ultimate Business Display	GSCA-F405C	4.6mm	5,000 Nits	SMB	30 x 16 ft 354.3 x 196.9 in 9,000 x 5,000 mm
2K FullHD Outdoor 578" Ultimate Business Display	GSCC-F578C	6.6mm	5,000 Nits	SMB	42 x 24 ft 503.9 x 283.5 in 12,800 x 7,200 mm
Indoor Scoreboard 230" Ultimate Business Display	LSCA-H230C	3.9mm	1,000 Nits	SMB	16 x 9.8 ft 196.9 x 118.1 in 5,000 x 3,000 mm
Outdoor Scoreboard 445" Ultimate Business Display	GSCD-S445C	10.4mm	5,000 Nits	SMB	26 x 26 ft 315 x 315 in 8,000 x 8,000 mm

THE LG DIFFERENCE



A sophisticated controller and LG webOS deliver advanced multi-view options and simplified system control.

- **webOS** with built-in Quad Core SoC can execute several tasks while providing smooth content playback without the need for an external media player
- **Built-in Media Player** saves system complexity not having to purchase an external device to play media
- **On-board Flash Storage** up to 3.6GB for content and applications for select models
- **Remote Control** with an intuitive user interface puts system and image control in the palm of your hand
- **Built-in AV-Over-IP Decoder** that can simultaneously display up to four 4K RTSP video streams
- **Built-in Scaling** capability can transform resolution either up or down for any area of the display