

# 10.1" Outdoor Touch or Non-Touch, IP65 Rated, High Bright Display, with Audio, HDMI

MOD-10180H - Non-Touch MOD-10180CH - Capacitive Touch



## 10" Outdoor Touch or Non-Touch Display

Durable, reliable, and beautifully vibrant, this small-format outdoor display works at an extended temperature range, making it ideal year round, no matter the temperature. To protect from the elements, ranging from water, moisture, sand, dust and insects, this commercial display is IP65 rated, allowing for hard use in nearly every weather condition. This display offers stunning, clear, crisp and easy-to-see visuals both in sun and ambient lighting. For added impact, the light sensor adjusts the display's brightness during cloudy days and at nighttime to optimize power consumption and ensure an ideal viewing experience. The Mimo Outdoor High Bright Displays are the perfect digital signage for amusement parks, sports arenas, quick service restaurant orders, outdoor kiosks, gas stations, and many more commercial applications.

#### Features:

- IP65 Outdoor Rating
- 16:10 Aspect Ratio
- Multi-point capacitive touch screen optional (MOD-10180CH)
- All aluminum housing designed specifically for outdoor 24/7 use

## **Product Specs**

#### **Display Size**

10.1 inch

## Resolution

1280 x 800

## Brightness

1000cd/m2

#### **Contrast Ratio**

1000:1

#### Connections

VGA, HDMI, 3.5mm audio, USB

## **Viewing Angle**

88/88/88/88

## **Operating Temperature**

-20 to 122c

## **Power Consumption**

40W

### **Mount Pattern**

VESA-100mm

## **Regulatory Certifications**

FCC. CE. ROHS

## Applications:

- Outdoor interactive digital signage
- Outdoor interactive wayfinding
- Outdoor menu boards with ordering capability
- Outdoor stadiums
- Outdoor amusement parks
- Outdoor restaurants
- Outdoor transportation
- Outdoor service and gas stations
- Food trucks