



4 Channel Surveillance Kit with Three 5MP IP Cameras and One 8MP Advanced Analytics Camera, 1TB

ZIPK4TA

4 Channel Network Video Recorder with Built-In PoE
3 5MP IP Cameras
1 8MP Advanced Analytics IP Camera



Front panel



Rear panel



Key Features

- EZ Wizard:** for easy network and system setup
- EZ Search:** search events from thumbnails
- EZ Record:** set up recording resolutions and recording type
- EZ Copy:** copy what you are playing onto a USB flash drive
- EZ App Setup:** just scan a QR code with the app to view your cameras on your mobile device

Recorder Features

- Up to 8MP resolution for live view, recording, and playback
- Plug & Play – get video automatically via the PoE ports without any setup
- Facial Recognition and Comparison*
- Human and Vehicle Detection*
- Supports H.265 and H.264 streams
- Free US-based DDNS service
- 4K monitor output
- Gigabit Ethernet port
- Built-in S.M.A.R.T technology (Self-Monitoring, Analysis and Reporting Technology for HDD)
- Remote monitoring via PC and mobile apps
- 1TB storage
*use with O8K1A

Camera Features

- Supports up to 5MP resolution (O5K1)
- Supports up to 8MP resolution (O8K1A)
- 2.8mm wide angle lens
- True Day/Night operation (IR cut filter)
- IR range up to 100ft (built-in IR LEDs)
- Supports H.265/H.264 compression
- IP66 compliant, weather resistant
- Includes Micro SD card slot up to 128GB

What's in the box:

- NVR with 1TB hard drive
- Three 5MP cameras
- One 8MP Advanced Analytics camera
- Three 60ft Ethernet cables
- One 3ft Ethernet cable
- Remote control
- 2 x AAA Batteries
- HDMI cable

| Camera Specifications | O5K1 | O8K1A |
|-----------------------------|--|--|
| Image Sensor | 1/2.7" 5MP CMOS | 1/2.7" Progressive CMOS |
| Resolution | 2592 x 1944 | 8MP 3840(H)×2160(V) |
| Minimum Illumination | 0 lux (IR LED on), F1.2 | Color 0.05lux @ F1.2(AGC ON) ; B/W 0 lux @ IR ON |
| Day/Night | IR cut filter | IR cut filter with auto switch Day/Night/Auto/Schedule |
| Compensation | DWDR/BLC | Off/On (5 Zone) |
| White Balance | Auto / Manual/Indoor | Auto/Manual |
| Electronic Shutter Speed | 1/5 ~ 1/20000 sec | 1/5 ~ 1/20000s |
| DNR | 3D | 3D |
| IR Range | 100ft. (depending on scene reflection) | 100ft. (depending on scene reflection) |
| Compression | H.265, H.264 | H.265, H.264 |
| Bitrate Control | VBR, CBR | VBR, CBR |
| Multiple Streaming | 2 streams | 2 streams |
| Ethernet | 10/100 Mbps | 10/100 Mbps |
| Power | PoE or 12VDC (power supply not included) | PoE or 12VDC (power supply not included) |
| Power Consumption | ~7W | ~7W |
| Operating Temperature | -22°F - 131°F | -22°F - 140°F |
| Operating Humidity | 0% - 90% RH | 0% - 95% RH |
| Unit Dimensions | 3.35" (H) x 3.55" (Dia.) | 3.94" (H) x 3.56" (Dia.) |
| Unit Weight | 1.5 lbs. | 1.5 lbs. |
| Alerts & Advanced Analytics | Motion Detection | Motion Detection, Human Detection, Vehicle Detection, Facial Recognition |

| Recorder Specifications | |
|---------------------------|--|
| Max. Bit Rate | 40 Mbps |
| Max. Recording Resolution | 8MP |
| PoE Ports | 4 |
| Monitor Output | 1 HDMI, 1 VGA |
| Display Resolutions | 3840 x 2160, 2560 x 1440, 1920 x 1080, 1440 x 900, 1290 x 1024, 1280 x 720, 1024 x 768 |
| USB Ports | 2 x USB 2.0 |
| HDD Slots | 1 (Up to 1TB) |
| Ethernet | RJ-45 (100/1000M) port |
| Remote Viewing | Speco Gray Viewer (Windows), Speco Gray app (iOS, Android) |
| Power Supply | 48VDC, 1.2A |
| Dimensions | 11.8" (W) x 2.1" (H) x 8.9" (D) |
| Model | N4JLA |

Optional Accessories



O5KJBD
Camera Junction Box



O5KWMT
Wall Mount

RESI-CAM®

³Hard drives excluded. iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. Amazon's trademark is used under license from Amazon.com, Inc. or its affiliates. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec. Rev. 10/14/20