



# 4K H.265 NVR with Smart Analytics

## N64NR

64 Channel NVR



### STORAGE 3TB - 112TB

N64NR3TB	N64NR12TB	N64NR24TB	N64NR40TB	N64NR80TB
N64NR6TB	N64NR16TB	N64NR30TB	N64NR64TB	N64NR96TB
N64NR8TB	N64NR20TB	N64NR32TB	N64NR72TB	N64NR112TB



Front panel



Rear panel



## Key Features

### EZ Wizards - For ease of use and setup

Camera: quickly discover and install all Speco IP cameras

Setup: for quick setup of general settings

Network: network setup and port forwarding

Record: quickly setup recording resolutions and recording type

Search: quickly search for events from thumbnails

Copy: quickly copy what you are playing onto a USB flash drive

### EZ Mobile - easy mobile setup for viewing on desktop or mobile apps

- Real time recording up to 8MP resolution (4K) at 30fps
- H.265 compression - Store up to 2x more than H.264!
- 4K HDMI out and one VGA monitor output, additional storage via 2 eSATA ports
- 8 SATA ports for up to 112TB of storage max
- Object and line crossing detection and alerts\*
- EZ Search 2.0 - Quickly find an event using time-sliced thumbnail images of your recordings with quick preview
- Smart Search - Specify a region on the camera view and search on changes in that area\*
- Free US-based DDNS and P2P services
- Remote viewing via web browser or your mobile device
- Easy video exporting via USB
- Remote control included
- Rack ears included
- 5 year limited warranty<sup>1</sup>

\*with Speco Smart Analytic Cameras

## Additional Features

- Find and install IP cameras on the local network without needing to locate the cameras manually
- Supports different recording types: Continuous, Motion, Analytics, and Sensor
- Create bookmark pins on playback for easy reference
- Instant playback for individual channels directly from the live view screen
- Customizable channel view placement
- Remote monitoring, recording, playback, configuration, upgrades, and PTZ control via the internet
- Simultaneous HDMI & VGA video output
- Supports 2-way audio communication (speaker required)

INTEGRATED WITH  
**speco access**



- Auto Live Camera Pop-Up
- View A Camera
- Event Tag

### Optional Accessory



**P16S18**

18 Port Switch  
with 16 Port PoE

<sup>1</sup>Limited Warranty/Hard drives excluded. Check www.specotech.com for more details. iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 4/6/21



800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com





## Technical Specifications: 4K H.265 NVR with Smart Analytics

Model		NR	
Video	Input	Max. IP Channels	64
		IP Camera	H.264/H.265 Auto Detection (Max 8MP)
	Output	Main Monitor	HDMI (Max. 4K) and VGA (Max. Full HD)
		Sub Monitor	1 HDMI
Audio	Network Input		64 Ch. IPC audio input
	2-way Audio		RCAx1
	Local Output		RCAx1
Recording	Encoding Resolutions		8MP/5MP/4MP/3MP/1080P/720P
	Codec		H.264/H.265 (Auto Detection)
	Max Frame Rate per Channel		Any Resolution @30fps
	Recording Mode		Analytics/Continuous/Motion/Sensor/Schedule/Manual
	Pre-Recording		Max. 5 seconds
	Post Recording		Max. 10 minutes
Search & Playback	Search		EZ Search, Motion, Specific Date/Time, Event, Museum, Bookmarks, Snapshots, Log
	Simultaneous Playback		Max 16 Ch.
	Smart Search		Highlighted color to display camera records in a certain period of time, different colors refer to different record events
	Playback Resolutions		8MP/5MP/4MP/3MP/1080P/720P
	Playback Functions		Play, pause, FF, FB, digital zoom, etc.
Backup	Media		USB drive, USB Portable HDD, Network
	Format		JPG, AVI, ZIP (Player+Proprietary Data)
Storage	HDD	Max Capacity of each HDD	14TB
		Internal SATA ports	8
	USB	Front	1 (USB 2.0)
		Rear	2 USBs: 1 USB 2.0, 1 USB 3.0
Alarm	Mode		Manual, sensor, motion, exception, intelligence
	Input		8 Ch. local
	Output		4 Ch local
	Linkage		Record/Snapshot/Preset/Email/Pop-up Window
User I/F	Input Method		IR Remote, Mouse
Network	Network Bandwidth		320Mbps
	P2P/Dynamic DNS		Free US-Based Speco P2P and DDNS Service
	Network Protocols		TCP/IP, PPPoE, DHCP, DNS, UPnP, NTP, SMTP
	Dual Network Card		Yes
	LAN 1		Recorder
	LAN 2		Cameras
Network Access	Mobile		iOS/Android via Speco Blue App, SecureGuard® Client
	Web Viewer		Windows IE
	VMS		SecureGuard®
	Max. User Access		Max 10 users online (web client)
Features	Digital Zoom		Live and Playback, Free Size
	Smart Analysis		* Crowd Density, People Counting, Object Detection, Tampering, Tripwire, Intrusion
	S.M.A.R.T		Temperature, Power On Time, Bad Sectors and Health
Power	Power Consumption		≤ 15W (without HDD)

\* Does not have built in DHCP server

Please note that specifications and unit exterior design are subject to change without notification. Rev. 4/6/21



800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com

