



# Summit B15 A11MT-401

Manufacturer Part #	SUMMITB15T401
OS	Windows 10 Pro (MSI recommends Windows 10 Pro for business.)
CPU	Core i7-1165G7
CPU Speed	1.2 - 4.7GHz
Chipset	-
Color	Ink Black
Screen Size	15.6" FHD, IPS-Level 60Hz 72%NTSC Thin Bezel, close to 100% sRGB, Touch Screen support MSI active Pen (MPP2.0)
Resolution	1920x1080 (16:9)
GPU	Intel® Iris® Xe
Keyboard	White backlight keyboard (84 Key)
Audio	Nahimic 3 / Hi-Res Audio
Speaker	Speakers 2W * 2
Memory	16GB (8G*2) DDR4 3200MHz
HDD Capacity	1TB NVMe SSD
HDD Interface	NVMe
Optical Drive Type	-
LAN	Ethernet Dongle
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
Bluetooth	BT 5.1
Card Reader	Micro SD
Webcam	IR HD Type [30fps/720p]
USB	1x USB 3.2 Gen1, 2x USB-A 3.2 Gen2
Type-C Port	1x Thunderbolt 4 [Support Power delivery, DP 1.4a, USB 4.0]
Video Port	HDMI (supports 4K @ 60Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	65W Compact
Battery Pack	3 cell (52Whr)
Dimension	14.06" x 9.21" x 0.67"
Weight	3.53 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)