



[DOWNLOAD SPECS](#)

PIXMA PRO-200

Specifications

Printer Type	Wireless Professional Dye-based Inkjet Printer
Printing Method	FINE: Full-Photolithography Inkjet Nozzle Engineering
Features	Wireless Printing ¹ , Fast Photo Printing ¹⁰ , Advanced Pattern Print, Black & White Photo Printing Mode, Borderless Printing ⁶ , Disc Label Printing, Contrast Reproduction, Paper Feed Skew Correction, Photo Printing, Grayscale Photo Printing, Index Print, Square Photo Printing, Gallery Wrap Printing
Print Speed (up to)	11" x 14" Bordered Colour Photo (A3+): 1 minute 30 seconds ¹⁰ 8" x 10" Bordered Colour Photo (A4): 53 Seconds ¹⁰
Number of Nozzles	768 Nozzles x 10 Inks, Total: 6,144
Print Resolution (Up to)	Colour: Up to 4800 x 2400 dpi ¹¹
OS Compatibility	Windows ¹¹ Windows [®] 10, Windows 8.1, Windows 7 SP1 Mac ¹³ Mac OS [®] X v10.11.6 – macOS v10.15 Mobile Operating Systems ¹⁴ iOS [®] , AndroidTM, Windows 10 Mobile

Standard Interfaces	Hi-Speed USB Ethernet (10/100) Wireless1 (IEEE 802.11a/b/g/n, 2.5/5.0GHz) Wireless PictBridge4
Ink Technology	Dye Based Ink Technology
Ink Droplet Size	Minimum 4 Picoliters
Ink Capacity	12.6ml per ink
Paper Sizes	3.5" x 3.5" (Square), 3.5" x 5", 4" x 6", 5" x 5" (Square), 5" x 7", 7" x 10", 8" x 10", Letter (8.5" x 11"), Legal (8.5" x 14"), 10" x 12", 11" x 17" (Ledger), 12" x 12" (Square), 13" x 19" (A3+), 210x594mm (Panorama Size), Custom (up to 13" x 39")
Maximum Print Length	39 Inches
Media Thickness	Top Feed - Plain Paper: 64 - 105 gsm Top Feed - Photo Paper: Approx. 380 gsm Manual Feed Slot - Photo Paper: Approx. 380 gsm / 0.1 - 0.6 mm
Paper Feed Method	Top Feed and Manual Feed Slot
Genuine Canon Media Compatibility	Plain: Plain Paper Super High Gloss: Photo Paper Pro Platinum Glossy: Photo Paper Plus Glossy II, Photo Paper Glossy Semi-Gloss: Photo Paper Plus Semi-Gloss, Photo Paper Pro Luster Matte: Matte Photo Paper, Photo Paper Premium Matte Fine Art: Premium Fine Art Rough Other: Printable Nail Stickers, Light Fabric Iron Transfers Non-Canon: Inkjet Greeting Cards, Photo Stickers, Cardstock, Printable CD / DVD / Blu-ray Discs, Recycled paper and chlorine-free paper can be used
Languages	33 Supported Languages: Bulgarian, Chinese (Simplified), Chinese (Traditional), Croatian, Czech, Danish, Dutch, English, Estonian, Finnish, French, German, Greek, Hungarian, Indonesian, Italian, Japanese, Korean, Latvian, Lithuanian, Norwegian, Polish, Portuguese, Romanian, Russian, Slovakian, Slovene, Spanish, Swedish, Thai, Turkish, Ukrainian, Vietnamese
Firmware	Printer Languages: Swift Graphic Raster Job Control Language: IVEC Status Reply: IVEC

Noise Level Approx	42.2 dB(A) ¹⁶ (Canon PT-201 Paper)
Physical Dimensions	Closed: 25.2" (L) x 15" (W) x 7.9" (H) Trays Extended: 25.2" (L) x 33" (W) x 16.4" (H)
Weight	32 lbs.
Power Consumption	1.6W ¹⁵ (1.0W Standby, 0.2W Off)
Operating Environment	Operating Temperature ¹⁷ : 41° - 95° F (5° - 35° C) Operating Humidity ¹⁷ : 10 - 90% RH
Warranty	1-Year limited warranty with InstantExchange Program. 1-Year toll-free U.S.-based technical phone support. ¹⁸
Software Included	PIXMA PRO-200 Wireless 13" Professional Inkjet Photo Printer Driver Canon Professional Print & Layout Software ² Media Configuration Tool
Mobile Apps	AirPrint ⁵ , Canon PRINT app ⁷ , Canon Print Service (Android Only), Easy-PhotoPrint Editor app ⁹ , Mopria ⁸ , Cloud Link ³
General Features	Auto Paper Width Detection, Auto Power On /Off, Auto/Manual Print Head Alignment, Driver Correction Mode, Multi-Purpose Tray, Paper Feed Skew Correction, Quiet Mode, Custom MIB (Management Information Base) Support, Optimum Image Generating (OIG) System
Certifications	Energy Star Certified
Display	3.0in Colour LCD