Key Features

10-point IR Touchscreen | Full HD 1080p Resolution |

Durable, Scratch-resistant Screen | 24/7 Anti-Viral

Protection | MultiTouch for MacOS




Product **Description**


Great for public kiosks, POS displays, and other retail and commercial applications, the ViewSonic" TD2423d is a 24" touch display with 10-point IR touch technology that lets users pinch, zoom and swipe for fast and intuitive navigation. With Full HD 1920x1080 resolution, 1000:1 static contrast ratio and 7H screen hardness, the TD2423d delivers sharp and bright images combined with durability for high-traffic applications. Flexible connectivity options include HDMI, DisplayPort, VGA, DVI, and a USB hub to connect your peripherals and accessories. VESA-mount compatibility offers additional convenience and flexibility for 3rd party stands and mounts. What's more, ViewSonic's exclusive ViewMode feature provides intuitive presets that deliver optimized screen performance in different applications. In addition, Flicker-Free technology and a Blue Light Filter help to eliminate eyestrain from extended viewing periods for improved productivity. Whether in retail or deployed in a high-traffic commercial setting, its scratch-resistant surface stands up to heavy use and safeguards its high quality touch experience. Combine this display with ViewSonic's Android and Windows media players for a perfect kiosk solution.



- 1. Stylus Pon 2. Menu Controls
- 3. VESA Compatible 100x100 4. Kensington Lock
- 6. USB-B 7. AC. In 8. Internal Speakers







PANEL



call: 888.881.8781 Contact Sales email: salesinfo@viewsonic.com visit: viewsonic.com

50 - 75 Hz

e gall	200			
)is	pl	av		

Display Size (in):	24
Viewable Area (in.);	24
Panel Type:	MVA
Resolutions	1920 x 1080
Resolution type:	Lull HD (1920x1080)
Static Contrast Ratio:	3,000:1
Light Source.	1FD
Brightness:	250 cd/m2
Colors.	16.7M
Color Space Support:	8 bits
Aspect Ratio.	16.9
Response Time (Typical GLG):	7ms
Viewing Angles:	178º horizontal, 178º vertical
Backlight Life (Hours):	30,000
Connector	

Connector:

USB Type A(2), USB Type B(1), 3.5mm Audio In(1), 3.5mm Audio Out(1), VGA(1), HDMI 1.4 In(1), DisplayPort(1)

Touch:

TOUCH.	
lauch lechnology:	Infrared
Touch Points	10-Point louch
Audio:	
Internal Speakers	2W (x2)
Power:	
Fco Mode (Conserve):	14W
Eco Mode (optimized):	16W
Consumption (typical):	18W
Consumption (max):	21.5W
Voltage:	AC 100-240V (universal), 50-60Hz
Stand-by:	0.5W
Power Supply:	Internal
Additional Hardware:	
WEST STREET, STREET, ST.	12

Kensington Lock Slot:

Controls:

Physical Controls: 1.2.3.4.5.6 (Power) Auto Image Adjust, Contrast/Brightness,

Input Select, Audio Adjust, Color Adjust, Information, Manual Image Adjust, Advanced Image Adjust, Setup Menu. Memory Recall (See user quide for complete QSD functionality)

Operating Conditions:

On Screen Display:

32-104° | (0 - 40° C) lemperature: Humidity (non-condensing): 20-90% Mount: 100 x 100 mm VESA Compatible:

Vid 110

11. VGA

12. DisplayPort

deo Signal:		
equency Horizontal:	24 - 82 KHz	

Frannomics:

ergonomics:	
iiit (Lorward/Back):	220 / 380

Weight (imperial):

Trequency Vertical:

NAME OF TAXABLE PARTY O		
Net (lbs):	11.5	
Net Without Stand (lbs):	10.3	
Ciross (lbs):	15.4	

Weight (metric):

Net (kg):	5.7	
Net Without Stand (kg):	4.7	
Gross (kg):	7.0	

Dimensions (imperial) (WxHxD):

Packaging (in.):	25.4 x 16.6 x 6.5
Physical (in.):	22.5 x 13.7 x 4.0
Physical Without Stand (in.):	22.5 x 13.7 x 2.4

Dimensions (metric) (WxHxD):

Packaging (mm):	6445.0 x 422.0 x 166.0
Physical (mm):	571.0 x 348.0 x 101.0
Physical Without Stand (mm):	571.0 x 348.0 x 61.0
Concept	

Regulations: cTUVus, TCC-B, ICHS003, Energy Star, EPEAL, MX-CoC., Mexico

PACKAGE CONTENTS: 102423d, Power Cable, HDML cable, USB Type B Uplink Cable, Quick Start Guide

Recycle/Disposal: Please dispose of in accordance with local, state or federal

Warranty: Three-year limited warranty on parts, labor and backlight UPC: 766907011685

Accessories:

TCI2-DMA-001, TCI2-WMK-001, NMP520-W, NMP660, 51NI2-042