

BlueParrott M300-XT

ENGINEERED TO KEEP YOU CONNECTED ON THE GO.

Our smallest and lightest Bluetooth® headset with 80% noise cancellation.

- > 80% noise cancellation with 2-mic tech

> Just 0.7 oz / 20 g for all day comfort

> IP54-rated protection against dust and moisture
- > Up to 14 hours of talk time

> Up to 300 ft / 100 m wireless range

> Customizable BlueParrott Button™



TECHNICAL SPECIFICATIONS

Audio	Noise reduction on calls	Yes
	Speaker size	10.3mm 0.41in
	Speaker max input power	5 mW
	Speaker frequency range	20Hz - 20kHz
	Speaker impedance	32 Ω
	Audio codecs supported	SBC
	Microphone type	2 x MEMS
	Microphone sensitivity	-42±1dB (0dB=1V/Pa, at 1KHz)
	Certifications and compliance	FCC, ISCED, CE, RoHS, REACH, Proposition 65
Fit & Comfort	Headset form factor	BT Mono
	EarGels	Large, medium, small
Connectivity	Connectivity	Bluetooth®
	Bluetooth profiles	A2DP v1.3, AVRCP v1.6, HFP v1.7, HSP v1.2
	Bluetooth version	5.1
	Operating range	Up to 100m 300ft
	Bluetooth pairing list	Up to 8 devices
	Simultaneous Bluetooth connections	2
	NFC	Yes
Battery	Talk time	Up to 14 hours
	Corded charging (cable dependent)	USB-C
	Charging time	Up to 150 minutes
	Standby time	Up to 420 hours
	Battery type	Rechargeable lithium ion battery
Software and Apps	Compatible software and apps	BlueParrott App, BlueParrott Updater

TECHNICAL SPECIFICATIONS

General info	Box content	EarGels, headset, user documents, USB cable
	Packaging dimensions (WxHxD)	41.5mm x 175mm x 131mm 1.63in x 6.89in x 5.16in
	Main unit dimensions (WxHxD)	110.7mm x 61mm x 25.4mm 4.36in x 2.4in x 1in
	Weight	20g 0.7oz
	USB cable length	1.2m 3.9ft
	IP rating	IP54
	Warranty	1 Year
Extended info	Operating temperature	-10°C to 60°C 14°F to 140°F
	Storage temperature	-10°C to 45°C 14°F to 113°F

PRODUCT TYPE	SKU	DESCRIPTION
Products	204357	BlueParrott M300-XT
Accessories	204354	BlueParrott M300-XT Refresher Kit